

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P563712

Luminaire Tested: **SQ4-PP3-125U-100D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563712  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 17637.2 lumens  
Efficiency: N/A  
Efficacy: 132.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 133.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563712  
CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563712

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13761	13761	13761
5°	13862	13777	13729
10°	13839	13741	13679
15°	13747	13672	13597
20°	13656	13579	13477
25°	13494	13400	13268
30°	13244	13175	13007
35°	12897	12810	12647
40°	12485	12406	12264
45°	12144	12059	11939
50°	11708	11633	11521
55°	11102	10955	10871
60°	10106	9818	9769
65°	8904	8533	8504
70°	7687	7370	7370
75°	6616	6523	6431
80°	5834	5903	5765
85°	4568	4981	4981



TEST NUMBER: P563712

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	282.1	1.6
10°-20°	805.4	4.6
20°-30°	1206.4	6.8
30°-40°	1415.1	8.0
40°-50°	1419.5	8.0
50°-60°	1210.9	6.9
60°-70°	789.7	4.5
70°-80°	396.2	2.2
80°-90°	113.3	0.6
90°-100°	724.6	4.1
100°-110°	1951.8	11.1
110°-120°	2048.3	11.6
120°-130°	1662.1	9.4
130°-140°	1303.6	7.4
140°-150°	1000.8	5.7
150°-160°	719.6	4.1
160°-170°	439.6	2.5
170°-180°	148.3	0.8
0°-30°	2293.9	13.0
0°-40°	3709.0	21.0
0°-60°	6339.4	35.9
0°-90°	7638.6	43.3
90°-120°	4724.6	26.8
90°-150°	8691.2	49.3
90°-180°	9999.0	56.7
0°-180°	17637.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2983	2983	2983	2983	2983	
5°	2994	2965	2975	2965	2965	284
15°	2878	2850	2863	2852	2847	812
25°	2651	2620	2633	2609	2607	1219
35°	2290	2267	2275	2248	2246	1431
45°	1862	1849	1848	1830	1830	1433
55°	1380	1375	1362	1354	1352	1227
65°	816	800	782	776	779	814
75°	371	371	366	363	361	403
85°	86	94	94	94	94	101
90°	4	12	24	26	26	11
95°	110	394	1188	607	420	115
105°	361	562	2158	3229	3031	380
115°	637	780	1797	3473	3928	627
125°	870	999	1614	2728	3210	777
135°	1048	1169	1569	2201	2492	809
145°	1211	1306	1549	1882	2020	760
155°	1375	1425	1535	1688	1742	633
165°	1492	1509	1541	1602	1610	421
175°	1551	1549	1543	1564	1561	147
180°	1549	1549	1549	1549	1549	



TEST NUMBER: P563712

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2983.1	2983.1	2983.1	2983.1	2983.1
2.5°	3001.9	2977.4	2983.1	2978.6	2966.3
5°	2993.5	2965.4	2975.2	2964.8	2964.8
7.5°	2973.1	2942.5	2952.2	2941.7	2941.2
10°	2954.3	2923.6	2933.4	2922.9	2920.3
12.5°	2927.1	2896.4	2908.3	2895.7	2895.2
15°	2878.5	2850.4	2862.8	2852.2	2847.1
17.5°	2823.6	2792.9	2807.9	2793.2	2791.2
20°	2781.8	2751.1	2766.1	2745.2	2745.2
22.5°	2731.6	2700.9	2718.0	2690.8	2690.8
25°	2651.0	2620.4	2632.7	2609.1	2606.6
27.5°	2555.3	2525.2	2538.1	2511.4	2510.9
30°	2486.3	2458.2	2473.3	2444.4	2441.9
32.5°	2411.0	2385.0	2395.9	2367.0	2364.5
35°	2290.2	2267.2	2274.6	2248.4	2245.8
37.5°	2163.2	2139.7	2148.0	2125.5	2124.5
40°	2073.2	2057.9	2060.2	2041.8	2036.6
42.5°	1989.6	1972.2	1974.4	1956.1	1955.1
45°	1861.5	1848.7	1848.4	1830.1	1830.1
47.5°	1725.5	1715.8	1713.0	1697.8	1697.3
50°	1631.4	1623.7	1620.9	1607.8	1605.3
52.5°	1533.1	1529.5	1520.6	1509.6	1509.1
55°	1380.4	1375.3	1362.1	1354.2	1351.7
57.5°	1214.7	1204.4	1189.6	1178.1	1180.2
60°	1095.4	1085.2	1064.1	1058.8	1058.8
62.5°	980.4	968.1	946.9	939.7	943.8
65°	815.7	800.4	781.7	776.5	779.1
67.5°	666.2	652.4	632.2	632.1	630.1
70°	569.9	562.3	546.4	546.4	546.4
72.5°	484.2	480.6	469.0	469.0	466.9
75°	371.2	371.2	366.0	363.3	360.8
77.5°	278.2	279.2	276.6	273.9	269.3
80°	219.6	224.7	222.2	219.6	217.0
82.5°	165.2	170.3	169.9	165.2	164.7
85°	86.3	93.9	94.1	94.1	94.1
87.5°	23.8	33.5	38.2	38.6	40.7
90°	3.9	11.7	23.7	25.6	25.6
92.5°	48.1	170.1	336.2	161.9	112.5
95°	110.5	394.1	1187.8	607.4	420.3
97.5°	176.4	451.1	1862.9	1556.3	1173.6
100°	226.9	473.8	2077.6	2173.8	1803.4
102.5°	275.8	505.8	2148.6	2636.2	2332.1
105°	361.1	561.7	2158.5	3229.3	3030.6
107.5°	441.6	620.6	2066.6	3534.1	3585.4
110°	495.2	665.0	1982.9	3628.7	3815.9



TEST NUMBER: P563712

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	552.1	709.5	1902.4	3607.8	3915.3
115°	637.3	780.1	1797.4	3473.0	3928.3
117.5°	715.0	848.9	1716.2	3258.0	3765.0
120°	765.5	894.8	1675.1	3103.6	3624.5
122.5°	809.7	937.4	1645.1	2945.7	3465.1
125°	870.1	999.4	1613.9	2727.8	3210.1
127.5°	928.1	1055.4	1594.2	2535.7	2966.3
130°	962.8	1090.2	1586.3	2425.6	2803.7
132.5°	997.6	1123.4	1578.4	2328.6	2675.8
135°	1047.7	1169.2	1568.6	2200.6	2491.9
137.5°	1095.4	1212.0	1563.4	2092.1	2331.3
140°	1128.6	1240.5	1558.7	2025.3	2241.4
142.5°	1163.3	1267.5	1555.5	1963.0	2145.1
145°	1211.4	1306.0	1548.8	1881.5	2020.4
147.5°	1263.5	1345.7	1542.1	1812.9	1922.1
150°	1298.3	1369.6	1539.0	1769.9	1860.6
152.5°	1329.8	1391.9	1537.4	1734.8	1808.5
155°	1375.2	1425.4	1535.0	1688.2	1742.2
157.5°	1415.1	1454.0	1535.4	1655.4	1691.7
160°	1440.3	1473.1	1537.0	1636.3	1663.3
162.5°	1462.4	1489.0	1538.6	1620.3	1639.6
165°	1491.6	1509.0	1540.9	1602.3	1610.0
167.5°	1515.3	1525.3	1542.9	1588.4	1591.5
170°	1531.1	1534.9	1542.9	1580.4	1580.4
172.5°	1540.5	1541.3	1544.5	1572.5	1572.5
175°	1550.8	1548.9	1542.9	1564.5	1560.7
177.5°	1555.2	1552.1	1544.1	1556.7	1553.6
180°	1548.8	1548.8	1548.8	1548.8	1548.8

(END OF REPORT)