

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564024

Luminaire Tested: **SQ4-PR1-050U-125D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564024
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13671.8 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 114.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564024
CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564024

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71		
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60		
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	51		
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44		
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38		
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33		
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32	29		
7	62	50	42	36	59	48	40	35	43	37	33	40	34	30	36	32	28	26		
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	25	23		
9	54	41	34	29	51	40	33	28	37	30	26	33	28	25	31	26	23	21		
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17873	17873	17873
5°	18034	17895	17802
10°	17977	17852	17758
15°	17898	17787	17691
20°	17808	17693	17562
25°	17683	17564	17360
30°	17492	17367	17119
35°	17234	17083	16839
40°	16840	16660	16358
45°	16155	15871	15545
50°	14945	14585	14298
55°	13044	12748	12481
60°	10992	10900	10684
65°	9507	9543	9471
70°	8732	8777	8777
75°	8386	8386	8447
80°	7890	7978	7890
85°	6357	7066	7066



TEST NUMBER: P564024

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.4	2.7
10°-20°	1048.3	7.7
20°-30°	1581.1	11.6
30°-40°	1883.9	13.8
40°-50°	1857.4	13.6
50°-60°	1419.5	10.4
60°-70°	878.4	6.4
70°-80°	498.9	3.6
80°-90°	154.1	1.1
90°-100°	292.9	2.1
100°-110°	795.7	5.8
110°-120°	818.1	6.0
120°-130°	654.1	4.8
130°-140°	513.9	3.8
140°-150°	394.1	2.9
150°-160°	283.4	2.1
160°-170°	173.3	1.3
170°-180°	58.4	0.4
0°-30°	2995.8	21.9
0°-40°	4879.7	35.7
0°-60°	8156.5	59.7
0°-90°	9688.0	70.9
90°-120°	1906.7	13.9
90°-150°	3468.7	25.4
90°-180°	3984.0	29.1
0°-180°	13671.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3874	3874	3874	3874	3874	
5°	3894	3852	3864	3851	3844	369
15°	3748	3708	3724	3711	3704	1058
25°	3474	3432	3451	3414	3411	1599
35°	3060	3024	3034	2993	2990	1910
45°	2476	2444	2433	2389	2383	1897
55°	1622	1596	1585	1558	1552	1453
65°	871	864	874	868	868	882
75°	470	470	470	474	474	497
85°	120	127	134	134	134	140
90°	2	8	14	18	18	8
95°	43	160	510	222	149	46
105°	141	220	875	1332	1254	150
115°	251	305	700	1393	1587	248
125°	345	393	634	1068	1260	308
135°	416	462	616	870	981	322
145°	481	515	608	739	795	302
155°	543	563	604	664	683	251
165°	589	596	606	632	634	166
175°	610	612	608	616	614	58
180°	610	610	610	610	610	

TEST NUMBER: P564024

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3874.4	3874.4	3874.4	3874.4	3874.4
2.5°	3898.5	3864.5	3874.4	3866.0	3847.7
5°	3894.5	3852.0	3864.4	3850.9	3844.4
7.5°	3864.4	3822.7	3835.1	3821.6	3817.7
10°	3837.7	3798.6	3811.0	3797.5	3791.0
12.5°	3808.4	3766.6	3781.7	3765.5	3759.0
15°	3747.6	3708.5	3724.3	3710.8	3704.2
17.5°	3680.9	3639.1	3654.8	3639.3	3630.8
20°	3627.5	3588.3	3604.1	3580.7	3577.4
22.5°	3568.7	3529.6	3545.4	3514.0	3513.4
25°	3474.0	3431.6	3450.6	3413.8	3410.6
27.5°	3361.2	3322.0	3337.8	3300.4	3296.4
30°	3283.8	3244.6	3260.4	3220.2	3213.7
32.5°	3195.7	3159.1	3172.3	3132.2	3128.2
35°	3060.2	3024.3	3033.5	2993.3	2990.1
37.5°	2906.0	2873.4	2878.6	2834.5	2831.2
40°	2796.5	2763.9	2766.5	2719.7	2716.4
42.5°	2676.4	2643.8	2641.0	2594.2	2591.0
45°	2476.2	2443.5	2432.8	2389.3	2382.7
47.5°	2247.9	2215.3	2195.2	2159.7	2155.1
50°	2082.4	2049.8	2032.3	2002.1	1992.3
52.5°	1903.5	1870.9	1856.1	1828.5	1818.7
55°	1621.9	1595.8	1585.1	1558.3	1551.8
57.5°	1354.2	1336.6	1333.5	1307.4	1304.8
60°	1191.4	1181.6	1181.4	1158.0	1158.0
62.5°	1052.5	1045.4	1050.5	1035.1	1032.5
65°	871.0	864.5	874.3	867.7	867.7
67.5°	727.5	727.5	733.5	730.8	730.8
70°	647.4	647.4	650.7	650.7	650.7
72.5°	575.3	572.7	581.3	581.3	578.7
75°	470.5	470.5	470.5	473.9	473.9
77.5°	366.4	367.1	369.8	369.0	366.4
80°	297.0	300.3	300.3	297.0	297.0
82.5°	227.6	230.9	230.9	230.2	227.6
85°	120.1	126.7	133.5	133.5	133.5
87.5°	35.1	46.7	56.1	56.9	54.3
90°	2.0	7.7	13.7	17.7	17.7
92.5°	17.7	80.2	139.3	59.8	50.6
95°	43.2	160.2	510.1	222.0	149.1
97.5°	71.4	176.9	782.0	608.4	427.3
100°	90.2	188.1	865.2	877.1	708.2
102.5°	109.1	199.2	887.2	1084.7	935.8
105°	141.3	219.9	875.0	1332.3	1253.6
107.5°	174.6	244.1	824.4	1460.1	1482.0
110°	198.2	261.5	786.7	1485.3	1579.3



TEST NUMBER: P564024

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.6	278.8	749.1	1464.4	1606.0
115°	251.1	304.8	700.4	1393.4	1587.2
117.5°	281.7	333.1	669.4	1292.7	1511.0
120°	302.1	352.0	655.3	1225.2	1442.0
122.5°	319.4	369.3	645.9	1157.6	1366.7
125°	345.3	393.3	633.7	1067.7	1259.5
127.5°	368.4	416.0	627.0	999.6	1164.2
130°	382.6	428.6	623.9	956.8	1104.5
132.5°	396.7	442.7	620.7	920.4	1051.2
135°	415.9	462.0	616.0	869.7	980.9
137.5°	436.7	478.5	613.7	824.9	918.6
140°	449.3	489.6	612.1	796.5	880.9
142.5°	461.8	499.0	610.5	774.2	844.8
145°	480.7	515.2	608.2	738.9	794.6
147.5°	501.9	531.4	606.2	711.2	754.9
150°	516.0	540.9	606.2	695.3	729.8
152.5°	527.0	548.8	604.7	681.0	709.4
155°	543.4	562.6	604.3	663.6	682.7
157.5°	559.5	574.5	604.3	651.7	666.3
160°	568.9	582.4	604.3	643.8	655.3
162.5°	578.4	588.7	605.8	637.4	645.9
165°	588.6	596.2	606.2	631.8	633.7
167.5°	599.2	603.0	608.2	625.1	626.6
170°	602.3	606.1	608.2	621.9	621.9
172.5°	605.4	607.7	608.2	618.8	618.8
175°	610.1	612.1	608.2	616.0	614.1
177.5°	611.7	611.7	607.0	613.2	610.1
180°	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)