

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564888

Luminaire Tested: **SQ4-PW1-0U-125D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564888
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-125D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9636.9 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 91.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564888
CATALOG NUMBER: SQ4-PW1-0U-125D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564888

CATALOG NUMBER: SQ4-PW1-0U-125D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17473	17473	17473
5°	17586	17447	17370
10°	17446	17305	17211
15°	17260	17069	17005
20°	17054	16792	16759
25°	16816	16510	16460
30°	16461	16212	16105
35°	15993	15768	15674
40°	15494	15253	15193
45°	14891	14696	14631
50°	14274	14155	14058
55°	13607	13607	13393
60°	12777	13024	12562
65°	11693	12276	11401
70°	10307	11297	10038
75°	8803	10111	8566
80°	6827	8512	6915
85°	4414	6537	5828



TEST NUMBER: P564888

CATALOG NUMBER: SQ4-PW1-0U-125D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	356.7	3.7
10°-20°	1007.0	10.4
20°-30°	1493.7	15.5
30°-40°	1747.8	18.1
40°-50°	1740.0	18.1
50°-60°	1502.5	15.6
60°-70°	1081.5	11.2
70°-80°	567.2	5.9
80°-90°	140.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2857.3	29.6
0°-40°	4605.1	47.8
0°-60°	7847.5	81.4
0°-90°	9636.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9636.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3788	3788	3788	3788	3788	
5°	3798	3755	3768	3758	3751	360
15°	3614	3568	3574	3567	3561	1019
25°	3304	3248	3244	3224	3234	1519
35°	2840	2801	2800	2773	2783	1775
45°	2283	2263	2253	2246	2243	1761
55°	1692	1689	1692	1668	1665	1510
65°	1071	1104	1125	1080	1044	1062
75°	494	540	567	530	481	529
85°	83	110	124	117	110	113
90°	0	0	0	0	0	



TEST NUMBER: P564888

CATALOG NUMBER: SQ4-PW1-0U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3787.7	3787.7	3787.7	3787.7	3787.7
2.5°	3809.0	3777.7	3787.7	3779.3	3761.0
5°	3797.7	3755.3	3767.7	3757.5	3751.0
7.5°	3759.0	3719.8	3728.9	3718.2	3714.3
10°	3724.3	3685.1	3694.2	3680.7	3674.2
12.5°	3684.2	3642.5	3651.5	3638.1	3634.2
15°	3614.1	3568.5	3574.1	3567.3	3560.7
17.5°	3532.7	3486.4	3487.3	3476.6	3475.3
20°	3474.0	3425.0	3420.6	3407.4	3413.9
22.5°	3409.9	3358.4	3353.8	3335.4	3344.5
25°	3303.8	3248.3	3243.7	3223.9	3233.7
27.5°	3181.0	3126.2	3126.3	3098.5	3108.9
30°	3090.2	3038.0	3043.5	3010.4	3023.5
32.5°	2994.1	2947.1	2950.0	2917.0	2930.0
35°	2839.9	2800.8	2799.9	2773.4	2783.2
37.5°	2682.4	2647.8	2642.4	2627.1	2629.7
40°	2572.9	2543.6	2532.9	2522.9	2522.9
42.5°	2458.2	2431.4	2420.8	2413.4	2410.8
45°	2282.6	2263.0	2252.6	2245.8	2242.6
47.5°	2109.1	2090.8	2081.7	2077.0	2073.7
50°	1988.9	1975.9	1972.3	1962.2	1958.9
52.5°	1868.8	1861.0	1857.5	1844.7	1841.4
55°	1691.9	1688.7	1691.9	1668.5	1665.2
57.5°	1507.7	1512.9	1523.7	1492.2	1484.4
60°	1384.9	1398.0	1411.6	1374.6	1361.6
62.5°	1259.4	1280.3	1299.5	1257.0	1238.8
65°	1071.2	1103.9	1124.6	1080.4	1044.5
67.5°	889.7	930.1	955.1	907.5	867.0
70°	764.2	809.9	837.6	789.9	744.2
72.5°	654.8	705.7	728.2	683.1	637.4
75°	493.9	539.6	567.3	529.5	480.6
77.5°	350.4	393.5	416.5	383.5	343.1
80°	257.0	302.6	320.4	292.9	260.3
82.5°	182.2	220.1	232.3	215.7	193.6
85°	83.4	109.5	123.5	116.7	110.1
87.5°	21.4	39.6	50.7	50.8	53.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)