

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564936

Luminaire Tested: **SQ4-PW1-100U-075D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564936
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-075D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13718.6 lumens
Efficiency: N/A
Efficacy: 132.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 103.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564936
CATALOG NUMBER: SQ4-PW1-100U-075D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564936

CATALOG NUMBER: SQ4-PW1-100U-075D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35				
2	87	80	74	69	79	73	68	64	60	57	54	49	46	44	38	36	35	30				
3	80	70	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25				
4	73	62	55	49	66	57	50	45	47	42	38	38	35	32	30	27	25	22				
5	67	55	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16				
7	57	45	37	32	52	41	34	29	35	29	25	28	24	21	22	19	17	15				
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10305	10305	10305
5°	10371	10289	10244
10°	10289	10206	10150
15°	10180	10067	10029
20°	10058	9903	9884
25°	9917	9737	9707
30°	9708	9561	9498
35°	9432	9299	9244
40°	9138	8996	8960
45°	8782	8667	8629
50°	8418	8348	8291
55°	8025	8025	7899
60°	7536	7681	7409
65°	6896	7240	6724
70°	6079	6663	5920
75°	5192	5964	5051
80°	4025	5018	4078
85°	2604	3853	3435



TEST NUMBER: P564936

CATALOG NUMBER: SQ4-PW1-100U-075D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.3	1.5
10°-20°	593.9	4.3
20°-30°	880.9	6.4
30°-40°	1030.8	7.5
40°-50°	1026.2	7.5
50°-60°	886.1	6.5
60°-70°	637.9	4.6
70°-80°	334.5	2.4
80°-90°	85.5	0.6
90°-100°	579.0	4.2
100°-110°	1598.3	11.7
110°-120°	1648.4	12.0
120°-130°	1324.6	9.7
130°-140°	1041.0	7.6
140°-150°	798.4	5.8
150°-160°	573.8	4.2
160°-170°	350.9	2.6
170°-180°	118.3	0.9
0°-30°	1685.1	12.3
0°-40°	2715.9	19.8
0°-60°	4628.2	33.7
0°-90°	5686.0	41.4
90°-120°	3825.6	27.9
90°-150°	6989.6	50.9
90°-180°	8033.0	58.6
0°-180°	13718.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2234	2234	2234	2234	2234	
5°	2240	2215	2222	2216	2212	212
15°	2132	2104	2108	2104	2100	601
25°	1948	1916	1913	1901	1907	896
35°	1675	1652	1651	1636	1641	1047
45°	1346	1335	1328	1324	1323	1039
55°	998	996	998	984	982	890
65°	632	651	663	637	616	626
75°	291	318	335	312	283	312
85°	49	65	73	69	65	65
90°	4	8	16	18	20	8
95°	85	313	1050	432	281	91
105°	285	440	1758	2685	2528	303
115°	510	617	1416	2804	3189	501
125°	700	797	1284	2172	2550	623
135°	843	934	1248	1760	1984	652
145°	977	1045	1232	1498	1612	612
155°	1102	1138	1222	1344	1387	508
165°	1193	1208	1228	1276	1286	336
175°	1236	1238	1230	1248	1244	117
180°	1236	1236	1236	1236	1236	

TEST NUMBER: P564936

CATALOG NUMBER: SQ4-PW1-100U-075D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2233.8	2233.8	2233.8	2233.8	2233.8
2.5°	2246.4	2227.9	2233.8	2228.9	2218.1
5°	2239.7	2214.7	2222.0	2216.0	2212.2
7.5°	2216.9	2193.8	2199.2	2192.8	2190.5
10°	2196.4	2173.3	2178.7	2170.8	2166.9
12.5°	2172.8	2148.2	2153.5	2145.6	2143.3
15°	2131.5	2104.5	2107.9	2103.8	2100.0
17.5°	2083.5	2056.1	2056.7	2050.4	2049.6
20°	2048.8	2020.0	2017.3	2009.5	2013.4
22.5°	2011.0	1980.6	1978.0	1967.1	1972.5
25°	1948.4	1915.7	1913.0	1901.3	1907.1
27.5°	1876.0	1843.7	1843.7	1827.3	1833.5
30°	1822.5	1791.7	1794.9	1775.4	1783.1
32.5°	1765.8	1738.1	1739.8	1720.3	1728.0
35°	1674.9	1651.8	1651.3	1635.6	1641.4
37.5°	1582.0	1561.6	1558.4	1549.3	1550.9
40°	1517.4	1500.1	1493.8	1487.9	1487.9
42.5°	1449.7	1433.9	1427.7	1423.3	1421.8
45°	1346.2	1334.7	1328.5	1324.5	1322.6
47.5°	1243.9	1233.1	1227.7	1224.9	1223.0
50°	1173.0	1165.3	1163.2	1157.2	1155.3
52.5°	1102.2	1097.5	1095.5	1087.9	1086.0
55°	997.8	995.9	997.8	984.0	982.1
57.5°	889.2	892.3	898.6	880.0	875.4
60°	816.8	824.5	832.5	810.7	803.0
62.5°	742.8	755.1	766.4	741.3	730.6
65°	631.8	651.0	663.3	637.2	616.0
67.5°	524.7	548.6	563.3	535.2	511.3
70°	450.7	477.6	494.0	465.8	438.9
72.5°	386.1	416.2	429.4	402.9	375.9
75°	291.3	318.2	334.6	312.3	283.4
77.5°	206.7	232.1	245.6	226.2	202.3
80°	151.5	178.5	188.9	172.8	153.5
82.5°	107.5	129.8	137.0	127.2	114.2
85°	49.2	64.6	72.8	68.8	64.9
87.5°	13.4	24.9	33.1	33.5	35.4
90°	4.0	7.8	15.8	17.8	19.8
92.5°	35.6	147.8	264.3	96.4	75.2
95°	85.1	313.3	1050.3	431.7	280.9
97.5°	140.8	350.9	1555.9	1197.9	867.6
100°	182.0	373.5	1742.6	1755.0	1426.2
102.5°	221.5	399.1	1779.0	2168.4	1856.6
105°	284.8	439.6	1758.5	2684.6	2527.9
107.5°	352.1	489.8	1660.4	2933.5	2990.8
110°	399.6	523.3	1584.4	2987.1	3172.8



TEST NUMBER: P564936

CATALOG NUMBER: SQ4-PW1-100U-075D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	442.3	561.4	1513.2	2944.8	3218.7
115°	510.3	616.7	1416.3	2803.7	3188.6
117.5°	569.7	675.7	1352.6	2605.1	3043.0
120°	609.2	713.7	1327.3	2470.7	2911.7
122.5°	647.2	747.0	1306.7	2345.2	2762.9
125°	700.2	796.9	1283.7	2172.5	2549.7
127.5°	745.3	842.0	1270.3	2026.6	2351.9
130°	775.4	872.1	1264.0	1937.3	2233.2
132.5°	803.9	895.9	1257.6	1862.3	2130.3
135°	842.6	933.5	1248.1	1759.6	1984.0
137.5°	886.2	968.9	1243.4	1673.4	1864.9
140°	909.9	991.1	1240.2	1615.9	1784.2
142.5°	936.8	1011.8	1237.1	1564.8	1713.0
145°	977.1	1044.8	1232.3	1498.0	1612.1
147.5°	1015.9	1075.1	1228.0	1441.6	1530.2
150°	1044.4	1092.8	1226.4	1408.0	1479.6
152.5°	1066.6	1111.8	1224.8	1379.2	1438.4
155°	1101.8	1138.5	1222.4	1344.1	1386.6
157.5°	1134.2	1162.4	1222.8	1318.4	1347.4
160°	1153.2	1178.3	1224.4	1304.0	1325.3
162.5°	1169.0	1191.1	1226.0	1291.2	1307.9
165°	1192.8	1208.2	1228.4	1276.1	1285.7
167.5°	1211.0	1220.2	1230.3	1266.8	1269.9
170°	1220.4	1228.2	1230.3	1262.0	1262.0
172.5°	1228.4	1233.0	1230.3	1255.6	1254.1
175°	1236.3	1238.2	1230.3	1248.1	1244.2
177.5°	1239.4	1237.9	1229.9	1240.9	1237.9
180°	1236.3	1236.3	1236.3	1236.3	1236.3

(END OF REPORT)