

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519146

Luminaire Tested: **SQ4-WB-050U-125D-835-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519146
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-050U-125D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12196.1 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 114.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519146
CATALOG NUMBER: SQ4-WB-050U-125D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519146

CATALOG NUMBER: SQ4-WB-050U-125D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	103	99	96	93	97	94	91	88	84	82	80	75	73	71	66	65	64	60				
2	95	89	83	79	90	84	79	75	75	72	69	67	65	62	60	58	56	53				
3	88	79	73	67	83	75	70	65	68	63	60	61	58	55	55	52	50	47				
4	81	72	64	59	77	68	62	57	62	57	52	56	52	48	50	47	44	41				
5	76	65	57	52	71	62	55	50	56	51	47	51	47	43	46	43	40	37				
6	70	59	51	46	66	56	49	44	51	46	42	47	42	39	42	39	36	34				
7	65	54	46	41	62	52	45	40	47	42	38	43	39	35	39	36	33	31				
8	61	50	42	37	58	48	41	36	44	38	34	40	35	32	37	33	30	28				
9	57	46	39	34	54	44	37	33	40	35	31	37	33	29	34	30	28	26				
10	54	42	36	31	51	41	34	30	38	32	29	35	30	27	32	28	25	24				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25991	25991	25991
5°	25666	25575	25724
10°	24249	24469	25036
15°	22385	22905	23932
20°	20328	21093	22488
25°	18233	19227	20951
30°	16303	17369	19358
35°	14256	15287	17472
40°	11999	12952	15125
45°	9903	10757	12628
50°	8268	9013	10521
55°	7019	7735	8689
60°	5999	6706	6933
65°	4777	5640	4480
70°	4235	4401	2734
75°	3921	3568	1674
80°	3613	3284	1445
85°	3271	3012	1175



TEST NUMBER: P519146

CATALOG NUMBER: SQ4-WB-050U-125D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	516.8	4.2
10°-20°	1344.2	11.0
20°-30°	1741.1	14.3
30°-40°	1704.9	14.0
40°-50°	1305.0	10.7
50°-60°	869.6	7.1
60°-70°	474.5	3.9
70°-80°	197.7	1.6
80°-90°	58.3	0.5
90°-100°	292.9	2.4
100°-110°	795.7	6.5
110°-120°	818.1	6.7
120°-130°	654.1	5.4
130°-140°	513.9	4.2
140°-150°	394.1	3.2
150°-160°	283.4	2.3
160°-170°	173.3	1.4
170°-180°	58.4	0.5
0°-30°	3602.0	29.5
0°-40°	5307.0	43.5
0°-60°	7481.6	61.3
0°-90°	8212.3	67.3
90°-120°	1906.7	15.6
90°-150°	3468.7	28.4
90°-180°	3984.0	32.7
0°-180°	12196.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5634	5634	5634	5634	5634	
5°	5543	5487	5523	5536	5555	516
15°	4687	4670	4796	4926	5011	1309
25°	3582	3592	3778	3942	4116	1647
35°	2532	2544	2714	2897	3103	1574
45°	1518	1547	1649	1774	1936	1184
55°	873	909	962	998	1080	791
65°	438	474	517	452	410	455
75°	220	220	200	138	94	235
85°	62	62	57	37	22	67
90°	2	8	14	18	18	6
95°	43	160	510	222	149	46
105°	141	220	875	1332	1254	150
115°	251	305	700	1393	1587	248
125°	345	393	634	1068	1260	308
135°	416	462	616	870	981	322
145°	481	515	608	739	795	302
155°	543	563	604	664	683	251
165°	589	596	606	632	634	166
175°	610	612	608	616	614	58
180°	610	610	610	610	610	

TEST NUMBER: P519146

CATALOG NUMBER: SQ4-WB-050U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5634.1	5634.1	5634.1	5634.1	5634.1
2.5°	5647.9	5597.7	5610.4	5610.0	5594.5
5°	5542.6	5487.0	5522.8	5535.6	5555.0
7.5°	5336.9	5294.9	5360.2	5408.5	5447.7
10°	5176.7	5140.5	5223.7	5294.1	5344.8
12.5°	4990.8	4960.4	5063.5	5158.0	5224.2
15°	4687.2	4670.3	4796.0	4926.5	5011.1
17.5°	4362.4	4354.2	4498.4	4650.6	4758.9
20°	4140.9	4138.5	4296.6	4455.2	4580.9
22.5°	3917.4	3922.7	4089.0	4253.9	4397.0
25°	3582.2	3591.9	3777.5	3942.1	4116.2
27.5°	3272.2	3276.5	3468.5	3642.3	3827.9
30°	3060.6	3072.6	3260.8	3440.7	3634.1
32.5°	2848.9	2863.0	3047.2	3233.1	3430.4
35°	2531.5	2543.6	2714.5	2897.1	3102.6
37.5°	2204.2	2220.6	2372.3	2545.0	2747.1
40°	1992.6	2016.7	2150.8	2313.5	2511.7
42.5°	1788.9	1818.8	1943.1	2097.5	2276.4
45°	1517.9	1546.9	1648.9	1773.8	1935.7
47.5°	1284.5	1317.9	1396.3	1503.8	1642.0
50°	1152.0	1183.5	1255.9	1335.5	1466.0
52.5°	1035.3	1066.8	1131.3	1192.6	1303.8
55°	872.7	908.9	961.7	998.2	1080.3
57.5°	739.2	774.0	815.8	832.3	882.1
60°	650.2	688.9	726.8	725.0	751.5
62.5°	569.1	602.0	639.8	613.6	615.1
65°	437.6	473.8	516.7	451.5	410.4
67.5°	353.5	361.3	405.4	314.8	266.0
70°	314.0	314.0	326.3	243.8	202.7
72.5°	276.4	276.4	265.0	198.3	155.3
75°	220.0	220.0	200.2	137.5	93.9
77.5°	169.6	167.7	153.3	102.6	68.2
80°	136.0	136.0	123.6	81.0	54.4
82.5°	106.3	106.3	95.9	63.3	40.5
85°	61.8	61.8	56.9	36.8	22.2
87.5°	22.1	23.3	22.5	15.4	13.4
90°	2.0	7.7	13.7	17.7	17.7
92.5°	17.7	80.2	139.3	59.8	50.6
95°	43.2	160.2	510.1	222.0	149.1
97.5°	71.4	176.9	782.0	608.4	427.3
100°	90.2	188.1	865.2	877.1	708.2
102.5°	109.1	199.2	887.2	1084.7	935.8
105°	141.3	219.9	875.0	1332.3	1253.6
107.5°	174.6	244.1	824.4	1460.1	1482.0
110°	198.2	261.5	786.7	1485.3	1579.3

TEST NUMBER: P519146

CATALOG NUMBER: SQ4-WB-050U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.6	278.8	749.1	1464.4	1606.0
115°	251.1	304.8	700.4	1393.4	1587.2
117.5°	281.7	333.1	669.4	1292.7	1511.0
120°	302.1	352.0	655.3	1225.2	1442.0
122.5°	319.4	369.3	645.9	1157.6	1366.7
125°	345.3	393.3	633.7	1067.7	1259.5
127.5°	368.4	416.0	627.0	999.6	1164.2
130°	382.6	428.6	623.9	956.8	1104.5
132.5°	396.7	442.7	620.7	920.4	1051.2
135°	415.9	462.0	616.0	869.7	980.9
137.5°	436.7	478.5	613.7	824.9	918.6
140°	449.3	489.6	612.1	796.5	880.9
142.5°	461.8	499.0	610.5	774.2	844.8
145°	480.7	515.2	608.2	738.9	794.6
147.5°	501.9	531.4	606.2	711.2	754.9
150°	516.0	540.9	606.2	695.3	729.8
152.5°	527.0	548.8	604.7	681.0	709.4
155°	543.4	562.6	604.3	663.6	682.7
157.5°	559.5	574.5	604.3	651.7	666.3
160°	568.9	582.4	604.3	643.8	655.3
162.5°	578.4	588.7	605.8	637.4	645.9
165°	588.6	596.2	606.2	631.8	633.7
167.5°	599.2	603.0	608.2	625.1	626.6
170°	602.3	606.1	608.2	621.9	621.9
172.5°	605.4	607.7	608.2	618.8	618.8
175°	610.1	612.1	608.2	616.0	614.1
177.5°	611.7	611.7	607.0	613.2	610.1
180°	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)