

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937215

Luminaire Tested: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937215
REPORT IS A COMBINATION OF REPORTS P933511 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9262.0 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937215
CATALOG NUMBER: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P937215

CATALOG NUMBER: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	50	49	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	43	41	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	38	35	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	33	30	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	30	26	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	27	23	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	20	17	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	19	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3813	3813	3813
5°	3724	4405	5125
10°	3376	6421	8496
15°	2869	8387	10259
20°	2334	9716	10456
25°	1947	10165	10243
30°	1641	10226	10224
35°	1450	10054	10489
40°	1262	9830	10761
45°	1143	9666	10803
50°	1047	9518	10625
55°	1002	9301	10154
60°	1025	8889	9410
65°	1064	8264	8388
70°	1131	7202	7087
75°	1249	5867	5530
80°	1354	4063	3727
85°	1180	2152	1908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10803 cd/sqm



TEST NUMBER: P937215

CATALOG NUMBER: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	0.9
10°-20°	353.4	3.8
20°-30°	618.1	6.7
30°-40°	795.6	8.6
40°-50°	888.7	9.6
50°-60°	851.2	9.2
60°-70°	674.5	7.3
70°-80°	396.7	4.3
80°-90°	112.8	1.2
90°-100°	337.7	3.6
100°-110°	887.9	9.6
110°-120°	920.6	9.9
120°-130°	738.5	8.0
130°-140°	579.4	6.3
140°-150°	444.7	4.8
150°-160°	320.3	3.5
160°-170°	196.0	2.1
170°-180°	66.2	0.7
0°-30°	1051.1	11.3
0°-40°	1846.8	19.9
0°-60°	3586.6	38.7
0°-90°	4770.7	51.5
90°-120°	2146.2	23.2
90°-150°	3908.9	42.2
90°-180°	4491.0	48.5
0°-180°	9262.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	616	616	616	616	616	
5°	600	644	725	820	850	55
15°	450	830	1399	1696	1750	125
25°	287	941	1667	1740	1742	132
35°	194	900	1570	1659	1724	121
45°	133	717	1387	1589	1661	103
55°	95	456	1177	1367	1405	87
65°	75	242	874	983	997	75
75°	56	149	480	527	529	58
85°	20	46	119	131	133	21
90°	5	13	35	18	18	5
95°	45	175	582	300	204	50
105°	160	242	982	1490	1390	170
115°	284	345	786	1568	1790	281
125°	395	443	715	1208	1426	351
135°	471	518	693	976	1106	364
145°	546	581	684	832	897	342
155°	618	635	684	751	773	284
165°	666	675	684	711	720	188
175°	693	693	689	698	698	66
180°	693	693	693	693	693	



TEST NUMBER: P937215

CATALOG NUMBER: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3
2.5°	616.3	616.3	620.3	622.3	626.2	628.2	632.2	636.2	648.0	650.0	654.0
5°	600.5	608.4	634.2	644.1	671.8	709.5	725.3	751.1	804.6	820.5	830.4
7.5°	576.7	594.5	658.0	673.8	743.2	842.3	883.9	939.4	1024.6	1066.2	1099.9
10°	539.0	576.7	689.7	727.3	840.3	990.9	1068.2	1145.5	1274.3	1331.8	1353.6
12.5°	497.4	558.9	723.4	774.9	937.4	1157.4	1250.5	1335.7	1482.4	1559.7	1571.6
15°	449.9	533.1	755.1	830.4	1040.4	1296.1	1399.2	1504.2	1640.9	1696.4	1710.3
17.5°	408.3	513.3	784.8	864.1	1119.7	1421.0	1526.0	1613.2	1724.2	1761.8	1771.7
20°	356.7	481.6	804.6	907.7	1203.0	1512.1	1613.2	1680.6	1755.9	1779.7	1783.6
22.5°	319.1	447.9	816.5	923.5	1258.4	1567.6	1652.8	1706.3	1757.9	1765.8	1767.8
25°	287.4	410.2	814.5	941.4	1306.0	1601.3	1666.7	1706.3	1736.1	1740.0	1740.0
27.5°	257.6	368.6	806.6	945.3	1341.7	1609.2	1660.7	1688.5	1702.4	1710.3	1710.3
30°	231.9	329.0	786.8	937.4	1357.5	1601.3	1642.9	1656.8	1670.7	1682.5	1688.5
32.5°	212.1	291.3	757.0	921.5	1359.5	1581.5	1611.2	1619.1	1638.9	1666.7	1676.6
35°	194.2	253.7	723.4	899.7	1347.6	1549.8	1569.6	1577.5	1617.1	1658.8	1672.6
37.5°	176.4	225.9	679.8	862.1	1329.8	1512.1	1526.0	1539.9	1601.3	1650.8	1666.7
40°	158.5	202.1	628.2	820.5	1302.0	1466.5	1478.4	1500.2	1581.5	1638.9	1654.8
42.5°	144.7	182.3	572.7	776.9	1266.4	1415.0	1432.8	1464.5	1557.7	1619.1	1637.0
45°	132.8	162.5	513.3	717.4	1220.8	1361.5	1387.3	1430.9	1529.9	1589.4	1605.3
47.5°	120.9	148.6	451.9	656.0	1171.2	1308.0	1341.7	1391.2	1492.3	1549.8	1563.6
50°	111.0	134.8	390.4	590.6	1117.7	1250.5	1290.2	1341.7	1444.7	1498.2	1516.1
52.5°	103.1	122.9	332.9	525.2	1056.3	1191.1	1236.6	1290.2	1387.3	1438.8	1450.7
55°	95.1	113.0	283.4	455.8	992.9	1127.6	1177.2	1228.7	1323.8	1367.4	1375.4
57.5°	91.2	105.0	241.8	390.4	925.5	1056.3	1111.8	1159.4	1248.5	1282.2	1290.2
60°	85.2	99.1	210.1	334.9	852.2	988.9	1036.5	1084.0	1159.4	1187.1	1193.0
62.5°	79.3	95.1	186.3	281.4	776.9	909.6	957.2	1000.8	1064.2	1084.0	1092.0
65°	75.3	91.2	168.5	241.8	699.6	826.4	874.0	911.6	963.2	983.0	986.9
67.5°	71.3	87.2	154.6	208.1	622.3	743.2	778.8	814.5	854.2	874.0	876.0
70°	65.4	83.2	142.7	184.3	543.0	648.0	677.8	715.4	747.1	757.0	763.0
72.5°	61.4	77.3	134.8	166.5	461.8	556.9	584.6	606.4	634.2	644.1	644.1
75°	55.5	69.4	126.8	148.6	378.5	455.8	479.6	501.4	523.2	527.2	521.2
77.5°	49.5	61.4	109.0	124.9	295.3	360.7	380.5	392.4	410.2	414.2	416.2
80°	41.6	53.5	85.2	97.1	214.0	265.6	279.4	289.3	305.2	305.2	309.2
82.5°	31.7	41.6	61.4	69.4	144.7	182.3	194.2	200.2	210.1	210.1	210.1
85°	19.8	25.8	39.6	45.6	87.2	111.0	118.9	120.9	128.8	130.8	130.8
87.5°	9.9	13.9	25.8	27.7	45.6	57.5	57.5	61.4	61.4	59.5	57.5
90°	4.6	8.3	12.1	13.0	20.4	30.3	35.3	31.4	23.6	17.7	17.7
92.5°	18.6	50.2	81.8	89.7	126.1	174.7	199.0	174.4	125.2	88.3	84.8
95°	44.6	102.5	160.3	174.8	310.4	491.3	581.7	519.1	393.8	299.9	289.3
97.5°	77.2	128.2	179.2	192.0	418.2	719.7	870.5	830.9	751.8	692.4	672.1
100°	102.3	148.6	194.9	206.5	457.4	792.0	959.3	962.2	968.0	972.3	948.2
102.5°	123.7	166.9	210.1	220.9	475.4	814.7	984.4	1034.8	1135.7	1211.3	1190.6
105°	160.0	196.6	233.2	242.3	488.7	817.3	981.6	1094.6	1320.7	1490.3	1479.2
107.5°	197.2	231.3	265.4	273.9	491.2	780.9	925.8	1083.5	1398.9	1635.4	1638.1
110°	222.3	253.1	283.8	291.5	487.4	748.7	879.3	1055.6	1408.2	1672.6	1684.2



TEST NUMBER: P937215

CATALOG NUMBER: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	246.9	276.2	305.6	312.9	487.6	720.5	837.0	1017.4	1378.2	1648.8	1666.6
115°	284.1	311.2	338.2	345.0	492.1	688.2	786.3	960.1	1307.7	1568.4	1593.0
117.5°	320.8	345.4	370.0	376.2	501.3	668.0	751.4	908.3	1222.0	1457.3	1484.6
120°	342.2	365.4	388.5	394.3	508.7	661.2	737.5	880.8	1167.4	1382.4	1409.0
122.5°	363.2	386.5	409.9	415.7	519.4	657.7	726.8	855.8	1113.9	1307.5	1333.7
125°	395.2	416.5	437.8	443.1	533.8	654.7	715.2	824.8	1044.1	1208.5	1232.6
127.5°	421.3	442.8	464.2	469.6	548.2	653.0	705.4	799.5	987.8	1129.0	1149.4
130°	435.2	458.4	481.5	487.3	558.8	654.1	701.7	785.5	953.1	1078.8	1097.6
132.5°	449.6	472.8	495.9	501.7	567.3	654.7	698.4	773.4	923.5	1036.0	1052.8
135°	471.0	492.1	513.2	518.5	576.6	654.1	692.8	755.6	881.3	975.5	990.0
137.5°	492.9	513.7	534.6	539.8	590.5	658.1	691.9	745.0	851.2	930.9	942.8
140°	511.0	530.2	549.5	554.3	599.1	658.8	688.6	734.5	826.3	895.1	906.2
142.5°	525.0	542.8	560.6	565.0	606.2	661.1	688.6	728.9	809.5	870.0	879.6
145°	546.4	561.9	577.3	581.2	615.5	661.2	684.0	717.0	782.9	832.3	839.5
147.5°	567.7	582.8	597.9	601.7	629.1	665.7	684.0	709.9	761.8	800.7	806.7
150°	581.7	595.3	609.0	612.4	636.3	668.1	684.0	705.9	749.7	782.6	787.5
152.5°	596.1	606.5	616.8	619.4	640.9	669.6	684.0	702.7	740.1	768.2	771.9
155°	617.5	625.1	632.8	634.7	651.1	673.0	684.0	698.9	728.7	751.0	753.4
157.5°	633.3	640.8	648.2	650.1	661.4	676.5	684.0	695.6	718.7	736.1	737.8
160°	644.0	649.8	655.6	657.0	666.0	678.0	684.0	693.9	713.7	728.6	729.6
162.5°	654.7	659.1	663.4	664.5	671.0	679.7	684.0	692.4	709.1	721.7	722.6
165°	666.3	670.3	674.2	675.2	678.1	682.0	684.0	690.0	702.0	711.0	712.0
167.5°	677.0	678.9	680.7	681.2	683.7	687.0	688.6	692.5	700.4	706.3	706.7
170°	684.0	685.9	687.7	688.2	688.3	688.5	688.6	692.5	700.4	706.3	706.3
172.5°	687.7	688.1	688.5	688.6	688.6	688.6	688.6	691.7	697.9	702.6	702.2
175°	692.8	692.8	692.8	692.8	691.4	689.5	688.6	690.6	694.5	697.5	697.5
177.5°	692.8	692.8	692.8	692.8	691.7	690.3	689.6	691.2	694.3	696.6	696.2
180°	692.8	692.8	692.8	692.8	692.8	692.8	692.8	692.8	692.8	692.8	692.8



TEST NUMBER: P937215

CATALOG NUMBER: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	616.3	616.3
2.5°	658.0	654.0
5°	846.2	850.2
7.5°	1139.5	1137.6
10°	1417.0	1434.8
12.5°	1619.1	1623.1
15°	1742.0	1749.9
17.5°	1789.6	1791.5
20°	1791.5	1787.6
22.5°	1769.7	1765.8
25°	1744.0	1742.0
27.5°	1720.2	1722.2
30°	1710.3	1716.2
32.5°	1710.3	1720.2
35°	1714.3	1724.2
37.5°	1712.3	1724.2
40°	1704.3	1718.2
42.5°	1682.5	1692.5
45°	1648.9	1660.7
47.5°	1605.3	1613.2
50°	1549.8	1557.7
52.5°	1480.4	1482.4
55°	1397.2	1405.1
57.5°	1308.0	1310.0
60°	1208.9	1214.8
62.5°	1103.9	1103.9
65°	992.9	996.8
67.5°	877.9	887.8
70°	761.0	763.0
72.5°	646.1	646.1
75°	527.2	529.1
77.5°	414.2	414.2
80°	307.2	309.2
82.5°	212.1	216.0
85°	132.8	132.8
87.5°	61.4	55.5
90°	17.7	17.7
92.5°	70.7	56.7
95°	246.7	204.1
97.5°	591.1	510.1
100°	851.6	755.1
102.5°	1108.0	1025.3
105°	1434.7	1390.3
107.5°	1648.8	1659.5
110°	1730.4	1776.7



TEST NUMBER: P937215

CATALOG NUMBER: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1737.7	1808.8
115°	1691.6	1790.2
117.5°	1593.9	1703.2
120°	1515.2	1621.4
122.5°	1438.5	1543.3
125°	1329.2	1425.7
127.5°	1230.8	1312.2
130°	1172.8	1248.0
132.5°	1120.2	1187.6
135°	1048.1	1106.2
137.5°	990.3	1037.9
140°	950.7	995.1
142.5°	917.8	956.0
145°	868.5	897.4
147.5°	830.6	854.6
150°	806.9	826.3
152.5°	786.5	801.2
155°	763.1	772.8
157.5°	744.6	751.4
160°	733.5	737.5
162.5°	726.3	730.0
165°	715.9	719.8
167.5°	708.4	710.0
170°	706.3	706.3
172.5°	700.8	699.3
175°	697.5	697.5
177.5°	694.5	692.8
180°	692.8	692.8



TEST NUMBER: P937215
 CATALOG NUMBER: SQ4-FB-075U-100D-835-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.79	6.70	6.72	7.66	8.91	18.95	19.87	19.89	20.83	22.07
	3H	6.50	7.32	7.44	8.29	9.56	20.79	21.61	21.74	22.58	23.85
	4H	6.80	7.58	7.76	8.55	9.83	21.44	22.21	22.40	23.19	24.46
	6H	7.05	7.77	8.02	8.75	10.04	21.86	22.58	22.84	23.56	24.85
	8H	7.12	7.81	8.10	8.80	10.09	21.98	22.67	22.96	23.67	24.95
	12H	7.14	7.79	8.13	8.78	10.10	22.05	22.70	23.04	23.69	25.01
4H	2H	13.00	13.78	13.97	14.75	16.03	19.23	20.01	20.20	20.99	22.26
	3H	14.57	15.23	15.55	16.23	17.52	21.28	21.93	22.26	22.93	24.23
	4H	14.67	15.27	15.66	16.26	17.58	22.05	22.64	23.03	23.64	24.95
	6H	14.69	15.20	15.68	16.22	17.53	22.58	23.10	23.58	24.12	25.43
	8H	14.66	15.15	15.66	16.16	17.49	22.75	23.23	23.75	24.24	25.57
	12H	14.62	15.06	15.64	16.09	17.42	22.84	23.27	23.86	24.30	25.64
8H	4H	16.12	16.60	17.12	17.61	18.94	22.11	22.59	23.11	23.61	24.93
	6H	16.36	16.76	17.39	17.82	19.14	22.74	23.14	23.76	24.19	25.52
	8H	16.38	16.73	17.42	17.77	19.12	22.96	23.31	23.99	24.35	25.69
	12H	16.35	16.66	17.39	17.70	19.09	23.10	23.41	24.14	24.45	25.83
12H	4H	16.26	16.70	17.28	17.73	19.06	22.07	22.50	23.09	23.53	24.86
	6H	16.62	16.97	17.65	18.01	19.36	22.72	23.08	23.76	24.12	25.46
	8H	16.69	17.00	17.73	18.04	19.43	22.95	23.26	23.99	24.30	25.69