

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938115

Luminaire Tested: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938115
REPORT IS A COMBINATION OF REPORTS P933608 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13613.0 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 112.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938115
CATALOG NUMBER: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P938115

CATALOG NUMBER: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	44	42	37	37	37	37
2	87	79	73	68	79	73	67	63	61	56	53	49	46	44	39	37	35	30	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	27	23	21	18	18	18	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	23	24	21	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	18	16	13	13	13	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12	12	12	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10	10	10	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4883	4883	4883
5°	4769	5643	6564
10°	4324	8224	10883
15°	3674	10742	13141
20°	2990	12444	13392
25°	2493	13020	13120
30°	2101	13098	13095
35°	1857	12877	13434
40°	1618	12591	13783
45°	1464	12380	13837
50°	1341	12190	13608
55°	1283	11913	13005
60°	1312	11385	12053
65°	1364	10584	10744
70°	1449	9224	9077
75°	1600	7514	7083
80°	1735	5205	4773
85°	1514	2756	2443

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13837 cd/sqm



TEST NUMBER: P938115

CATALOG NUMBER: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	0.8
10°-20°	452.6	3.3
20°-30°	791.6	5.8
30°-40°	1019.1	7.5
40°-50°	1138.3	8.4
50°-60°	1090.2	8.0
60°-70°	864.0	6.3
70°-80°	508.0	3.7
80°-90°	145.6	1.1
90°-100°	564.1	4.1
100°-110°	1483.0	10.9
110°-120°	1537.7	11.3
120°-130°	1233.4	9.1
130°-140°	967.8	7.1
140°-150°	742.8	5.5
150°-160°	534.9	3.9
160°-170°	327.3	2.4
170°-180°	110.6	0.8
0°-30°	1346.3	9.9
0°-40°	2365.4	17.4
0°-60°	4593.8	33.7
0°-90°	6111.4	44.9
90°-120°	3584.7	26.3
90°-150°	6528.7	48.0
90°-180°	7502.0	55.1
0°-180°	13613.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	789	789	789	789	789	
5°	769	825	929	1051	1089	71
15°	576	1064	1792	2173	2241	160
25°	368	1206	2135	2229	2231	170
35°	249	1152	2010	2125	2208	155
45°	170	919	1777	2036	2127	132
55°	122	584	1508	1752	1800	111
65°	96	310	1119	1259	1277	96
75°	71	190	614	675	678	74
85°	25	58	152	168	170	27
90°	8	22	59	30	30	8
95°	75	292	972	501	341	83
105°	267	405	1640	2489	2322	283
115°	474	576	1313	2620	2990	469
125°	660	740	1194	2018	2381	586
135°	787	866	1157	1629	1848	609
145°	912	971	1142	1390	1499	572
155°	1031	1060	1142	1254	1291	474
165°	1113	1128	1142	1188	1202	314
175°	1157	1157	1150	1165	1165	110
180°	1157	1157	1157	1157	1157	



TEST NUMBER: P938115
 CATALOG NUMBER: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	789.4	789.4	789.4	789.4	789.4	789.4	789.4	789.4	789.4	789.4	789.4
2.5°	789.4	789.4	794.5	797.0	802.1	804.7	809.7	814.8	830.0	832.6	837.7
5°	769.1	779.3	812.3	825.0	860.5	908.7	929.0	962.0	1030.6	1050.9	1063.6
7.5°	738.7	761.5	842.7	863.0	951.9	1078.8	1132.1	1203.2	1312.3	1365.6	1408.8
10°	690.4	738.7	883.3	931.6	1076.3	1269.2	1368.2	1467.2	1632.2	1705.8	1733.7
12.5°	637.1	715.8	926.5	992.5	1200.6	1482.4	1601.7	1710.8	1898.7	1997.7	2012.9
15°	576.2	682.8	967.1	1063.6	1332.6	1660.1	1792.1	1926.6	2101.8	2172.8	2190.6
17.5°	522.9	657.4	1005.2	1106.7	1434.2	1820.0	1954.5	2066.2	2208.4	2256.6	2269.3
20°	456.9	616.8	1030.6	1162.6	1540.8	1936.8	2066.2	2152.5	2249.0	2279.4	2284.5
22.5°	408.7	573.7	1045.8	1182.9	1611.9	2007.8	2117.0	2185.5	2251.5	2261.7	2264.2
25°	368.1	525.4	1043.3	1205.7	1672.8	2051.0	2134.8	2185.5	2223.6	2228.7	2228.7
27.5°	330.0	472.1	1033.1	1210.8	1718.5	2061.1	2127.1	2162.7	2180.4	2190.6	2190.6
30°	297.0	421.4	1007.7	1200.6	1738.8	2051.0	2104.3	2122.1	2139.8	2155.1	2162.7
32.5°	271.6	373.1	969.6	1180.3	1741.3	2025.6	2063.7	2073.8	2099.2	2134.8	2147.4
35°	248.8	324.9	926.5	1152.4	1726.1	1985.0	2010.4	2020.5	2071.3	2124.6	2142.4
37.5°	225.9	289.4	870.7	1104.2	1703.2	1936.8	1954.5	1972.3	2051.0	2114.4	2134.8
40°	203.1	258.9	804.7	1050.9	1667.7	1878.4	1893.6	1921.5	2025.6	2099.2	2119.5
42.5°	185.3	233.5	733.6	995.0	1622.0	1812.4	1835.2	1875.8	1995.1	2073.8	2096.7
45°	170.1	208.1	657.4	918.9	1563.6	1743.8	1776.8	1832.7	1959.6	2035.8	2056.1
47.5°	154.8	190.4	578.7	840.2	1500.2	1675.3	1718.5	1781.9	1911.4	1985.0	2002.8
50°	142.1	172.6	500.1	756.4	1431.6	1601.7	1652.5	1718.5	1850.5	1919.0	1941.8
52.5°	132.0	157.4	426.4	672.7	1352.9	1525.5	1583.9	1652.5	1776.8	1842.8	1858.1
55°	121.8	144.7	363.0	583.8	1271.7	1444.3	1507.8	1573.8	1695.6	1751.5	1761.6
57.5°	116.8	134.5	309.7	500.1	1185.4	1352.9	1424.0	1484.9	1599.2	1642.3	1652.5
60°	109.1	126.9	269.1	429.0	1091.5	1266.6	1327.6	1388.5	1484.9	1520.5	1528.1
62.5°	101.5	121.8	238.6	360.4	995.0	1165.1	1226.0	1281.9	1363.1	1388.5	1398.6
65°	96.5	116.8	215.8	309.7	896.0	1058.5	1119.4	1167.6	1233.6	1259.0	1264.1
67.5°	91.4	111.7	198.0	266.5	797.0	951.9	997.6	1043.3	1094.0	1119.4	1122.0
70°	83.8	106.6	182.8	236.1	695.5	830.0	868.1	916.3	957.0	969.6	977.3
72.5°	78.7	99.0	172.6	213.2	591.4	713.3	748.8	776.7	812.3	825.0	825.0
75°	71.1	88.8	162.5	190.4	484.8	583.8	614.3	642.2	670.1	675.2	667.6
77.5°	63.5	78.7	139.6	159.9	378.2	462.0	487.4	502.6	525.4	530.5	533.1
80°	53.3	68.5	109.1	124.4	274.1	340.1	357.9	370.6	390.9	390.9	396.0
82.5°	40.6	53.3	78.7	88.8	185.3	233.5	248.8	256.4	269.1	269.1	269.1
85°	25.4	33.0	50.8	58.4	111.7	142.1	152.3	154.8	165.0	167.5	167.5
87.5°	12.7	17.8	33.0	35.5	58.4	73.6	73.6	78.7	78.7	76.2	73.6
90°	7.8	14.0	20.2	21.7	34.1	50.7	59.0	52.4	39.3	29.5	29.5
92.5°	31.1	83.9	136.7	149.9	210.7	291.8	332.4	291.3	209.2	147.6	141.7
95°	74.6	171.2	267.8	292.0	518.5	820.6	971.6	867.0	657.8	500.9	483.1
97.5°	128.9	214.1	299.4	320.7	698.4	1202.1	1453.9	1387.8	1255.6	1156.4	1122.6
100°	170.9	248.2	325.5	344.8	763.9	1322.8	1602.2	1607.0	1616.7	1623.9	1583.6
102.5°	206.6	278.7	350.9	368.9	794.0	1360.7	1644.1	1728.3	1896.8	2023.1	1988.6
105°	267.2	328.3	389.3	404.6	816.2	1365.1	1639.5	1828.3	2205.9	2489.1	2470.5
107.5°	329.3	386.2	443.2	457.4	820.4	1304.3	1546.3	1809.7	2336.4	2731.4	2735.9
110°	371.2	422.6	474.0	486.9	814.1	1250.4	1468.6	1763.0	2351.9	2793.6	2812.9



TEST NUMBER: P938115

CATALOG NUMBER: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	412.4	461.4	510.4	522.7	814.4	1203.4	1397.9	1699.2	2301.9	2753.9	2783.6
115°	474.5	519.7	565.0	576.3	822.0	1149.5	1313.3	1603.6	2184.2	2619.6	2660.8
117.5°	535.9	577.0	618.0	628.3	837.2	1115.7	1255.0	1517.0	2041.0	2434.0	2479.6
120°	571.6	610.3	648.9	658.6	849.6	1104.3	1231.7	1471.1	1949.8	2308.9	2353.3
122.5°	606.6	645.6	684.6	694.3	867.5	1098.4	1213.9	1429.5	1860.6	2183.9	2227.6
125°	660.1	695.7	731.2	740.1	891.6	1093.5	1194.5	1377.6	1743.8	2018.5	2058.8
127.5°	703.6	739.5	775.4	784.4	915.7	1090.7	1178.2	1335.4	1649.9	1885.7	1919.7
130°	726.9	765.6	804.2	813.9	933.2	1092.3	1171.9	1311.9	1591.8	1801.8	1833.2
132.5°	751.0	789.7	828.3	838.0	947.5	1093.5	1166.5	1291.8	1542.4	1730.3	1758.4
135°	786.7	821.9	857.1	865.9	963.0	1092.5	1157.2	1262.1	1472.0	1629.4	1653.6
137.5°	823.2	858.1	893.0	901.7	986.3	1099.2	1155.6	1244.3	1421.7	1554.8	1574.6
140°	853.5	885.6	917.7	925.7	1000.5	1100.3	1150.2	1226.8	1380.1	1495.0	1513.6
142.5°	876.8	906.5	936.2	943.6	1012.5	1104.3	1150.2	1217.5	1352.1	1453.1	1469.1
145°	912.5	938.4	964.3	970.8	1028.0	1104.3	1142.4	1197.5	1307.6	1390.2	1402.3
147.5°	948.3	973.5	998.7	1005.0	1050.8	1111.9	1142.4	1185.7	1272.4	1337.4	1347.4
150°	971.6	994.4	1017.1	1022.8	1062.7	1115.8	1142.4	1179.0	1252.2	1307.1	1315.2
152.5°	995.6	1012.9	1030.2	1034.5	1070.5	1118.4	1142.4	1173.6	1236.1	1283.0	1289.1
155°	1031.4	1044.2	1056.9	1060.1	1087.5	1124.1	1142.4	1167.3	1217.0	1254.3	1258.4
157.5°	1057.8	1070.2	1082.6	1085.7	1104.6	1129.8	1142.4	1161.7	1200.4	1229.4	1232.2
160°	1075.6	1085.3	1095.0	1097.4	1112.4	1132.4	1142.4	1159.0	1192.1	1217.0	1218.6
162.5°	1093.5	1100.7	1108.0	1109.8	1120.7	1135.2	1142.4	1156.4	1184.3	1205.3	1206.9
165°	1112.9	1119.5	1126.1	1127.7	1132.6	1139.1	1142.4	1152.4	1172.5	1187.5	1189.1
167.5°	1130.8	1133.9	1137.0	1137.8	1141.9	1147.4	1150.2	1156.8	1169.9	1179.7	1180.4
170°	1142.4	1145.5	1148.6	1149.4	1149.7	1150.0	1150.2	1156.8	1169.9	1179.7	1179.7
172.5°	1148.6	1149.3	1150.0	1150.2	1150.2	1150.2	1150.2	1155.4	1165.7	1173.5	1172.9
175°	1157.2	1157.2	1157.2	1157.2	1154.9	1151.8	1150.2	1153.5	1160.1	1165.0	1165.0
177.5°	1157.2	1157.2	1157.2	1157.2	1155.4	1152.9	1151.7	1154.3	1159.5	1163.4	1162.7
180°	1157.2	1157.2	1157.2	1157.2	1157.2	1157.2	1157.2	1157.2	1157.2	1157.2	1157.2



TEST NUMBER: P938115

CATALOG NUMBER: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	789.4	789.4
2.5°	842.7	837.7
5°	1083.9	1089.0
7.5°	1459.6	1457.0
10°	1814.9	1837.8
12.5°	2073.8	2078.9
15°	2231.2	2241.4
17.5°	2292.1	2294.7
20°	2294.7	2289.6
22.5°	2266.7	2261.7
25°	2233.7	2231.2
27.5°	2203.3	2205.8
30°	2190.6	2198.2
32.5°	2190.6	2203.3
35°	2195.7	2208.4
37.5°	2193.1	2208.4
40°	2183.0	2200.7
42.5°	2155.1	2167.8
45°	2111.9	2127.1
47.5°	2056.1	2066.2
50°	1985.0	1995.1
52.5°	1896.1	1898.7
55°	1789.5	1799.7
57.5°	1675.3	1677.8
60°	1548.4	1556.0
62.5°	1413.9	1413.9
65°	1271.7	1276.8
67.5°	1124.5	1137.2
70°	974.7	977.3
72.5°	827.5	827.5
75°	675.2	677.7
77.5°	530.5	530.5
80°	393.4	396.0
82.5°	271.6	276.7
85°	170.1	170.1
87.5°	78.7	71.1
90°	29.5	29.5
92.5°	118.2	94.7
95°	412.0	340.9
97.5°	987.3	852.0
100°	1422.5	1261.3
102.5°	1850.5	1712.5
105°	2396.3	2322.1
107.5°	2753.8	2771.8
110°	2890.2	2967.5



TEST NUMBER: P938115
CATALOG NUMBER: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2902.3	3021.1
115°	2825.4	2990.0
117.5°	2662.2	2844.8
120°	2530.7	2708.1
122.5°	2402.6	2577.6
125°	2220.0	2381.2
127.5°	2055.7	2191.7
130°	1958.9	2084.5
132.5°	1871.0	1983.5
135°	1750.6	1847.6
137.5°	1654.0	1733.4
140°	1587.8	1662.0
142.5°	1532.9	1596.8
145°	1450.6	1498.9
147.5°	1387.5	1427.5
150°	1347.7	1380.1
152.5°	1313.6	1338.1
155°	1274.6	1290.8
157.5°	1243.6	1255.0
160°	1225.2	1231.7
162.5°	1213.1	1219.3
165°	1195.7	1202.2
167.5°	1183.1	1185.9
170°	1179.7	1179.7
172.5°	1170.5	1168.1
175°	1165.0	1165.0
177.5°	1160.0	1157.2
180°	1157.2	1157.2



TEST NUMBER: P938115
 CATALOG NUMBER: SQ4-FB-125U-125D-835-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.03	6.88	7.02	7.89	9.22	19.19	20.04	20.18	21.05	22.39
	3H	6.73	7.49	7.73	8.51	9.87	21.02	21.79	22.03	22.81	24.17
	4H	7.03	7.75	8.04	8.77	10.14	21.67	22.39	22.68	23.41	24.78
	6H	7.28	7.95	8.30	8.97	10.35	22.09	22.76	23.12	23.78	25.17
	8H	7.35	7.98	8.38	9.03	10.40	22.21	22.85	23.24	23.89	25.26
	12H	7.36	7.97	8.40	9.01	10.41	22.27	22.88	23.31	23.92	25.32
4H	2H	13.23	13.96	14.25	14.98	16.34	19.46	20.19	20.49	21.21	22.58
	3H	14.80	15.41	15.83	16.45	17.84	21.50	22.11	22.53	23.16	24.54
	4H	14.89	15.45	15.93	16.49	17.89	22.27	22.82	23.31	23.86	25.27
	6H	14.90	15.38	15.95	16.45	17.85	22.80	23.28	23.85	24.35	25.74
	8H	14.88	15.33	15.93	16.39	17.80	22.96	23.41	24.01	24.47	25.88
	12H	14.84	15.24	15.90	16.31	17.73	23.05	23.46	24.12	24.53	25.95
8H	4H	16.33	16.78	17.38	17.84	19.25	22.33	22.77	23.38	23.83	25.25
	6H	16.57	16.95	17.65	18.05	19.46	22.95	23.32	24.02	24.42	25.83
	8H	16.59	16.92	17.67	18.00	19.43	23.17	23.49	24.25	24.58	26.01
	12H	16.56	16.85	17.65	17.93	19.40	23.31	23.60	24.39	24.67	26.15
12H	4H	16.48	16.88	17.54	17.95	19.37	22.28	22.68	23.35	23.76	25.18
	6H	16.83	17.16	17.91	18.24	19.67	22.93	23.26	24.01	24.34	25.77
	8H	16.90	17.19	17.99	18.27	19.74	23.16	23.45	24.25	24.53	26.00