

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562583

Luminaire Tested: **SQ4-PC3-025U-125D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562583
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8827.4 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 77.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562583
CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562583

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	84				
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71				
2	96	88	82	76	92	85	79	74	79	74	70	73	69	66	68	65	62	59				
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50				
4	80	69	60	54	77	66	59	53	62	55	50	58	52	48	54	49	46	43				
5	74	61	53	46	71	59	51	45	55	49	43	52	46	42	48	44	40	37				
6	68	55	47	40	65	53	45	40	50	43	38	47	41	36	44	39	35	33				
7	63	50	42	36	60	48	41	35	45	39	34	43	37	32	40	35	31	29				
8	59	46	37	32	56	44	37	31	42	35	30	39	33	29	37	32	28	26				
9	55	42	34	28	53	41	33	28	38	32	27	36	30	26	34	29	25	23				
10	51	38	31	26	49	37	30	25	35	29	24	33	28	24	31	26	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16626	16626	16626
5°	16751	16643	16582
10°	16711	16633	16585
15°	16623	16623	16607
20°	16514	16563	16563
25°	16358	16477	16426
30°	16159	16354	16283
35°	15918	16163	16049
40°	15655	15876	15715
45°	15370	15479	15240
50°	14969	14969	14729
55°	14493	14305	14091
60°	13794	13517	13300
65°	12749	12495	12385
70°	11163	11252	11207
75°	8981	9934	9993
80°	6383	8423	8512
85°	3889	7064	7064



TEST NUMBER: P562583

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.8	2.9
10°-20°	734.1	8.3
20°-30°	1111.7	12.6
30°-40°	1332.8	15.1
40°-50°	1359.0	15.4
50°-60°	1186.3	13.4
60°-70°	849.3	9.6
70°-80°	437.5	5.0
80°-90°	111.8	1.3
90°-100°	108.9	1.2
100°-110°	286.4	3.2
110°-120°	297.0	3.4
120°-130°	238.2	2.7
130°-140°	186.9	2.1
140°-150°	143.5	1.6
150°-160°	103.3	1.2
160°-170°	63.2	0.7
170°-180°	21.4	0.2
0°-30°	2101.7	23.8
0°-40°	3434.5	38.9
0°-60°	5979.9	67.7
0°-90°	7378.5	83.6
90°-120°	692.3	7.8
90°-150°	1261.0	14.3
90°-180°	1449.0	16.4
0°-180°	8827.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2703	2703	2703	2703	2703	
5°	2713	2686	2696	2688	2686	258
15°	2610	2588	2610	2610	2608	736
25°	2410	2393	2428	2420	2420	1109
35°	2120	2115	2152	2137	2137	1326
45°	1767	1762	1780	1757	1752	1360
55°	1352	1334	1334	1314	1314	1205
65°	876	856	858	851	851	866
75°	378	395	418	420	420	408
85°	55	84	100	103	100	75
90°	1	4	12	6	6	3
95°	14	56	188	97	66	16
105°	52	78	317	481	448	55
115°	92	111	254	506	578	91
125°	128	143	231	390	460	113
135°	152	167	224	315	357	118
145°	176	188	221	268	290	110
155°	199	205	221	242	249	92
165°	215	218	221	229	232	61
175°	224	224	222	225	225	21
180°	224	224	224	224	224	



TEST NUMBER: P562583

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2703.1	2703.1	2703.1	2703.1	2703.1
2.5°	2719.1	2695.6	2703.1	2696.9	2687.1
5°	2713.1	2686.2	2695.6	2688.0	2685.6
7.5°	2693.6	2666.7	2679.1	2674.0	2671.6
10°	2675.6	2648.6	2663.1	2658.0	2655.5
12.5°	2651.5	2626.6	2643.0	2638.0	2637.5
15°	2610.5	2588.5	2610.5	2610.4	2608.0
17.5°	2558.9	2538.9	2562.4	2563.9	2562.4
20°	2522.9	2500.9	2530.4	2528.0	2530.4
22.5°	2478.8	2460.7	2492.4	2485.9	2488.4
25°	2410.3	2393.1	2427.8	2420.3	2420.3
27.5°	2329.2	2316.9	2354.7	2346.7	2346.7
30°	2275.1	2262.9	2302.6	2292.6	2292.6
32.5°	2215.0	2206.7	2244.6	2232.6	2232.6
35°	2119.9	2115.0	2152.5	2137.4	2137.4
37.5°	2021.8	2017.4	2051.4	2033.2	2027.3
40°	1949.7	1947.3	1977.3	1957.2	1957.2
42.5°	1877.7	1875.2	1901.2	1877.2	1877.2
45°	1767.0	1762.1	1779.5	1756.9	1752.0
47.5°	1646.4	1641.5	1652.4	1627.8	1625.4
50°	1564.3	1559.4	1564.3	1541.7	1539.3
52.5°	1480.2	1471.4	1472.2	1449.6	1449.2
55°	1351.5	1334.4	1334.0	1314.0	1314.0
57.5°	1215.4	1192.9	1194.9	1177.8	1175.3
60°	1121.3	1096.8	1098.8	1083.7	1081.2
62.5°	1029.2	1000.8	1006.7	989.6	989.1
65°	876.0	856.4	858.5	851.0	851.0
67.5°	728.8	710.7	723.8	717.8	717.3
70°	620.7	608.5	625.7	625.7	623.2
72.5°	520.6	520.1	541.6	541.7	543.1
75°	377.9	395.1	418.0	420.5	420.5
77.5°	252.3	282.6	307.9	308.8	308.4
80°	180.2	214.5	237.8	242.7	240.3
82.5°	122.1	158.4	177.7	182.7	180.2
85°	55.1	84.4	100.1	102.6	100.1
87.5°	16.3	34.5	42.3	41.1	37.2
90°	1.4	4.2	11.5	5.7	5.7
92.5°	6.0	29.0	64.2	28.4	18.3
95°	14.3	56.4	187.7	96.7	65.9
97.5°	24.9	61.9	280.9	223.3	164.5
100°	33.0	66.6	309.5	313.7	243.6
102.5°	39.8	71.2	317.5	390.7	330.7
105°	51.6	78.2	316.7	480.7	448.5
107.5°	63.6	88.3	298.6	527.5	535.3
110°	71.6	94.1	283.7	539.5	573.2



TEST NUMBER: P562583

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	79.7	101.0	270.0	531.9	583.5
115°	91.7	111.3	253.6	506.0	577.5
117.5°	103.5	121.4	242.5	470.1	549.4
120°	110.3	127.1	237.9	446.0	523.0
122.5°	117.2	134.0	234.4	421.9	497.8
125°	127.5	142.9	230.7	389.9	460.0
127.5°	135.8	151.5	227.5	364.2	423.3
130°	140.4	157.2	226.4	348.0	402.7
132.5°	145.0	161.8	225.3	334.1	383.2
135°	151.9	167.3	223.5	314.8	356.8
137.5°	159.1	174.2	223.3	300.3	334.7
140°	164.8	178.8	222.1	288.8	321.0
142.5°	169.4	182.3	222.1	280.6	308.4
145°	176.3	187.5	220.7	268.4	289.5
147.5°	183.1	194.1	220.7	258.3	275.7
150°	187.7	197.5	220.7	252.5	266.5
152.5°	192.3	199.9	220.7	247.9	258.5
155°	199.2	204.8	220.7	242.3	249.3
157.5°	204.3	209.7	220.7	237.4	242.5
160°	207.8	212.0	220.7	235.1	237.9
162.5°	211.2	214.3	220.7	232.8	235.6
165°	214.9	217.7	220.7	229.3	232.1
167.5°	218.4	219.8	222.1	227.9	229.0
170°	220.7	222.1	222.1	227.8	227.8
172.5°	221.8	222.1	222.1	226.7	225.5
175°	223.5	223.5	222.1	225.0	225.0
177.5°	223.5	223.5	222.4	224.7	223.5
180°	223.5	223.5	223.5	223.5	223.5

(END OF REPORT)