

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519695

Luminaire Tested: **SQ4-075U-0D-835-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519695
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8981.3 lumens
Efficiency: N/A
Efficacy: 166.3 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 54
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519695
CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519695

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	3416	40576	11076
100°	3585	34443	28365
105°	3799	23423	33286
110°	3982	15957	31968
115°	4120	11505	25999
120°	4204	9111	20063
125°	4184	7691	15240
130°	4126	6737	11957
135°	4095	6060	9658
140°	4087	5558	8008
145°	4086	5154	6762
150°	4125	4854	5864
155°	4181	4629	5245
160°	4214	4464	4838
165°	4240	4361	4567
170°	4250	4287	4397
175°	4256	4238	4283



TEST NUMBER: P519695

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	650.2	7.2
100°-110°	1789.0	19.9
110°-120°	1846.5	20.6
120°-130°	1479.4	16.5
130°-140°	1162.0	12.9
140°-150°	890.5	9.9
150°-160°	640.2	7.1
160°-170°	391.5	4.4
170°-180°	132.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4285.7	47.7
90°-150°	7817.7	87.0
90°-180°	8981.0	100.0
0°-180°	8981.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	12	20	26	26	
95°	97	355	1150	492	314	108
105°	320	492	1971	3002	2801	337
115°	566	690	1581	3148	3573	559
125°	780	889	1434	2426	2842	696
135°	942	1045	1393	1962	2220	727
145°	1088	1163	1373	1672	1801	682
155°	1232	1272	1364	1503	1546	566
165°	1332	1349	1370	1426	1434	375
175°	1379	1382	1373	1390	1387	131
180°	1379	1379	1379	1379	1379	



TEST NUMBER: P519695

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.9	11.5	20.5	26.4	26.4
92.5°	40.5	173.0	299.8	115.1	94.5
95°	96.8	354.9	1149.9	491.7	313.9
97.5°	157.8	393.6	1754.7	1352.0	953.9
100°	202.4	417.5	1944.8	1963.0	1601.6
102.5°	244.6	446.0	1994.1	2435.3	2103.8
105°	319.7	491.8	1971.2	3002.1	2801.3
107.5°	391.3	548.5	1859.1	3279.6	3339.3
110°	442.9	586.3	1774.6	3348.7	3555.2
112.5°	489.9	628.7	1690.2	3304.2	3618.5
115°	566.1	689.5	1581.0	3148.3	3572.8
117.5°	638.9	752.4	1511.8	2929.5	3409.7
120°	683.5	792.4	1481.3	2765.6	3261.8
122.5°	723.4	832.3	1460.2	2621.9	3092.9
125°	780.3	889.2	1434.4	2426.5	2842.4
127.5°	834.2	938.1	1417.4	2263.4	2628.2
130°	862.4	968.5	1408.0	2166.5	2499.2
132.5°	895.2	1001.4	1400.9	2081.3	2381.8
135°	941.6	1044.8	1393.3	1962.4	2220.5
137.5°	985.0	1080.8	1386.9	1866.3	2079.1
140°	1017.9	1106.8	1384.5	1802.5	1994.6
142.5°	1046.0	1128.0	1379.8	1745.5	1910.2
145°	1088.3	1162.8	1372.8	1672.0	1801.0
147.5°	1133.4	1197.7	1369.3	1606.9	1710.1
150°	1161.6	1218.9	1366.9	1571.1	1651.4
152.5°	1187.4	1240.2	1364.6	1540.3	1606.9
155°	1232.0	1272.1	1364.0	1502.8	1545.8
157.5°	1264.3	1296.9	1364.0	1472.0	1501.8
160°	1287.7	1313.5	1364.0	1455.4	1478.4
162.5°	1306.5	1327.7	1366.3	1441.3	1459.6
165°	1331.7	1348.9	1369.8	1425.8	1434.4
167.5°	1349.3	1362.5	1372.8	1412.7	1415.0
170°	1361.0	1369.7	1372.8	1408.0	1408.0
172.5°	1370.4	1374.5	1372.8	1400.9	1398.6
175°	1378.6	1381.5	1372.8	1390.3	1387.4
177.5°	1381.0	1381.0	1371.6	1385.6	1381.0
180°	1378.6	1378.6	1378.6	1378.6	1378.6

(END OF REPORT)