

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562727

Luminaire Tested: **SQ4-PC3-075U-075D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562727
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-075D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8843.3 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562727
CATALOG NUMBER: SQ4-PC3-075U-075D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562727

CATALOG NUMBER: SQ4-PC3-075U-075D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	58	47	40	34	40	34	30	34	29	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9806	9806	9806
5°	9879	9816	9779
10°	9855	9809	9781
15°	9804	9804	9794
20°	9739	9768	9768
25°	9647	9717	9687
30°	9530	9645	9603
35°	9388	9532	9466
40°	9233	9363	9268
45°	9065	9129	8988
50°	8828	8828	8687
55°	8548	8437	8310
60°	8135	7971	7845
65°	7519	7369	7305
70°	6584	6636	6609
75°	5297	5858	5894
80°	3765	4966	5019
85°	2294	4164	4164



TEST NUMBER: P562727

CATALOG NUMBER: SQ4-PC3-075U-075D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.9	1.7
10°-20°	433.0	4.9
20°-30°	655.7	7.4
30°-40°	786.1	8.9
40°-50°	801.5	9.1
50°-60°	699.7	7.9
60°-70°	500.9	5.7
70°-80°	258.0	2.9
80°-90°	67.0	0.8
90°-100°	325.1	3.7
100°-110°	894.5	10.1
110°-120°	923.3	10.4
120°-130°	739.7	8.4
130°-140°	581.0	6.6
140°-150°	445.2	5.0
150°-160°	320.1	3.6
160°-170°	195.7	2.2
170°-180°	66.0	0.7
0°-30°	1239.5	14.0
0°-40°	2025.5	22.9
0°-60°	3526.7	39.9
0°-90°	4352.6	49.2
90°-120°	2142.9	24.2
90°-150°	3908.8	44.2
90°-180°	4491.0	50.8
0°-180°	8843.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1600	1584	1590	1585	1584	152
15°	1540	1527	1540	1540	1538	434
25°	1422	1411	1432	1427	1427	654
35°	1250	1247	1269	1261	1261	782
45°	1042	1039	1050	1036	1033	802
55°	797	787	787	775	775	711
65°	517	505	506	502	502	511
75°	223	233	246	248	248	241
85°	32	50	59	60	59	44
90°	2	6	10	13	13	5
95°	48	178	575	246	157	51
105°	160	246	986	1501	1401	169
115°	283	345	790	1574	1786	279
125°	390	445	717	1213	1421	348
135°	471	522	697	981	1110	363
145°	544	581	686	836	900	341
155°	616	636	682	751	773	283
165°	666	674	685	713	717	188
175°	689	691	686	695	694	65
180°	689	689	689	689	689	

TEST NUMBER: P562727

CATALOG NUMBER: SQ4-PC3-075U-075D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1594.2	1594.2	1594.2	1594.2	1594.2
2.5°	1603.6	1589.8	1594.2	1590.5	1584.7
5°	1600.1	1584.2	1589.8	1585.3	1583.8
7.5°	1588.6	1572.7	1580.0	1577.0	1575.6
10°	1577.9	1562.1	1570.6	1567.6	1566.1
12.5°	1563.8	1549.1	1558.8	1555.8	1555.5
15°	1539.6	1526.6	1539.6	1539.5	1538.1
17.5°	1509.2	1497.3	1511.2	1512.1	1511.2
20°	1487.9	1474.9	1492.3	1490.9	1492.3
22.5°	1461.9	1451.2	1469.9	1466.1	1467.5
25°	1421.5	1411.4	1431.8	1427.4	1427.4
27.5°	1373.7	1366.4	1388.7	1384.0	1384.0
30°	1341.8	1334.6	1358.0	1352.1	1352.1
32.5°	1306.3	1301.4	1323.8	1316.7	1316.7
35°	1250.3	1247.4	1269.4	1260.6	1260.6
37.5°	1192.4	1189.8	1209.8	1199.1	1195.6
40°	1149.9	1148.4	1166.1	1154.3	1154.3
42.5°	1107.4	1105.9	1121.2	1107.1	1107.1
45°	1042.1	1039.2	1049.5	1036.2	1033.3
47.5°	971.0	968.1	974.5	960.0	958.6
50°	922.6	919.7	922.6	909.2	907.8
52.5°	873.0	867.8	868.2	854.9	854.7
55°	797.1	787.0	786.8	774.9	774.9
57.5°	716.8	703.5	704.7	694.6	693.2
60°	661.3	646.9	648.0	639.1	637.7
62.5°	607.0	590.2	593.7	583.6	583.4
65°	516.6	505.1	506.3	501.9	501.9
67.5°	429.8	419.2	426.9	423.3	423.0
70°	366.1	358.9	369.0	369.0	367.5
72.5°	307.0	306.7	319.4	319.4	320.3
75°	222.9	233.0	246.5	248.0	248.0
77.5°	148.8	166.7	181.6	182.1	181.9
80°	106.3	126.5	140.2	143.1	141.7
82.5°	72.0	93.4	104.8	107.7	106.3
85°	32.5	49.8	59.0	60.5	59.0
87.5°	9.7	21.0	25.7	26.2	23.9
90°	1.5	5.8	10.3	13.2	13.2
92.5°	20.2	86.5	149.9	57.6	47.2
95°	48.4	177.5	574.9	245.8	156.9
97.5°	78.9	196.8	877.3	676.0	477.0
100°	101.2	208.8	972.4	981.5	800.8
102.5°	122.3	223.0	997.0	1217.7	1051.9
105°	159.9	245.9	985.6	1501.0	1400.6
107.5°	195.7	274.2	929.6	1639.8	1669.6
110°	221.5	293.2	887.3	1674.3	1777.6



TEST NUMBER: P562727

CATALOG NUMBER: SQ4-PC3-075U-075D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	244.9	314.3	845.1	1652.1	1809.3
115°	283.1	344.7	790.5	1574.1	1786.4
117.5°	319.4	376.2	755.9	1464.8	1704.8
120°	341.7	396.2	740.7	1382.8	1630.9
122.5°	361.7	416.2	730.1	1311.0	1546.4
125°	390.1	444.6	717.2	1213.2	1421.2
127.5°	417.1	469.0	708.7	1131.7	1314.1
130°	431.2	484.3	704.0	1083.2	1249.6
132.5°	447.6	500.7	700.5	1040.6	1190.9
135°	470.8	522.4	696.7	981.2	1110.3
137.5°	492.5	540.4	693.4	933.2	1039.6
140°	508.9	553.4	692.3	901.2	997.3
142.5°	523.0	564.0	689.9	872.8	955.1
145°	544.1	581.4	686.4	836.0	900.5
147.5°	566.7	598.8	684.6	803.4	855.1
150°	580.8	609.5	683.5	785.6	825.7
152.5°	593.7	620.1	682.3	770.2	803.4
155°	616.0	636.1	682.0	751.4	772.9
157.5°	632.1	648.5	682.0	736.0	750.9
160°	643.9	656.8	682.0	727.7	739.2
162.5°	653.2	663.9	683.2	720.6	729.8
165°	665.9	674.5	684.9	712.9	717.2
167.5°	674.7	681.3	686.4	706.4	707.5
170°	680.5	684.8	686.4	704.0	704.0
172.5°	685.2	687.2	686.4	700.4	699.3
175°	689.3	690.8	686.4	695.2	693.7
177.5°	690.5	690.5	685.8	692.8	690.5
180°	689.3	689.3	689.3	689.3	689.3

(END OF REPORT)