

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562751

Luminaire Tested: **SQ4-PC3-075U-100D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562751
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-100D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10273.4 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562751
CATALOG NUMBER: SQ4-PC3-075U-100D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562751

CATALOG NUMBER: SQ4-PC3-075U-100D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	54	52	48				
2	90	83	77	72	84	77	72	67	67	63	59	57	54	52	48	46	44	40				
3	82	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34				
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29				
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25				
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	28	25	22				
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13029	13029	13029
5°	13127	13042	12994
10°	13095	13034	12997
15°	13026	13026	13014
20°	12941	12979	12979
25°	12818	12912	12872
30°	12662	12815	12759
35°	12474	12665	12576
40°	12267	12441	12315
45°	12045	12130	11942
50°	11730	11730	11542
55°	11357	11210	11042
60°	10809	10592	10423
65°	9991	9791	9705
70°	8747	8817	8783
75°	7039	7783	7831
80°	5001	6599	6670
85°	3042	5540	5540



TEST NUMBER: P562751

CATALOG NUMBER: SQ4-PC3-075U-100D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.5	2.0
10°-20°	575.3	5.6
20°-30°	871.2	8.5
30°-40°	1044.4	10.2
40°-50°	1065.0	10.4
50°-60°	929.6	9.0
60°-70°	665.5	6.5
70°-80°	342.8	3.3
80°-90°	88.4	0.9
90°-100°	325.1	3.2
100°-110°	894.5	8.7
110°-120°	923.3	9.0
120°-130°	739.7	7.2
130°-140°	581.0	5.7
140°-150°	445.2	4.3
150°-160°	320.1	3.1
160°-170°	195.7	1.9
170°-180°	66.0	0.6
0°-30°	1646.9	16.0
0°-40°	2691.3	26.2
0°-60°	4685.9	45.6
0°-90°	5782.7	56.3
90°-120°	2142.9	20.9
90°-150°	3908.8	38.0
90°-180°	4491.0	43.7
0°-180°	10273.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2118	2118	2118	2118	2118	
5°	2126	2105	2112	2106	2104	202
15°	2046	2028	2046	2046	2044	577
25°	1889	1875	1902	1897	1897	869
35°	1661	1657	1687	1675	1675	1039
45°	1385	1381	1394	1377	1373	1066
55°	1059	1046	1045	1030	1030	944
65°	686	671	673	667	667	679
75°	296	310	328	330	330	320
85°	43	66	78	80	78	59
90°	2	6	10	13	13	5
95°	48	178	575	246	157	51
105°	160	246	986	1501	1401	169
115°	283	345	790	1574	1786	279
125°	390	445	717	1213	1421	348
135°	471	522	697	981	1110	363
145°	544	581	686	836	900	341
155°	616	636	682	751	773	283
165°	666	674	685	713	717	188
175°	689	691	686	695	694	65
180°	689	689	689	689	689	

TEST NUMBER: P562751

CATALOG NUMBER: SQ4-PC3-075U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2118.2	2118.2	2118.2	2118.2	2118.2
2.5°	2130.7	2112.3	2118.2	2113.3	2105.6
5°	2126.0	2104.9	2112.3	2106.4	2104.5
7.5°	2110.7	2089.6	2099.4	2095.4	2093.5
10°	2096.6	2075.5	2086.8	2082.8	2080.9
12.5°	2077.8	2058.2	2071.1	2067.2	2066.8
15°	2045.6	2028.4	2045.6	2045.6	2043.7
17.5°	2005.2	1989.5	2008.0	2009.1	2008.0
20°	1977.0	1959.7	1982.9	1980.9	1982.9
22.5°	1942.5	1928.3	1953.1	1948.0	1949.9
25°	1888.7	1875.3	1902.5	1896.6	1896.6
27.5°	1825.2	1815.6	1845.2	1838.9	1838.9
30°	1782.8	1773.2	1804.4	1796.5	1796.5
32.5°	1735.7	1729.2	1758.9	1749.5	1749.5
35°	1661.2	1657.4	1686.7	1674.9	1674.9
37.5°	1584.3	1580.9	1607.5	1593.2	1588.6
40°	1527.8	1525.9	1549.4	1533.7	1533.7
42.5°	1471.4	1469.4	1489.8	1471.0	1471.0
45°	1384.7	1380.8	1394.5	1376.7	1372.9
47.5°	1290.1	1286.3	1294.8	1275.6	1273.7
50°	1225.8	1222.0	1225.8	1208.1	1206.2
52.5°	1159.9	1153.0	1153.6	1136.0	1135.6
55°	1059.1	1045.7	1045.4	1029.7	1029.7
57.5°	952.4	934.8	936.3	922.9	921.0
60°	878.7	859.5	861.0	849.2	847.3
62.5°	806.5	784.2	788.8	775.5	775.1
65°	686.5	671.1	672.7	666.8	666.8
67.5°	571.1	556.9	567.2	562.5	562.1
70°	486.4	476.8	490.3	490.3	488.4
72.5°	407.9	407.6	424.4	424.4	425.6
75°	296.2	309.6	327.5	329.5	329.5
77.5°	197.7	221.5	241.2	242.0	241.6
80°	141.2	168.1	186.3	190.2	188.3
82.5°	95.7	124.1	139.3	143.1	141.2
85°	43.1	66.2	78.5	80.4	78.5
87.5°	12.8	27.5	33.4	34.0	30.9
90°	1.5	5.8	10.3	13.2	13.2
92.5°	20.2	86.5	149.9	57.6	47.2
95°	48.4	177.5	574.9	245.8	156.9
97.5°	78.9	196.8	877.3	676.0	477.0
100°	101.2	208.8	972.4	981.5	800.8
102.5°	122.3	223.0	997.0	1217.7	1051.9
105°	159.9	245.9	985.6	1501.0	1400.6
107.5°	195.7	274.2	929.6	1639.8	1669.6
110°	221.5	293.2	887.3	1674.3	1777.6

TEST NUMBER: P562751

CATALOG NUMBER: SQ4-PC3-075U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	244.9	314.3	845.1	1652.1	1809.3
115°	283.1	344.7	790.5	1574.1	1786.4
117.5°	319.4	376.2	755.9	1464.8	1704.8
120°	341.7	396.2	740.7	1382.8	1630.9
122.5°	361.7	416.2	730.1	1311.0	1546.4
125°	390.1	444.6	717.2	1213.2	1421.2
127.5°	417.1	469.0	708.7	1131.7	1314.1
130°	431.2	484.3	704.0	1083.2	1249.6
132.5°	447.6	500.7	700.5	1040.6	1190.9
135°	470.8	522.4	696.7	981.2	1110.3
137.5°	492.5	540.4	693.4	933.2	1039.6
140°	508.9	553.4	692.3	901.2	997.3
142.5°	523.0	564.0	689.9	872.8	955.1
145°	544.1	581.4	686.4	836.0	900.5
147.5°	566.7	598.8	684.6	803.4	855.1
150°	580.8	609.5	683.5	785.6	825.7
152.5°	593.7	620.1	682.3	770.2	803.4
155°	616.0	636.1	682.0	751.4	772.9
157.5°	632.1	648.5	682.0	736.0	750.9
160°	643.9	656.8	682.0	727.7	739.2
162.5°	653.2	663.9	683.2	720.6	729.8
165°	665.9	674.5	684.9	712.9	717.2
167.5°	674.7	681.3	686.4	706.4	707.5
170°	680.5	684.8	686.4	704.0	704.0
172.5°	685.2	687.2	686.4	700.4	699.3
175°	689.3	690.8	686.4	695.2	693.7
177.5°	690.5	690.5	685.8	692.8	690.5
180°	689.3	689.3	689.3	689.3	689.3

(END OF REPORT)