

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562895

Luminaire Tested: **SQ4-PC3-100U-050D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562895
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-050D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8978.4 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 64.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562895
CATALOG NUMBER: SQ4-PC3-100U-050D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562895

CATALOG NUMBER: SQ4-PC3-100U-050D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	39	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13
7	55	43	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6653	6653	6653
5°	6703	6660	6635
10°	6687	6655	6637
15°	6652	6652	6645
20°	6608	6627	6627
25°	6545	6593	6572
30°	6466	6544	6516
35°	6370	6467	6422
40°	6264	6353	6289
45°	6151	6194	6098
50°	5989	5989	5894
55°	5799	5724	5638
60°	5520	5409	5322
65°	5101	4999	4956
70°	4467	4503	4485
75°	3593	3976	4000
80°	2554	3369	3404
85°	1553	2830	2830



TEST NUMBER: P562895

CATALOG NUMBER: SQ4-PC3-100U-050D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.4	1.1
10°-20°	293.8	3.3
20°-30°	444.9	5.0
30°-40°	533.3	5.9
40°-50°	543.8	6.1
50°-60°	474.7	5.3
60°-70°	339.8	3.8
70°-80°	175.0	1.9
80°-90°	46.2	0.5
90°-100°	434.2	4.8
100°-110°	1198.7	13.4
110°-120°	1236.3	13.8
120°-130°	993.5	11.1
130°-140°	780.8	8.7
140°-150°	598.8	6.7
150°-160°	430.4	4.8
160°-170°	263.2	2.9
170°-180°	88.7	1.0
0°-30°	841.0	9.4
0°-40°	1374.3	15.3
0°-60°	2392.8	26.7
0°-90°	2953.9	32.9
90°-120°	2869.2	32.0
90°-150°	5242.2	58.4
90°-180°	6024.0	67.1
0°-180°	8978.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1082	1082	1082	1082	1082	
5°	1086	1075	1079	1076	1075	103
15°	1045	1036	1045	1044	1044	295
25°	964	958	972	968	968	444
35°	848	846	861	855	855	531
45°	707	705	712	703	701	544
55°	541	534	534	526	526	482
65°	350	343	344	340	340	347
75°	151	158	167	168	168	163
85°	22	34	40	41	40	30
90°	3	6	12	13	15	5
95°	64	235	788	324	211	68
105°	214	330	1319	2013	1896	227
115°	383	462	1062	2103	2391	376
125°	525	598	963	1629	1912	467
135°	632	700	936	1320	1488	489
145°	733	784	924	1124	1209	459
155°	826	854	917	1008	1040	381
165°	895	906	921	957	964	252
175°	927	929	923	936	933	88
180°	927	927	927	927	927	



TEST NUMBER: P562895

CATALOG NUMBER: SQ4-PC3-100U-050D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1081.6	1081.6	1081.6	1081.6	1081.6
2.5°	1088.0	1078.6	1081.6	1079.1	1075.2
5°	1085.6	1074.9	1078.6	1075.6	1074.6
7.5°	1077.8	1067.0	1072.0	1070.0	1069.0
10°	1070.6	1059.8	1065.6	1063.6	1062.6
12.5°	1061.0	1051.0	1057.6	1055.6	1055.4
15°	1044.6	1035.8	1044.6	1044.5	1043.6
17.5°	1023.9	1015.9	1025.3	1025.9	1025.3
20°	1009.5	1000.7	1012.5	1011.5	1012.5
22.5°	991.9	984.6	997.3	994.7	995.7
25°	964.4	957.6	971.5	968.4	968.4
27.5°	932.0	927.1	942.2	939.0	939.0
30°	910.4	905.5	921.4	917.4	917.4
32.5°	886.3	883.0	898.1	893.3	893.3
35°	848.3	846.3	861.3	855.3	855.3
37.5°	809.0	807.2	820.8	813.6	811.2
40°	780.2	779.2	791.2	783.2	783.2
42.5°	751.3	750.3	760.7	751.1	751.1
45°	707.1	705.1	712.1	703.0	701.0
47.5°	658.8	656.8	661.2	651.4	650.4
50°	625.9	624.0	625.9	616.9	615.9
52.5°	592.3	588.8	589.1	580.1	579.9
55°	540.8	534.0	533.8	525.8	525.8
57.5°	486.3	477.3	478.1	471.3	470.3
60°	448.7	438.9	439.7	433.6	432.6
62.5°	411.8	400.5	402.8	396.0	395.8
65°	350.5	342.7	343.5	340.5	340.5
67.5°	291.6	284.4	289.6	287.2	287.0
70°	248.4	243.5	250.4	250.4	249.4
72.5°	208.3	208.1	216.7	216.7	217.3
75°	151.2	158.1	167.3	168.3	168.3
77.5°	101.0	113.1	123.2	123.6	123.4
80°	72.1	85.8	95.1	97.1	96.1
82.5°	48.9	63.4	71.1	73.1	72.1
85°	22.0	33.8	40.1	41.0	40.1
87.5°	7.0	14.6	18.4	18.7	17.4
90°	3.0	5.9	11.9	13.4	14.8
92.5°	26.7	110.8	198.2	72.3	56.4
95°	63.8	235.0	787.8	323.8	210.7
97.5°	105.6	263.2	1166.9	898.4	650.7
100°	136.5	280.1	1307.0	1316.2	1069.6
102.5°	166.2	299.3	1334.3	1626.3	1392.4
105°	213.6	329.7	1318.9	2013.4	1895.9
107.5°	264.1	367.3	1245.3	2200.2	2243.1
110°	299.7	392.5	1188.3	2240.3	2379.6



TEST NUMBER: P562895

CATALOG NUMBER: SQ4-PC3-100U-050D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.7	421.1	1134.9	2208.6	2414.0
115°	382.7	462.5	1062.2	2102.8	2391.4
117.5°	427.3	506.7	1014.4	1953.8	2282.3
120°	456.9	535.3	995.4	1853.0	2183.7
122.5°	485.4	560.3	980.0	1758.9	2072.2
125°	525.2	597.7	962.8	1629.4	1912.3
127.5°	559.0	631.5	952.7	1519.9	1763.9
130°	581.5	654.1	948.0	1453.0	1674.9
132.5°	602.9	672.0	943.2	1396.7	1597.8
135°	632.0	700.2	936.1	1319.7	1488.0
137.5°	664.6	726.7	932.5	1255.1	1398.7
140°	682.4	743.3	930.2	1211.9	1338.1
142.5°	702.6	758.9	927.8	1173.6	1284.7
145°	732.9	783.6	924.2	1123.5	1209.1
147.5°	761.9	806.3	921.0	1081.2	1147.7
150°	783.3	819.6	919.8	1056.0	1109.7
152.5°	799.9	833.9	918.6	1034.4	1078.8
155°	826.3	853.9	916.8	1008.0	1040.0
157.5°	850.7	871.8	917.1	988.8	1010.6
160°	864.9	883.8	918.3	978.0	994.0
162.5°	876.8	893.3	919.5	968.4	980.9
165°	894.6	906.2	921.3	957.0	964.3
167.5°	908.2	915.2	922.8	950.1	952.4
170°	915.3	921.1	922.8	946.5	946.5
172.5°	921.3	924.7	922.8	941.7	940.6
175°	927.2	928.7	922.8	936.0	933.1
177.5°	929.6	928.4	922.5	930.7	928.4
180°	927.2	927.2	927.2	927.2	927.2

(END OF REPORT)