

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563087

Luminaire Tested: **SQ4-PC3-150U-050D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563087
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11990.8 lumens
Efficiency: N/A
Efficacy: 142.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563087
CATALOG NUMBER: SQ4-PC3-150U-050D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563087

CATALOG NUMBER: SQ4-PC3-150U-050D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6653	6653	6653
5°	6703	6660	6635
10°	6687	6655	6637
15°	6652	6652	6645
20°	6608	6627	6627
25°	6545	6593	6572
30°	6466	6544	6516
35°	6370	6467	6422
40°	6264	6353	6289
45°	6151	6194	6098
50°	5989	5989	5894
55°	5799	5724	5638
60°	5520	5409	5322
65°	5101	4999	4956
70°	4467	4503	4485
75°	3593	3976	4000
80°	2554	3369	3404
85°	1553	2830	2830



TEST NUMBER: P563087

CATALOG NUMBER: SQ4-PC3-150U-050D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.4	0.9
10°-20°	293.8	2.4
20°-30°	444.9	3.7
30°-40°	533.3	4.4
40°-50°	543.8	4.5
50°-60°	474.7	4.0
60°-70°	339.8	2.8
70°-80°	175.0	1.5
80°-90°	47.2	0.4
90°-100°	651.3	5.4
100°-110°	1761.1	14.7
110°-120°	1851.5	15.4
120°-130°	1503.9	12.5
130°-140°	1179.7	9.8
140°-150°	905.4	7.6
150°-160°	651.2	5.4
160°-170°	397.8	3.3
170°-180°	134.1	1.1
0°-30°	841.0	7.0
0°-40°	1374.3	11.5
0°-60°	2392.8	20.0
0°-90°	2954.9	24.6
90°-120°	4263.9	35.6
90°-150°	7852.9	65.5
90°-180°	9036.0	75.4
0°-180°	11990.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1082	1082	1082	1082	1082	
5°	1086	1075	1079	1076	1075	103
15°	1045	1036	1045	1044	1044	295
25°	964	958	972	968	968	444
35°	848	846	861	855	855	531
45°	707	705	712	703	701	544
55°	541	534	534	526	526	482
65°	350	343	344	340	340	347
75°	151	158	167	168	168	163
85°	22	34	40	41	40	30
90°	3	9	20	21	20	8
95°	101	355	1083	561	333	106
105°	327	506	1954	2882	2764	345
115°	576	705	1620	3136	3541	569
125°	789	904	1460	2464	2895	703
135°	946	1058	1421	1990	2252	731
145°	1100	1182	1402	1703	1833	688
155°	1242	1290	1389	1528	1578	573
165°	1352	1365	1396	1450	1457	381
175°	1403	1402	1397	1415	1412	133
180°	1402	1402	1402	1402	1402	

TEST NUMBER: P563087

CATALOG NUMBER: SQ4-PC3-150U-050D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1081.6	1081.6	1081.6	1081.6	1081.6
2.5°	1088.0	1078.6	1081.6	1079.1	1075.2
5°	1085.6	1074.9	1078.6	1075.6	1074.6
7.5°	1077.8	1067.0	1072.0	1070.0	1069.0
10°	1070.6	1059.8	1065.6	1063.6	1062.6
12.5°	1061.0	1051.0	1057.6	1055.6	1055.4
15°	1044.6	1035.8	1044.6	1044.5	1043.6
17.5°	1023.9	1015.9	1025.3	1025.9	1025.3
20°	1009.5	1000.7	1012.5	1011.5	1012.5
22.5°	991.9	984.6	997.3	994.7	995.7
25°	964.4	957.6	971.5	968.4	968.4
27.5°	932.0	927.1	942.2	939.0	939.0
30°	910.4	905.5	921.4	917.4	917.4
32.5°	886.3	883.0	898.1	893.3	893.3
35°	848.3	846.3	861.3	855.3	855.3
37.5°	809.0	807.2	820.8	813.6	811.2
40°	780.2	779.2	791.2	783.2	783.2
42.5°	751.3	750.3	760.7	751.1	751.1
45°	707.1	705.1	712.1	703.0	701.0
47.5°	658.8	656.8	661.2	651.4	650.4
50°	625.9	624.0	625.9	616.9	615.9
52.5°	592.3	588.8	589.1	580.1	579.9
55°	540.8	534.0	533.8	525.8	525.8
57.5°	486.3	477.3	478.1	471.3	470.3
60°	448.7	438.9	439.7	433.6	432.6
62.5°	411.8	400.5	402.8	396.0	395.8
65°	350.5	342.7	343.5	340.5	340.5
67.5°	291.6	284.4	289.6	287.2	287.0
70°	248.4	243.5	250.4	250.4	249.4
72.5°	208.3	208.1	216.7	216.7	217.3
75°	151.2	158.1	167.3	168.3	168.3
77.5°	101.0	113.1	123.2	123.6	123.4
80°	72.1	85.8	95.1	97.1	96.1
82.5°	48.9	63.4	71.1	73.1	72.1
85°	22.0	33.8	40.1	41.0	40.1
87.5°	7.0	15.2	19.9	20.2	18.3
90°	3.0	8.9	19.6	21.1	19.6
92.5°	42.8	156.1	308.1	133.7	96.9
95°	101.1	354.8	1083.2	560.6	333.4
97.5°	162.3	406.9	1688.4	1397.3	1026.2
100°	208.2	428.0	1876.7	1957.2	1582.5
102.5°	250.4	457.2	1943.1	2381.7	2101.5
105°	327.4	505.9	1953.6	2881.8	2763.8
107.5°	398.6	561.4	1868.3	3193.7	3232.9
110°	454.1	601.6	1792.2	3277.5	3444.1



TEST NUMBER: P563087

CATALOG NUMBER: SQ4-PC3-150U-050D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	503.6	641.6	1722.2	3260.7	3540.7
115°	576.3	704.6	1620.2	3136.5	3540.7
117.5°	647.5	767.9	1553.0	2946.8	3404.9
120°	690.9	808.9	1513.1	2810.6	3278.2
122.5°	732.0	847.6	1489.0	2664.6	3135.8
125°	789.0	904.1	1460.3	2464.3	2895.0
127.5°	841.5	954.5	1443.4	2300.8	2679.6
130°	870.5	987.0	1436.2	2199.8	2542.0
132.5°	900.6	1016.0	1428.9	2108.6	2423.7
135°	945.9	1058.0	1421.1	1989.8	2252.3
137.5°	991.5	1097.4	1414.5	1893.3	2107.2
140°	1022.8	1121.7	1412.1	1831.2	2021.5
142.5°	1053.0	1145.9	1407.2	1775.2	1941.9
145°	1099.8	1182.4	1401.5	1703.1	1833.0
147.5°	1142.3	1215.5	1394.9	1637.9	1737.6
150°	1173.7	1238.6	1392.4	1602.4	1682.1
152.5°	1202.7	1259.3	1391.2	1569.5	1635.0
155°	1241.6	1290.3	1389.4	1527.8	1578.0
157.5°	1282.0	1315.9	1389.7	1498.8	1531.8
160°	1304.9	1333.0	1390.9	1480.5	1504.1
162.5°	1323.0	1346.3	1392.1	1465.9	1483.6
165°	1351.7	1365.0	1395.5	1449.9	1457.3
167.5°	1371.3	1380.5	1395.8	1436.3	1439.8
170°	1383.4	1387.8	1397.0	1430.2	1430.2
172.5°	1393.0	1393.9	1397.0	1422.9	1421.7
175°	1403.0	1401.5	1397.0	1415.0	1412.1
177.5°	1406.3	1402.8	1396.7	1408.7	1405.1
180°	1401.5	1401.5	1401.5	1401.5	1401.5

(END OF REPORT)