

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563375

Luminaire Tested: **SQ4-PP3-075U-050D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563375  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-050D-835-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7416.5 lumens  
Efficiency: N/A  
Efficacy: 136.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 54.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563375  
CATALOG NUMBER: SQ4-PP3-075U-050D-835-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563375

CATALOG NUMBER: SQ4-PP3-075U-050D-835-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	37	32	30	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	42	60	51	44	39	42	37	33	34	30	27	26	24	22	18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7027	7027	7027
5°	7078	7035	7010
10°	7066	7016	6985
15°	7020	6982	6943
20°	6973	6934	6881
25°	6890	6843	6775
30°	6763	6727	6642
35°	6586	6541	6458
40°	6375	6335	6263
45°	6201	6158	6097
50°	5979	5940	5883
55°	5670	5594	5552
60°	5161	5013	4988
65°	4547	4357	4343
70°	3926	3764	3764
75°	3379	3332	3284
80°	2979	3014	2943
85°	2329	2541	2541



TEST NUMBER: P563375

CATALOG NUMBER: SQ4-PP3-075U-050D-835-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.0	1.5
10°-20°	308.5	4.2
20°-30°	462.0	6.2
30°-40°	541.9	7.3
40°-50°	543.6	7.3
50°-60°	463.8	6.3
60°-70°	302.5	4.1
70°-80°	151.7	2.0
80°-90°	43.8	0.6
90°-100°	325.1	4.4
100°-110°	894.5	12.1
110°-120°	923.3	12.4
120°-130°	739.7	10.0
130°-140°	581.0	7.8
140°-150°	445.2	6.0
150°-160°	320.1	4.3
160°-170°	195.7	2.6
170°-180°	66.0	0.9
0°-30°	878.5	11.8
0°-40°	1420.4	19.2
0°-60°	2427.8	32.7
0°-90°	2925.8	39.4
90°-120°	2142.9	28.9
90°-150°	3908.8	52.7
90°-180°	4491.0	60.6
0°-180°	7416.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1142	1142	1142	1142	1142	
5°	1146	1136	1139	1135	1135	109
15°	1102	1092	1096	1092	1090	311
25°	1015	1004	1008	999	998	467
35°	877	868	871	861	860	548
45°	713	708	708	701	701	549
55°	529	527	522	519	518	470
65°	312	306	299	297	298	312
75°	142	142	140	139	138	154
85°	33	36	36	36	36	39
90°	2	6	10	13	13	4
95°	48	178	575	246	157	51
105°	160	246	986	1501	1401	169
115°	283	345	790	1574	1786	279
125°	390	445	717	1213	1421	348
135°	471	522	697	981	1110	363
145°	544	581	686	836	900	341
155°	616	636	682	751	773	283
165°	666	674	685	713	717	188
175°	689	691	686	695	694	65
180°	689	689	689	689	689	

TEST NUMBER: P563375

CATALOG NUMBER: SQ4-PP3-075U-050D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1142.4	1142.4	1142.4	1142.4	1142.4
2.5°	1149.6	1140.3	1142.4	1140.7	1136.0
5°	1146.4	1135.7	1139.4	1135.4	1135.4
7.5°	1138.6	1126.9	1130.6	1126.6	1126.4
10°	1131.4	1119.7	1123.4	1119.4	1118.4
12.5°	1121.0	1109.3	1113.8	1109.0	1108.8
15°	1102.4	1091.6	1096.4	1092.3	1090.4
17.5°	1081.4	1069.6	1075.4	1069.7	1068.9
20°	1065.3	1053.6	1059.3	1051.3	1051.3
22.5°	1046.1	1034.4	1040.9	1030.5	1030.5
25°	1015.3	1003.5	1008.3	999.2	998.3
27.5°	978.6	967.1	972.0	961.8	961.6
30°	952.2	941.4	947.2	936.2	935.2
32.5°	923.4	913.4	917.6	906.5	905.5
35°	877.1	868.3	871.1	861.1	860.1
37.5°	828.4	819.4	822.6	814.0	813.6
40°	794.0	788.1	789.0	781.9	780.0
42.5°	762.0	755.3	756.2	749.1	748.7
45°	712.9	708.0	707.9	700.9	700.9
47.5°	660.8	657.1	656.0	650.2	650.0
50°	624.8	621.9	620.8	615.8	614.8
52.5°	587.1	585.8	582.3	578.1	577.9
55°	528.7	526.7	521.7	518.6	517.7
57.5°	465.2	461.3	455.6	451.2	452.0
60°	419.5	415.6	407.5	405.5	405.5
62.5°	375.5	370.8	362.7	359.9	361.5
65°	312.4	306.5	299.4	297.4	298.4
67.5°	255.1	249.8	242.1	242.1	241.3
70°	218.3	215.3	209.3	209.3	209.3
72.5°	185.4	184.1	179.6	179.6	178.8
75°	142.2	142.2	140.2	139.2	138.2
77.5°	106.5	106.9	105.9	104.9	103.1
80°	84.1	86.1	85.1	84.1	83.1
82.5°	63.3	65.2	65.1	63.3	63.1
85°	33.0	36.0	36.0	36.0	36.0
87.5°	9.1	13.1	14.9	15.5	16.3
90°	1.5	5.8	10.3	13.2	13.2
92.5°	20.2	86.5	149.9	57.6	47.2
95°	48.4	177.5	574.9	245.8	156.9
97.5°	78.9	196.8	877.3	676.0	477.0
100°	101.2	208.8	972.4	981.5	800.8
102.5°	122.3	223.0	997.0	1217.7	1051.9
105°	159.9	245.9	985.6	1501.0	1400.6
107.5°	195.7	274.2	929.6	1639.8	1669.6
110°	221.5	293.2	887.3	1674.3	1777.6



TEST NUMBER: P563375

CATALOG NUMBER: SQ4-PP3-075U-050D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	244.9	314.3	845.1	1652.1	1809.3
115°	283.1	344.7	790.5	1574.1	1786.4
117.5°	319.4	376.2	755.9	1464.8	1704.8
120°	341.7	396.2	740.7	1382.8	1630.9
122.5°	361.7	416.2	730.1	1311.0	1546.4
125°	390.1	444.6	717.2	1213.2	1421.2
127.5°	417.1	469.0	708.7	1131.7	1314.1
130°	431.2	484.3	704.0	1083.2	1249.6
132.5°	447.6	500.7	700.5	1040.6	1190.9
135°	470.8	522.4	696.7	981.2	1110.3
137.5°	492.5	540.4	693.4	933.2	1039.6
140°	508.9	553.4	692.3	901.2	997.3
142.5°	523.0	564.0	689.9	872.8	955.1
145°	544.1	581.4	686.4	836.0	900.5
147.5°	566.7	598.8	684.6	803.4	855.1
150°	580.8	609.5	683.5	785.6	825.7
152.5°	593.7	620.1	682.3	770.2	803.4
155°	616.0	636.1	682.0	751.4	772.9
157.5°	632.1	648.5	682.0	736.0	750.9
160°	643.9	656.8	682.0	727.7	739.2
162.5°	653.2	663.9	683.2	720.6	729.8
165°	665.9	674.5	684.9	712.9	717.2
167.5°	674.7	681.3	686.4	706.4	707.5
170°	680.5	684.8	686.4	704.0	704.0
172.5°	685.2	687.2	686.4	700.4	699.3
175°	689.3	690.8	686.4	695.2	693.7
177.5°	690.5	690.5	685.8	692.8	690.5
180°	689.3	689.3	689.3	689.3	689.3

(END OF REPORT)