

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563687

Luminaire Tested: **SQ4-PP3-125U-075D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563687
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-075D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11811.4 lumens
Efficiency: N/A
Efficacy: 134.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 87.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563687
CATALOG NUMBER: SQ4-PP3-125U-075D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563687

CATALOG NUMBER: SQ4-PP3-125U-075D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	87	79	73	68	78	72	67	63	59	55	52	46	44	41	34	33	32	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	31	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	33	27	47	37	30	26	30	25	22	24	21	18	19	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10357	10357	10357
5°	10433	10369	10333
10°	10415	10342	10295
15°	10346	10290	10234
20°	10278	10220	10142
25°	10156	10086	9985
30°	9967	9916	9789
35°	9707	9640	9519
40°	9397	9337	9230
45°	9140	9076	8986
50°	8812	8756	8670
55°	8356	8245	8182
60°	7606	7388	7353
65°	6701	6421	6401
70°	5785	5546	5546
75°	4981	4910	4841
80°	4392	4442	4339
85°	3437	3747	3747



TEST NUMBER: P563687

CATALOG NUMBER: SQ4-PP3-125U-075D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	1.3
10°-20°	454.6	3.8
20°-30°	681.0	5.8
30°-40°	798.8	6.8
40°-50°	801.2	6.8
50°-60°	683.5	5.8
60°-70°	445.8	3.8
70°-80°	223.6	1.9
80°-90°	64.6	0.5
90°-100°	543.4	4.6
100°-110°	1463.8	12.4
110°-120°	1536.2	13.0
120°-130°	1246.6	10.6
130°-140°	977.7	8.3
140°-150°	750.6	6.4
150°-160°	539.7	4.6
160°-170°	329.7	2.8
170°-180°	111.2	0.9
0°-30°	1294.8	11.0
0°-40°	2093.6	17.7
0°-60°	3578.4	30.3
0°-90°	4312.4	36.5
90°-120°	3543.5	30.0
90°-150°	6518.4	55.2
90°-180°	7499.0	63.5
0°-180°	11811.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1684	1684	1684	1684	1684	
5°	1690	1674	1679	1674	1674	160
15°	1625	1609	1616	1610	1607	458
25°	1496	1479	1486	1473	1471	688
35°	1293	1280	1284	1269	1268	808
45°	1051	1044	1043	1033	1033	809
55°	779	776	769	764	763	692
65°	460	452	441	438	440	459
75°	210	210	207	205	204	227
85°	49	53	53	53	53	57
90°	3	9	18	19	19	8
95°	83	296	891	456	315	87
105°	271	421	1619	2422	2273	285
115°	478	585	1348	2605	2946	470
125°	653	750	1210	2046	2408	583
135°	786	877	1176	1650	1869	607
145°	909	980	1162	1411	1515	570
155°	1031	1069	1151	1266	1307	475
165°	1119	1132	1156	1202	1208	315
175°	1163	1162	1157	1173	1170	110
180°	1162	1162	1162	1162	1162	

TEST NUMBER: P563687

CATALOG NUMBER: SQ4-PP3-125U-075D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1683.8	1683.8	1683.8	1683.8	1683.8
2.5°	1694.4	1680.6	1683.8	1681.3	1674.4
5°	1689.7	1673.9	1679.4	1673.5	1673.5
7.5°	1678.2	1660.9	1666.4	1660.5	1660.2
10°	1667.6	1650.3	1655.8	1649.8	1648.4
12.5°	1652.2	1634.9	1641.6	1634.5	1634.2
15°	1624.8	1608.9	1615.9	1610.0	1607.1
17.5°	1593.8	1576.5	1584.9	1576.7	1575.5
20°	1570.2	1552.9	1561.3	1549.5	1549.5
22.5°	1541.9	1524.5	1534.2	1518.8	1518.8
25°	1496.4	1479.1	1486.1	1472.8	1471.3
27.5°	1442.4	1425.4	1432.7	1417.6	1417.3
30°	1403.4	1387.6	1396.1	1379.8	1378.3
32.5°	1360.9	1346.2	1352.4	1336.1	1334.7
35°	1292.8	1279.8	1283.9	1269.1	1267.7
37.5°	1221.0	1207.8	1212.5	1199.8	1199.2
40°	1170.3	1161.6	1162.9	1152.5	1149.6
42.5°	1123.0	1113.2	1114.5	1104.1	1103.6
45°	1050.7	1043.5	1043.4	1033.0	1033.0
47.5°	974.0	968.5	966.9	958.3	958.1
50°	920.9	916.5	915.0	907.5	906.1
52.5°	865.4	863.4	858.3	852.1	851.8
55°	779.2	776.3	768.9	764.4	763.0
57.5°	685.6	679.9	671.5	665.0	666.2
60°	618.3	612.6	600.6	597.7	597.7
62.5°	553.4	546.5	534.5	530.4	532.7
65°	460.4	451.8	441.2	438.3	439.8
67.5°	376.0	368.2	356.8	356.8	355.7
70°	321.7	317.4	308.4	308.4	308.4
72.5°	273.3	271.3	264.7	264.7	263.6
75°	209.6	209.6	206.6	205.1	203.7
77.5°	157.0	157.6	156.1	154.6	152.0
80°	124.0	126.8	125.4	123.9	122.5
82.5°	93.3	96.2	95.9	93.3	93.0
85°	48.7	53.0	53.1	53.1	53.1
87.5°	13.6	19.4	22.4	22.8	23.9
90°	3.0	8.7	17.8	19.2	19.2
92.5°	36.1	127.6	252.2	121.4	84.3
95°	82.9	295.6	890.8	455.5	315.2
97.5°	132.3	338.3	1397.2	1167.2	880.2
100°	170.2	355.4	1558.2	1630.3	1352.5
102.5°	206.9	379.3	1611.5	1977.1	1749.1
105°	270.8	421.3	1618.9	2422.0	2272.9
107.5°	331.2	465.4	1549.9	2650.6	2689.1
110°	371.4	498.8	1487.2	2721.5	2861.9



TEST NUMBER: P563687

CATALOG NUMBER: SQ4-PP3-125U-075D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	414.0	532.1	1426.8	2705.8	2936.5
115°	478.0	585.0	1348.1	2604.8	2946.2
117.5°	536.3	636.7	1287.1	2443.5	2823.7
120°	574.2	671.1	1256.3	2327.7	2718.4
122.5°	607.3	703.1	1233.8	2209.3	2598.8
125°	652.6	749.5	1210.5	2045.9	2407.6
127.5°	696.1	791.6	1195.7	1901.8	2224.7
130°	722.1	817.6	1189.7	1819.2	2102.8
132.5°	748.2	842.5	1183.8	1746.4	2006.9
135°	785.8	876.9	1176.4	1650.5	1869.0
137.5°	821.6	909.0	1172.6	1569.1	1748.5
140°	846.4	930.4	1169.0	1519.0	1681.0
142.5°	872.5	950.6	1166.7	1472.2	1608.8
145°	908.6	979.5	1161.6	1411.1	1515.3
147.5°	947.7	1009.3	1156.6	1359.7	1441.6
150°	973.7	1027.2	1154.2	1327.4	1395.4
152.5°	997.4	1044.0	1153.0	1301.1	1356.4
155°	1031.4	1069.0	1151.3	1266.1	1306.6
157.5°	1061.3	1090.5	1151.6	1241.6	1268.8
160°	1080.2	1104.8	1152.7	1227.2	1247.5
162.5°	1096.8	1116.8	1153.9	1215.2	1229.7
165°	1118.7	1131.7	1155.7	1201.7	1207.5
167.5°	1136.5	1144.0	1157.2	1191.3	1193.6
170°	1148.3	1151.2	1157.2	1185.3	1185.3
172.5°	1155.4	1156.0	1158.4	1179.4	1179.4
175°	1163.1	1161.7	1157.2	1173.4	1170.5
177.5°	1166.4	1164.0	1158.1	1167.5	1165.2
180°	1161.6	1161.6	1161.6	1161.6	1161.6

(END OF REPORT)