

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563711

Luminaire Tested: **SQ4-PP3-125U-100D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563711
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13228.0 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 102.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563711
CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563711

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13761	13761	13761
5°	13862	13777	13729
10°	13839	13741	13679
15°	13747	13672	13597
20°	13656	13579	13477
25°	13494	13401	13267
30°	13244	13174	13007
35°	12898	12809	12647
40°	12485	12406	12265
45°	12144	12059	11940
50°	11709	11633	11520
55°	11102	10955	10871
60°	10107	9818	9769
65°	8904	8533	8504
70°	7688	7370	7370
75°	6616	6523	6431
80°	5834	5905	5763
85°	4566	4982	4982



TEST NUMBER: P563711

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.6	1.6
10°-20°	604.1	4.6
20°-30°	904.8	6.8
30°-40°	1061.3	8.0
40°-50°	1064.6	8.0
50°-60°	908.2	6.9
60°-70°	592.3	4.5
70°-80°	297.2	2.2
80°-90°	85.0	0.6
90°-100°	543.4	4.1
100°-110°	1463.8	11.1
110°-120°	1536.2	11.6
120°-130°	1246.6	9.4
130°-140°	977.7	7.4
140°-150°	750.6	5.7
150°-160°	539.7	4.1
160°-170°	329.7	2.5
170°-180°	111.2	0.8
0°-30°	1720.4	13.0
0°-40°	2781.7	21.0
0°-60°	4754.6	35.9
0°-90°	5729.0	43.3
90°-120°	3543.5	26.8
90°-150°	6518.4	49.3
90°-180°	7499.0	56.7
0°-180°	13228.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2237	2237	2237	2237	2237	
5°	2245	2224	2231	2224	2224	213
15°	2159	2138	2147	2139	2135	609
25°	1988	1965	1975	1957	1955	914
35°	1718	1700	1706	1686	1684	1073
45°	1396	1386	1386	1373	1373	1075
55°	1035	1032	1022	1016	1014	920
65°	612	600	586	582	584	611
75°	278	278	274	272	271	302
85°	65	70	71	71	71	76
90°	3	9	18	19	19	8
95°	83	296	891	456	315	87
105°	271	421	1619	2422	2273	285
115°	478	585	1348	2605	2946	470
125°	653	750	1210	2046	2408	583
135°	786	877	1176	1650	1869	607
145°	909	980	1162	1411	1515	570
155°	1031	1069	1151	1266	1307	475
165°	1119	1132	1156	1202	1208	315
175°	1163	1162	1157	1173	1170	110
180°	1162	1162	1162	1162	1162	



TEST NUMBER: P563711

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2237.3	2237.3	2237.3	2237.3	2237.3
2.5°	2251.4	2233.0	2237.3	2234.0	2224.8
5°	2245.1	2224.1	2231.4	2223.6	2223.6
7.5°	2229.8	2206.8	2214.2	2206.3	2205.9
10°	2215.7	2192.7	2200.0	2192.2	2190.2
12.5°	2195.3	2172.3	2181.2	2171.8	2171.4
15°	2158.9	2137.8	2147.1	2139.2	2135.3
17.5°	2117.7	2094.7	2105.9	2094.9	2093.4
20°	2086.3	2063.3	2074.6	2058.9	2058.9
22.5°	2048.7	2025.7	2038.5	2018.1	2018.1
25°	1988.3	1965.3	1974.6	1956.9	1954.9
27.5°	1916.5	1893.9	1903.6	1883.6	1883.2
30°	1864.7	1843.7	1854.9	1833.3	1831.4
32.5°	1808.3	1788.7	1796.9	1775.3	1773.4
35°	1717.7	1700.4	1705.9	1686.3	1684.3
37.5°	1622.4	1604.7	1611.0	1594.1	1593.4
40°	1554.9	1543.4	1545.1	1531.3	1527.5
42.5°	1492.2	1479.2	1480.8	1467.1	1466.3
45°	1396.1	1386.5	1386.3	1372.6	1372.6
47.5°	1294.1	1286.9	1284.7	1273.4	1273.0
50°	1223.6	1217.8	1215.7	1205.9	1203.9
52.5°	1149.8	1147.1	1140.4	1132.2	1131.8
55°	1035.3	1031.5	1021.6	1015.7	1013.7
57.5°	911.0	903.3	892.2	883.6	885.1
60°	821.6	813.9	798.1	794.1	794.1
62.5°	735.3	726.1	710.2	704.8	707.9
65°	611.8	600.3	586.3	582.4	584.3
67.5°	499.6	489.3	474.1	474.1	472.6
70°	427.5	421.7	409.8	409.8	409.8
72.5°	363.1	360.5	351.8	351.7	350.2
75°	278.4	278.4	274.5	272.5	270.6
77.5°	208.6	209.4	207.5	205.4	202.0
80°	164.7	168.5	166.7	164.7	162.7
82.5°	123.9	127.8	127.5	123.9	123.5
85°	64.7	70.5	70.6	70.6	70.6
87.5°	17.8	25.1	28.7	29.0	30.5
90°	3.0	8.7	17.8	19.2	19.2
92.5°	36.1	127.6	252.2	121.4	84.3
95°	82.9	295.6	890.8	455.5	315.2
97.5°	132.3	338.3	1397.2	1167.2	880.2
100°	170.2	355.4	1558.2	1630.3	1352.5
102.5°	206.9	379.3	1611.5	1977.1	1749.1
105°	270.8	421.3	1618.9	2422.0	2272.9
107.5°	331.2	465.4	1549.9	2650.6	2689.1
110°	371.4	498.8	1487.2	2721.5	2861.9



TEST NUMBER: P563711

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	414.0	532.1	1426.8	2705.8	2936.5
115°	478.0	585.0	1348.1	2604.8	2946.2
117.5°	536.3	636.7	1287.1	2443.5	2823.7
120°	574.2	671.1	1256.3	2327.7	2718.4
122.5°	607.3	703.1	1233.8	2209.3	2598.8
125°	652.6	749.5	1210.5	2045.9	2407.6
127.5°	696.1	791.6	1195.7	1901.8	2224.7
130°	722.1	817.6	1189.7	1819.2	2102.8
132.5°	748.2	842.5	1183.8	1746.4	2006.9
135°	785.8	876.9	1176.4	1650.5	1869.0
137.5°	821.6	909.0	1172.6	1569.1	1748.5
140°	846.4	930.4	1169.0	1519.0	1681.0
142.5°	872.5	950.6	1166.7	1472.2	1608.8
145°	908.6	979.5	1161.6	1411.1	1515.3
147.5°	947.7	1009.3	1156.6	1359.7	1441.6
150°	973.7	1027.2	1154.2	1327.4	1395.4
152.5°	997.4	1044.0	1153.0	1301.1	1356.4
155°	1031.4	1069.0	1151.3	1266.1	1306.6
157.5°	1061.3	1090.5	1151.6	1241.6	1268.8
160°	1080.2	1104.8	1152.7	1227.2	1247.5
162.5°	1096.8	1116.8	1153.9	1215.2	1229.7
165°	1118.7	1131.7	1155.7	1201.7	1207.5
167.5°	1136.5	1144.0	1157.2	1191.3	1193.6
170°	1148.3	1151.2	1157.2	1185.3	1185.3
172.5°	1155.4	1156.0	1158.4	1179.4	1179.4
175°	1163.1	1161.7	1157.2	1173.4	1170.5
177.5°	1166.4	1164.0	1158.1	1167.5	1165.2
180°	1161.6	1161.6	1161.6	1161.6	1161.6

(END OF REPORT)