

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563735

Luminaire Tested: **SQ4-PP3-125U-125D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563735
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14809.2 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 117.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563735
CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563735

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17561	17561	17561
5°	17690	17582	17520
10°	17660	17535	17457
15°	17543	17448	17352
20°	17427	17329	17198
25°	17220	17101	16931
30°	16901	16813	16599
35°	16459	16347	16140
40°	15933	15832	15652
45°	15497	15389	15236
50°	14941	14845	14702
55°	14168	13980	13873
60°	12898	12528	12466
65°	11362	10889	10853
70°	9810	9405	9405
75°	8444	8325	8206
80°	7446	7534	7357
85°	5829	6359	6359



TEST NUMBER: P563735

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.0	1.8
10°-20°	770.9	5.2
20°-30°	1154.7	7.8
30°-40°	1354.4	9.1
40°-50°	1358.6	9.2
50°-60°	1159.0	7.8
60°-70°	755.9	5.1
70°-80°	379.2	2.6
80°-90°	107.7	0.7
90°-100°	543.4	3.7
100°-110°	1463.8	9.9
110°-120°	1536.2	10.4
120°-130°	1246.6	8.4
130°-140°	977.7	6.6
140°-150°	750.6	5.1
150°-160°	539.7	3.6
160°-170°	329.7	2.2
170°-180°	111.2	0.8
0°-30°	2195.5	14.8
0°-40°	3549.9	24.0
0°-60°	6067.5	41.0
0°-90°	7310.2	49.4
90°-120°	3543.5	23.9
90°-150°	6518.4	44.0
90°-180°	7499.0	50.6
0°-180°	14809.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2855	2855	2855	2855	2855	
5°	2865	2838	2848	2838	2838	272
15°	2755	2728	2740	2730	2725	777
25°	2537	2508	2520	2497	2495	1167
35°	2192	2170	2177	2152	2150	1369
45°	1782	1769	1769	1752	1752	1372
55°	1321	1316	1304	1296	1294	1174
65°	781	766	748	743	746	779
75°	355	355	350	348	345	385
85°	83	90	90	90	90	97
90°	3	9	18	19	19	9
95°	83	296	891	456	315	87
105°	271	421	1619	2422	2273	285
115°	478	585	1348	2605	2946	470
125°	653	750	1210	2046	2408	583
135°	786	877	1176	1650	1869	607
145°	909	980	1162	1411	1515	570
155°	1031	1069	1151	1266	1307	475
165°	1119	1132	1156	1202	1208	315
175°	1163	1162	1157	1173	1170	110
180°	1162	1162	1162	1162	1162	



TEST NUMBER: P563735

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2855.1	2855.1	2855.1	2855.1	2855.1
2.5°	2873.1	2849.6	2855.1	2850.8	2839.1
5°	2865.1	2838.2	2847.6	2837.6	2837.6
7.5°	2845.6	2816.2	2825.6	2815.5	2815.1
10°	2827.6	2798.2	2807.6	2797.5	2795.0
12.5°	2801.5	2772.2	2783.5	2771.5	2771.0
15°	2755.0	2728.1	2740.0	2729.9	2725.0
17.5°	2702.5	2673.1	2687.4	2673.4	2671.4
20°	2662.4	2633.1	2647.4	2627.4	2627.4
22.5°	2614.4	2585.0	2601.4	2575.3	2575.3
25°	2537.3	2507.9	2519.8	2497.2	2494.8
27.5°	2445.7	2416.9	2429.2	2403.7	2403.2
30°	2379.7	2352.7	2367.2	2339.6	2337.1
32.5°	2307.6	2282.6	2293.1	2265.5	2263.1
35°	2192.0	2170.0	2177.0	2151.9	2149.5
37.5°	2070.4	2047.9	2055.9	2034.3	2033.3
40°	1984.3	1969.6	1971.8	1954.2	1949.3
42.5°	1904.2	1887.6	1889.7	1872.2	1871.2
45°	1781.6	1769.4	1769.1	1751.6	1751.6
47.5°	1651.5	1642.2	1639.5	1625.0	1624.5
50°	1561.4	1554.1	1551.4	1538.8	1536.4
52.5°	1467.3	1463.9	1455.3	1444.8	1444.3
55°	1321.2	1316.3	1303.7	1296.1	1293.7
57.5°	1162.6	1152.8	1138.5	1127.6	1129.5
60°	1048.5	1038.7	1018.4	1013.4	1013.4
62.5°	938.4	926.6	906.3	899.4	903.3
65°	780.7	766.0	748.2	743.2	745.7
67.5°	637.6	624.4	605.1	605.0	603.0
70°	545.5	538.2	523.0	523.0	523.0
72.5°	463.4	460.0	448.9	448.9	446.9
75°	355.3	355.3	350.3	347.8	345.3
77.5°	266.2	267.2	264.7	262.1	257.7
80°	210.2	215.1	212.7	210.1	207.7
82.5°	158.1	163.0	162.6	158.1	157.6
85°	82.6	89.9	90.1	90.1	90.1
87.5°	22.6	31.6	35.6	35.9	37.9
90°	3.0	8.7	17.8	19.2	19.2
92.5°	36.1	127.6	252.2	121.4	84.3
95°	82.9	295.6	890.8	455.5	315.2
97.5°	132.3	338.3	1397.2	1167.2	880.2
100°	170.2	355.4	1558.2	1630.3	1352.5
102.5°	206.9	379.3	1611.5	1977.1	1749.1
105°	270.8	421.3	1618.9	2422.0	2272.9
107.5°	331.2	465.4	1549.9	2650.6	2689.1
110°	371.4	498.8	1487.2	2721.5	2861.9



TEST NUMBER: P563735

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	414.0	532.1	1426.8	2705.8	2936.5
115°	478.0	585.0	1348.1	2604.8	2946.2
117.5°	536.3	636.7	1287.1	2443.5	2823.7
120°	574.2	671.1	1256.3	2327.7	2718.4
122.5°	607.3	703.1	1233.8	2209.3	2598.8
125°	652.6	749.5	1210.5	2045.9	2407.6
127.5°	696.1	791.6	1195.7	1901.8	2224.7
130°	722.1	817.6	1189.7	1819.2	2102.8
132.5°	748.2	842.5	1183.8	1746.4	2006.9
135°	785.8	876.9	1176.4	1650.5	1869.0
137.5°	821.6	909.0	1172.6	1569.1	1748.5
140°	846.4	930.4	1169.0	1519.0	1681.0
142.5°	872.5	950.6	1166.7	1472.2	1608.8
145°	908.6	979.5	1161.6	1411.1	1515.3
147.5°	947.7	1009.3	1156.6	1359.7	1441.6
150°	973.7	1027.2	1154.2	1327.4	1395.4
152.5°	997.4	1044.0	1153.0	1301.1	1356.4
155°	1031.4	1069.0	1151.3	1266.1	1306.6
157.5°	1061.3	1090.5	1151.6	1241.6	1268.8
160°	1080.2	1104.8	1152.7	1227.2	1247.5
162.5°	1096.8	1116.8	1153.9	1215.2	1229.7
165°	1118.7	1131.7	1155.7	1201.7	1207.5
167.5°	1136.5	1144.0	1157.2	1191.3	1193.6
170°	1148.3	1151.2	1157.2	1185.3	1185.3
172.5°	1155.4	1156.0	1158.4	1179.4	1179.4
175°	1163.1	1161.7	1157.2	1173.4	1170.5
177.5°	1166.4	1164.0	1158.1	1167.5	1165.2
180°	1161.6	1161.6	1161.6	1161.6	1161.6

(END OF REPORT)