

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563759

Luminaire Tested: **SQ4-PP3-150U-050D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563759
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-050D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11962.9 lumens
Efficiency: N/A
Efficacy: 142.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563759
CATALOG NUMBER: SQ4-PP3-150U-050D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563759

CATALOG NUMBER: SQ4-PP3-150U-050D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	26	24	23	18
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	29	25	25	21	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7027	7027	7027
5°	7078	7035	7010
10°	7066	7016	6985
15°	7020	6982	6943
20°	6973	6934	6881
25°	6890	6843	6775
30°	6763	6727	6642
35°	6586	6541	6458
40°	6375	6335	6263
45°	6201	6158	6097
50°	5979	5940	5883
55°	5670	5594	5552
60°	5161	5013	4988
65°	4547	4357	4343
70°	3926	3764	3764
75°	3379	3332	3284
80°	2979	3014	2943
85°	2329	2541	2541



TEST NUMBER: P563759

CATALOG NUMBER: SQ4-PP3-150U-050D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.0	0.9
10°-20°	308.5	2.6
20°-30°	462.0	3.9
30°-40°	541.9	4.5
40°-50°	543.6	4.5
50°-60°	463.8	3.9
60°-70°	302.5	2.5
70°-80°	151.7	1.3
80°-90°	44.9	0.4
90°-100°	651.3	5.4
100°-110°	1761.1	14.7
110°-120°	1851.5	15.5
120°-130°	1503.9	12.6
130°-140°	1179.7	9.9
140°-150°	905.4	7.6
150°-160°	651.2	5.4
160°-170°	397.8	3.3
170°-180°	134.1	1.1
0°-30°	878.5	7.3
0°-40°	1420.4	11.9
0°-60°	2427.8	20.3
0°-90°	2926.9	24.5
90°-120°	4263.9	35.6
90°-150°	7852.9	65.6
90°-180°	9036.0	75.5
0°-180°	11962.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1142	1142	1142	1142	1142	
5°	1146	1136	1139	1135	1135	109
15°	1102	1092	1096	1092	1090	311
25°	1015	1004	1008	999	998	467
35°	877	868	871	861	860	548
45°	713	708	708	701	701	549
55°	529	527	522	519	518	470
65°	312	306	299	297	298	312
75°	142	142	140	139	138	154
85°	33	36	36	36	36	39
90°	3	9	20	21	20	8
95°	101	355	1083	561	333	106
105°	327	506	1954	2882	2764	345
115°	576	705	1620	3136	3541	569
125°	789	904	1460	2464	2895	703
135°	946	1058	1421	1990	2252	731
145°	1100	1182	1402	1703	1833	688
155°	1242	1290	1389	1528	1578	573
165°	1352	1365	1396	1450	1457	381
175°	1403	1402	1397	1415	1412	133
180°	1402	1402	1402	1402	1402	

TEST NUMBER: P563759

CATALOG NUMBER: SQ4-PP3-150U-050D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1142.4	1142.4	1142.4	1142.4	1142.4
2.5°	1149.6	1140.3	1142.4	1140.7	1136.0
5°	1146.4	1135.7	1139.4	1135.4	1135.4
7.5°	1138.6	1126.9	1130.6	1126.6	1126.4
10°	1131.4	1119.7	1123.4	1119.4	1118.4
12.5°	1121.0	1109.3	1113.8	1109.0	1108.8
15°	1102.4	1091.6	1096.4	1092.3	1090.4
17.5°	1081.4	1069.6	1075.4	1069.7	1068.9
20°	1065.3	1053.6	1059.3	1051.3	1051.3
22.5°	1046.1	1034.4	1040.9	1030.5	1030.5
25°	1015.3	1003.5	1008.3	999.2	998.3
27.5°	978.6	967.1	972.0	961.8	961.6
30°	952.2	941.4	947.2	936.2	935.2
32.5°	923.4	913.4	917.6	906.5	905.5
35°	877.1	868.3	871.1	861.1	860.1
37.5°	828.4	819.4	822.6	814.0	813.6
40°	794.0	788.1	789.0	781.9	780.0
42.5°	762.0	755.3	756.2	749.1	748.7
45°	712.9	708.0	707.9	700.9	700.9
47.5°	660.8	657.1	656.0	650.2	650.0
50°	624.8	621.9	620.8	615.8	614.8
52.5°	587.1	585.8	582.3	578.1	577.9
55°	528.7	526.7	521.7	518.6	517.7
57.5°	465.2	461.3	455.6	451.2	452.0
60°	419.5	415.6	407.5	405.5	405.5
62.5°	375.5	370.8	362.7	359.9	361.5
65°	312.4	306.5	299.4	297.4	298.4
67.5°	255.1	249.8	242.1	242.1	241.3
70°	218.3	215.3	209.3	209.3	209.3
72.5°	185.4	184.1	179.6	179.6	178.8
75°	142.2	142.2	140.2	139.2	138.2
77.5°	106.5	106.9	105.9	104.9	103.1
80°	84.1	86.1	85.1	84.1	83.1
82.5°	63.3	65.2	65.1	63.3	63.1
85°	33.0	36.0	36.0	36.0	36.0
87.5°	9.4	13.7	16.7	17.1	17.5
90°	3.0	8.9	19.6	21.1	19.6
92.5°	42.8	156.1	308.1	133.7	96.9
95°	101.1	354.8	1083.2	560.6	333.4
97.5°	162.3	406.9	1688.4	1397.3	1026.2
100°	208.2	428.0	1876.7	1957.2	1582.5
102.5°	250.4	457.2	1943.1	2381.7	2101.5
105°	327.4	505.9	1953.6	2881.8	2763.8
107.5°	398.6	561.4	1868.3	3193.7	3232.9
110°	454.1	601.6	1792.2	3277.5	3444.1



TEST NUMBER: P563759

CATALOG NUMBER: SQ4-PP3-150U-050D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	503.6	641.6	1722.2	3260.7	3540.7
115°	576.3	704.6	1620.2	3136.5	3540.7
117.5°	647.5	767.9	1553.0	2946.8	3404.9
120°	690.9	808.9	1513.1	2810.6	3278.2
122.5°	732.0	847.6	1489.0	2664.6	3135.8
125°	789.0	904.1	1460.3	2464.3	2895.0
127.5°	841.5	954.5	1443.4	2300.8	2679.6
130°	870.5	987.0	1436.2	2199.8	2542.0
132.5°	900.6	1016.0	1428.9	2108.6	2423.7
135°	945.9	1058.0	1421.1	1989.8	2252.3
137.5°	991.5	1097.4	1414.5	1893.3	2107.2
140°	1022.8	1121.7	1412.1	1831.2	2021.5
142.5°	1053.0	1145.9	1407.2	1775.2	1941.9
145°	1099.8	1182.4	1401.5	1703.1	1833.0
147.5°	1142.3	1215.5	1394.9	1637.9	1737.6
150°	1173.7	1238.6	1392.4	1602.4	1682.1
152.5°	1202.7	1259.3	1391.2	1569.5	1635.0
155°	1241.6	1290.3	1389.4	1527.8	1578.0
157.5°	1282.0	1315.9	1389.7	1498.8	1531.8
160°	1304.9	1333.0	1390.9	1480.5	1504.1
162.5°	1323.0	1346.3	1392.1	1465.9	1483.6
165°	1351.7	1365.0	1395.5	1449.9	1457.3
167.5°	1371.3	1380.5	1395.8	1436.3	1439.8
170°	1383.4	1387.8	1397.0	1430.2	1430.2
172.5°	1393.0	1393.9	1397.0	1422.9	1421.7
175°	1403.0	1401.5	1397.0	1415.0	1412.1
177.5°	1406.3	1402.8	1396.7	1408.7	1405.1
180°	1401.5	1401.5	1401.5	1401.5	1401.5

(END OF REPORT)