

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562821

Luminaire Tested: **SQ4-PC3-0U-075D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562821
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8701.7 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct

Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562821
CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562821

CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9806	9806	9806
5°	9879	9816	9779
10°	9855	9809	9782
15°	9804	9804	9794
20°	9739	9768	9768
25°	9647	9717	9687
30°	9530	9645	9603
35°	9388	9532	9466
40°	9233	9363	9268
45°	9065	9129	8988
50°	8828	8828	8687
55°	8548	8437	8310
60°	8135	7971	7844
65°	7519	7369	7304
70°	6583	6636	6610
75°	5297	5858	5894
80°	3765	4968	5019
85°	2290	4167	4167



TEST NUMBER: P562821

CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.7	3.5
10°-20°	865.9	10.0
20°-30°	1311.3	15.1
30°-40°	1572.1	18.1
40°-50°	1603.0	18.4
50°-60°	1399.3	16.1
60°-70°	1001.8	11.5
70°-80°	516.0	5.9
80°-90°	130.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2479.0	28.5
0°-40°	4051.1	46.6
0°-60°	7053.4	81.1
0°-90°	8701.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8701.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3188	3188	3188	3188	3188	
5°	3200	3168	3180	3171	3168	304
15°	3079	3053	3079	3079	3076	868
25°	2843	2823	2864	2855	2855	1308
35°	2500	2495	2539	2521	2521	1564
45°	2084	2078	2099	2072	2066	1604
55°	1594	1574	1574	1550	1550	1421
65°	1033	1010	1013	1004	1004	1022
75°	446	466	493	496	496	482
85°	65	100	118	121	118	91
90°	0	0	0	0	0	



TEST NUMBER: P562821

CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3188.4	3188.4	3188.4	3188.4	3188.4
2.5°	3207.3	3179.5	3188.4	3181.0	3169.5
5°	3200.2	3168.4	3179.5	3170.6	3167.7
7.5°	3177.1	3145.4	3160.0	3154.1	3151.2
10°	3155.9	3124.1	3141.1	3135.2	3132.3
12.5°	3127.5	3098.1	3117.5	3111.6	3111.0
15°	3079.1	3053.2	3079.1	3079.1	3076.2
17.5°	3018.3	2994.6	3022.4	3024.2	3022.4
20°	2975.8	2949.8	2984.7	2981.8	2984.7
22.5°	2923.8	2902.5	2939.8	2932.2	2935.1
25°	2843.0	2822.7	2863.6	2854.8	2854.8
27.5°	2747.3	2732.9	2777.4	2768.0	2768.0
30°	2683.5	2669.1	2716.0	2704.2	2704.2
32.5°	2612.7	2602.9	2647.5	2633.4	2633.4
35°	2500.5	2494.7	2538.9	2521.2	2521.2
37.5°	2384.8	2379.6	2419.6	2398.2	2391.3
40°	2299.8	2296.9	2332.2	2308.6	2308.6
42.5°	2214.7	2211.8	2242.5	2214.1	2214.1
45°	2084.2	2078.5	2099.0	2072.3	2066.5
47.5°	1941.9	1936.2	1949.0	1920.0	1917.1
50°	1845.1	1839.3	1845.1	1818.5	1815.6
52.5°	1745.9	1735.5	1736.5	1709.9	1709.3
55°	1594.2	1574.0	1573.5	1549.9	1549.9
57.5°	1433.6	1407.0	1409.4	1389.2	1386.3
60°	1322.6	1293.7	1296.0	1278.2	1275.3
62.5°	1213.9	1180.5	1187.4	1167.3	1166.7
65°	1033.3	1010.2	1012.6	1003.7	1003.7
67.5°	859.7	838.3	853.8	846.7	846.1
70°	732.1	717.7	738.0	738.0	735.1
72.5°	614.1	613.5	638.9	638.9	640.6
75°	445.8	466.0	493.0	496.0	496.0
77.5°	297.6	333.4	363.1	364.3	363.7
80°	212.6	253.0	280.5	286.3	283.4
82.5°	144.1	186.8	209.6	215.4	212.6
85°	64.9	99.6	118.1	121.0	118.1
87.5°	18.9	39.7	47.2	47.1	42.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)