

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563349

Luminaire Tested: **SQ4-PP3-050U-125D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563349  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 20594.2 lumens  
Efficiency: N/A  
Efficacy: 123.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 167  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563349

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563349

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60
2	94	86	80	75	89	82	76	72	74	69	66	66	63	60	59	57	55	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	43
4	79	68	59	53	74	64	57	51	58	52	48	53	48	44	47	44	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	29
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	31	54	43	35	30	39	33	29	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	20	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17561	17561	17561
5°	17690	17582	17520
10°	17660	17535	17457
15°	17543	17448	17352
20°	17427	17329	17198
25°	17220	17101	16931
30°	16901	16812	16599
35°	16459	16347	16140
40°	15933	15832	15651
45°	15497	15389	15236
50°	14941	14845	14702
55°	14168	13980	13873
60°	12898	12529	12466
65°	11362	10889	10853
70°	9810	9405	9405
75°	8444	8325	8206
80°	7446	7534	7357
85°	5829	6359	6359



TEST NUMBER: P563349

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	540.0	2.6
10°-20°	1541.7	7.5
20°-30°	2309.3	11.2
30°-40°	2708.7	13.2
40°-50°	2717.2	13.2
50°-60°	2318.0	11.3
60°-70°	1511.7	7.3
70°-80°	758.4	3.7
80°-90°	213.4	1.0
90°-100°	439.4	2.1
100°-110°	1193.5	5.8
110°-120°	1227.1	6.0
120°-130°	981.1	4.8
130°-140°	770.9	3.7
140°-150°	591.1	2.9
150°-160°	425.1	2.1
160°-170°	260.0	1.3
170°-180°	87.6	0.4
0°-30°	4391.0	21.3
0°-40°	7099.7	34.5
0°-60°	12134.9	58.9
0°-90°	14618.5	71.0
90°-120°	2860.0	13.9
90°-150°	5203.1	25.3
90°-180°	5976.0	29.0
0°-180°	20594.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5710	5710	5710	5710	5710	
5°	5730	5676	5695	5675	5675	544
15°	5510	5456	5480	5460	5450	1554
25°	5075	5016	5040	4994	4990	2333
35°	4384	4340	4354	4304	4299	2739
45°	3563	3539	3538	3503	3503	2744
55°	2642	2633	2607	2592	2587	2348
65°	1561	1532	1496	1486	1491	1558
75°	711	711	701	696	691	771
85°	165	180	180	180	180	194
90°	3	12	21	26	26	11
95°	65	240	765	333	224	69
105°	212	330	1312	1998	1880	225
115°	377	457	1051	2090	2381	372
125°	518	590	950	1602	1889	462
135°	624	693	924	1304	1471	482
145°	721	773	912	1108	1192	453
155°	815	844	906	995	1024	376
165°	883	894	909	948	950	249
175°	915	918	912	924	921	87
180°	915	915	915	915	915	

TEST NUMBER: P563349

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5710.2	5710.2	5710.2	5710.2	5710.2
2.5°	5746.2	5699.2	5710.2	5701.6	5678.2
5°	5730.2	5676.4	5695.2	5675.2	5675.2
7.5°	5691.2	5632.5	5651.1	5631.1	5630.1
10°	5655.1	5596.4	5615.1	5595.0	5590.1
12.5°	5603.1	5544.4	5567.1	5543.0	5542.0
15°	5510.0	5456.2	5480.0	5459.7	5450.0
17.5°	5404.9	5346.2	5374.9	5346.8	5342.9
20°	5324.8	5266.1	5294.8	5254.8	5254.8
22.5°	5228.8	5170.0	5202.7	5150.7	5150.7
25°	5074.6	5015.9	5039.6	4994.4	4989.5
27.5°	4891.4	4833.7	4858.4	4807.3	4806.4
30°	4759.3	4705.5	4734.3	4679.1	4674.2
32.5°	4615.2	4565.3	4586.2	4531.0	4526.1
35°	4384.0	4339.9	4354.0	4303.8	4298.9
37.5°	4140.8	4095.7	4111.7	4068.7	4066.7
40°	3968.6	3939.2	3943.6	3908.3	3898.5
42.5°	3808.5	3775.2	3779.4	3744.4	3742.4
45°	3563.2	3538.8	3538.2	3503.2	3503.2
47.5°	3303.0	3284.4	3279.0	3249.9	3249.0
50°	3122.8	3108.2	3102.8	3077.7	3072.8
52.5°	2934.7	2927.8	2910.6	2889.6	2888.6
55°	2642.4	2632.6	2607.4	2592.2	2587.4
57.5°	2325.1	2305.5	2277.1	2255.1	2259.1
60°	2096.9	2077.3	2036.9	2026.8	2026.8
62.5°	1876.7	1853.2	1812.6	1798.8	1806.6
65°	1561.4	1532.1	1496.4	1486.5	1491.4
67.5°	1275.2	1248.7	1210.1	1210.0	1206.1
70°	1091.0	1076.3	1046.0	1046.0	1046.0
72.5°	926.8	920.0	897.8	897.7	893.8
75°	710.6	710.6	700.6	695.5	690.6
77.5°	532.5	534.4	529.5	524.3	515.5
80°	420.4	430.2	425.4	420.3	415.4
82.5°	316.3	326.1	325.3	316.3	315.3
85°	165.2	179.8	180.2	180.2	180.2
87.5°	44.6	62.0	68.2	69.4	73.4
90°	2.9	11.6	20.6	26.5	26.5
92.5°	26.5	120.3	208.9	89.7	75.9
95°	64.7	240.3	765.1	333.0	223.7
97.5°	107.1	265.4	1173.0	912.6	641.0
100°	135.4	282.1	1297.8	1315.6	1062.4
102.5°	163.6	298.9	1330.8	1627.0	1403.7
105°	211.9	329.9	1312.5	1998.4	1880.5
107.5°	261.9	366.1	1236.6	2190.2	2223.0
110°	297.2	392.2	1180.1	2228.0	2369.0



TEST NUMBER: P563349

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	327.8	418.2	1123.6	2196.7	2409.0
115°	376.7	457.3	1050.6	2090.1	2380.8
117.5°	422.6	499.7	1004.1	1939.1	2266.6
120°	453.2	528.0	982.9	1837.8	2163.0
122.5°	479.1	553.9	968.8	1736.3	2050.0
125°	517.9	589.9	950.5	1601.6	1889.3
127.5°	552.7	624.0	940.5	1499.4	1746.3
130°	573.9	642.9	935.8	1435.3	1656.8
132.5°	595.0	664.1	931.1	1380.5	1576.8
135°	623.9	692.9	924.1	1304.5	1471.4
137.5°	655.1	717.8	920.5	1237.4	1377.8
140°	673.9	734.3	918.2	1194.7	1321.3
142.5°	692.7	748.6	915.8	1161.3	1267.2
145°	721.0	772.8	912.3	1108.4	1191.8
147.5°	752.8	797.1	909.3	1066.8	1132.4
150°	774.0	811.4	909.3	1042.9	1094.7
152.5°	790.4	823.2	907.0	1021.5	1064.1
155°	815.2	843.9	906.4	995.3	1024.1
157.5°	839.3	861.7	906.4	977.5	999.4
160°	853.4	873.6	906.4	965.6	982.9
162.5°	867.5	883.1	908.7	956.1	968.8
165°	882.9	894.4	909.3	947.7	950.5
167.5°	898.7	904.5	912.3	937.6	939.9
170°	903.5	909.2	912.3	932.9	932.9
172.5°	908.2	911.6	912.3	928.2	928.2
175°	915.2	918.1	912.3	924.0	921.1
177.5°	917.6	917.6	910.5	919.8	915.2
180°	915.2	915.2	915.2	915.2	915.2

(END OF REPORT)