

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563807

Luminaire Tested: **SQ4-PP3-150U-100D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563807
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-100D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14765.1 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 112.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563807
CATALOG NUMBER: SQ4-PP3-150U-100D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563807

CATALOG NUMBER: SQ4-PP3-150U-100D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	34	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	73	62	54	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	38	33	38	32	28	30	26	24	23	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	52	40	33	28	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13761	13761	13761
5°	13862	13777	13729
10°	13839	13741	13679
15°	13747	13672	13597
20°	13656	13579	13477
25°	13494	13401	13267
30°	13244	13174	13007
35°	12898	12809	12647
40°	12485	12406	12265
45°	12144	12059	11940
50°	11709	11633	11520
55°	11102	10955	10871
60°	10107	9818	9769
65°	8904	8533	8504
70°	7688	7370	7370
75°	6616	6523	6431
80°	5834	5905	5763
85°	4566	4982	4982



TEST NUMBER: P563807

CATALOG NUMBER: SQ4-PP3-150U-100D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.6	1.4
10°-20°	604.1	4.1
20°-30°	904.8	6.1
30°-40°	1061.3	7.2
40°-50°	1064.6	7.2
50°-60°	908.2	6.2
60°-70°	592.3	4.0
70°-80°	297.2	2.0
80°-90°	85.2	0.6
90°-100°	651.3	4.4
100°-110°	1761.1	11.9
110°-120°	1851.5	12.5
120°-130°	1503.9	10.2
130°-140°	1179.7	8.0
140°-150°	905.4	6.1
150°-160°	651.2	4.4
160°-170°	397.8	2.7
170°-180°	134.1	0.9
0°-30°	1720.4	11.7
0°-40°	2781.7	18.8
0°-60°	4754.6	32.2
0°-90°	5729.2	38.8
90°-120°	4263.9	28.9
90°-150°	7852.9	53.2
90°-180°	9036.0	61.2
0°-180°	14765.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2237	2237	2237	2237	2237	
5°	2245	2224	2231	2224	2224	213
15°	2159	2138	2147	2139	2135	609
25°	1988	1965	1975	1957	1955	914
35°	1718	1700	1706	1686	1684	1073
45°	1396	1386	1386	1373	1373	1075
55°	1035	1032	1022	1016	1014	920
65°	612	600	586	582	584	611
75°	278	278	274	272	271	302
85°	65	70	71	71	71	76
90°	3	9	20	21	20	9
95°	101	355	1083	561	333	106
105°	327	506	1954	2882	2764	345
115°	576	705	1620	3136	3541	569
125°	789	904	1460	2464	2895	703
135°	946	1058	1421	1990	2252	731
145°	1100	1182	1402	1703	1833	688
155°	1242	1290	1389	1528	1578	573
165°	1352	1365	1396	1450	1457	381
175°	1403	1402	1397	1415	1412	133
180°	1402	1402	1402	1402	1402	



TEST NUMBER: P563807

CATALOG NUMBER: SQ4-PP3-150U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2237.3	2237.3	2237.3	2237.3	2237.3
2.5°	2251.4	2233.0	2237.3	2234.0	2224.8
5°	2245.1	2224.1	2231.4	2223.6	2223.6
7.5°	2229.8	2206.8	2214.2	2206.3	2205.9
10°	2215.7	2192.7	2200.0	2192.2	2190.2
12.5°	2195.3	2172.3	2181.2	2171.8	2171.4
15°	2158.9	2137.8	2147.1	2139.2	2135.3
17.5°	2117.7	2094.7	2105.9	2094.9	2093.4
20°	2086.3	2063.3	2074.6	2058.9	2058.9
22.5°	2048.7	2025.7	2038.5	2018.1	2018.1
25°	1988.3	1965.3	1974.6	1956.9	1954.9
27.5°	1916.5	1893.9	1903.6	1883.6	1883.2
30°	1864.7	1843.7	1854.9	1833.3	1831.4
32.5°	1808.3	1788.7	1796.9	1775.3	1773.4
35°	1717.7	1700.4	1705.9	1686.3	1684.3
37.5°	1622.4	1604.7	1611.0	1594.1	1593.4
40°	1554.9	1543.4	1545.1	1531.3	1527.5
42.5°	1492.2	1479.2	1480.8	1467.1	1466.3
45°	1396.1	1386.5	1386.3	1372.6	1372.6
47.5°	1294.1	1286.9	1284.7	1273.4	1273.0
50°	1223.6	1217.8	1215.7	1205.9	1203.9
52.5°	1149.8	1147.1	1140.4	1132.2	1131.8
55°	1035.3	1031.5	1021.6	1015.7	1013.7
57.5°	911.0	903.3	892.2	883.6	885.1
60°	821.6	813.9	798.1	794.1	794.1
62.5°	735.3	726.1	710.2	704.8	707.9
65°	611.8	600.3	586.3	582.4	584.3
67.5°	499.6	489.3	474.1	474.1	472.6
70°	427.5	421.7	409.8	409.8	409.8
72.5°	363.1	360.5	351.8	351.7	350.2
75°	278.4	278.4	274.5	272.5	270.6
77.5°	208.6	209.4	207.5	205.4	202.0
80°	164.7	168.5	166.7	164.7	162.7
82.5°	123.9	127.8	127.5	123.9	123.5
85°	64.7	70.5	70.6	70.6	70.6
87.5°	17.9	25.2	29.0	29.4	30.6
90°	3.0	8.9	19.6	21.1	19.6
92.5°	42.8	156.1	308.1	133.7	96.9
95°	101.1	354.8	1083.2	560.6	333.4
97.5°	162.3	406.9	1688.4	1397.3	1026.2
100°	208.2	428.0	1876.7	1957.2	1582.5
102.5°	250.4	457.2	1943.1	2381.7	2101.5
105°	327.4	505.9	1953.6	2881.8	2763.8
107.5°	398.6	561.4	1868.3	3193.7	3232.9
110°	454.1	601.6	1792.2	3277.5	3444.1

TEST NUMBER: P563807

CATALOG NUMBER: SQ4-PP3-150U-100D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	503.6	641.6	1722.2	3260.7	3540.7
115°	576.3	704.6	1620.2	3136.5	3540.7
117.5°	647.5	767.9	1553.0	2946.8	3404.9
120°	690.9	808.9	1513.1	2810.6	3278.2
122.5°	732.0	847.6	1489.0	2664.6	3135.8
125°	789.0	904.1	1460.3	2464.3	2895.0
127.5°	841.5	954.5	1443.4	2300.8	2679.6
130°	870.5	987.0	1436.2	2199.8	2542.0
132.5°	900.6	1016.0	1428.9	2108.6	2423.7
135°	945.9	1058.0	1421.1	1989.8	2252.3
137.5°	991.5	1097.4	1414.5	1893.3	2107.2
140°	1022.8	1121.7	1412.1	1831.2	2021.5
142.5°	1053.0	1145.9	1407.2	1775.2	1941.9
145°	1099.8	1182.4	1401.5	1703.1	1833.0
147.5°	1142.3	1215.5	1394.9	1637.9	1737.6
150°	1173.7	1238.6	1392.4	1602.4	1682.1
152.5°	1202.7	1259.3	1391.2	1569.5	1635.0
155°	1241.6	1290.3	1389.4	1527.8	1578.0
157.5°	1282.0	1315.9	1389.7	1498.8	1531.8
160°	1304.9	1333.0	1390.9	1480.5	1504.1
162.5°	1323.0	1346.3	1392.1	1465.9	1483.6
165°	1351.7	1365.0	1395.5	1449.9	1457.3
167.5°	1371.3	1380.5	1395.8	1436.3	1439.8
170°	1383.4	1387.8	1397.0	1430.2	1430.2
172.5°	1393.0	1393.9	1397.0	1422.9	1421.7
175°	1403.0	1401.5	1397.0	1415.0	1412.1
177.5°	1406.3	1402.8	1396.7	1408.7	1405.1
180°	1401.5	1401.5	1401.5	1401.5	1401.5

(END OF REPORT)