

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563879

Luminaire Tested: **SQ4-PR1-025U-075D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563879  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-025U-075D-835-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5734.2 lumens  
Efficiency: N/A  
Efficacy: 118.0 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 48.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563879  
CATALOG NUMBER: SQ4-PR1-025U-075D-835-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563879

CATALOG NUMBER: SQ4-PR1-025U-075D-835-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75				
1	104	99	96	92	99	95	91	88	86	83	81	78	76	74	70	69	67	64				
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	58	54				
3	87	77	70	64	82	74	67	62	67	62	57	61	57	53	56	52	49	46				
4	80	69	61	54	76	66	58	53	60	54	49	55	50	46	50	46	43	40				
5	73	62	53	47	70	59	51	46	54	48	43	50	44	40	45	41	38	35				
6	68	55	47	41	64	53	46	40	49	43	38	45	40	35	41	37	33	31				
7	63	50	42	36	60	48	41	35	45	38	33	41	36	32	38	33	30	27				
8	58	46	38	32	56	44	37	32	41	34	30	38	32	28	35	30	27	25				
9	55	42	34	29	52	40	33	28	37	31	27	35	29	26	32	27	24	22				
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10541	10541	10541
5°	10636	10554	10499
10°	10602	10528	10473
15°	10555	10490	10434
20°	10502	10435	10358
25°	10428	10358	10238
30°	10316	10242	10096
35°	10164	10075	9931
40°	9932	9825	9647
45°	9528	9361	9167
50°	8814	8602	8432
55°	7693	7518	7361
60°	6483	6428	6301
65°	5608	5628	5586
70°	5151	5176	5176
75°	4945	4945	4981
80°	4654	4704	4654
85°	3747	4164	4164



TEST NUMBER: P563879

CATALOG NUMBER: SQ4-PR1-025U-075D-835-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.1	2.8
10°-20°	463.7	8.1
20°-30°	699.4	12.2
30°-40°	833.3	14.5
40°-50°	821.6	14.3
50°-60°	627.9	10.9
60°-70°	388.6	6.8
70°-80°	220.7	3.8
80°-90°	68.3	1.2
90°-100°	108.9	1.9
100°-110°	286.4	5.0
110°-120°	297.0	5.2
120°-130°	238.2	4.2
130°-140°	186.9	3.3
140°-150°	143.5	2.5
150°-160°	103.3	1.8
160°-170°	63.2	1.1
170°-180°	21.4	0.4
0°-30°	1325.1	23.1
0°-40°	2158.4	37.6
0°-60°	3607.8	62.9
0°-90°	4285.3	74.7
90°-120°	692.3	12.1
90°-150°	1261.0	22.0
90°-180°	1449.0	25.3
0°-180°	5734.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1714	1714	1714	1714	1714	
5°	1723	1704	1709	1703	1700	163
15°	1658	1640	1647	1641	1638	468
25°	1537	1518	1526	1510	1509	707
35°	1354	1338	1342	1324	1323	845
45°	1095	1081	1076	1057	1054	839
55°	717	706	701	689	686	643
65°	385	382	387	384	384	390
75°	208	208	208	210	210	220
85°	53	56	59	59	59	62
90°	1	4	12	6	6	3
95°	14	56	188	97	66	16
105°	52	78	317	481	448	55
115°	92	111	254	506	578	91
125°	128	143	231	390	460	113
135°	152	167	224	315	357	118
145°	176	188	221	268	290	110
155°	199	205	221	242	249	92
165°	215	218	221	229	232	61
175°	224	224	222	225	225	21
180°	224	224	224	224	224	

TEST NUMBER: P563879

CATALOG NUMBER: SQ4-PR1-025U-075D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1713.7	1713.7	1713.7	1713.7	1713.7
2.5°	1724.4	1709.4	1713.7	1710.0	1701.9
5°	1722.6	1703.8	1709.3	1703.3	1700.5
7.5°	1709.3	1690.8	1696.3	1690.4	1688.6
10°	1697.5	1680.2	1685.7	1679.7	1676.8
12.5°	1684.5	1666.0	1672.7	1665.6	1662.7
15°	1657.6	1640.3	1647.3	1641.3	1638.5
17.5°	1628.1	1609.7	1616.6	1609.7	1606.0
20°	1604.5	1587.2	1594.2	1583.8	1582.4
22.5°	1578.5	1561.2	1568.2	1554.3	1554.0
25°	1536.6	1517.8	1526.3	1510.0	1508.6
27.5°	1486.7	1469.4	1476.4	1459.8	1458.1
30°	1452.5	1435.2	1442.1	1424.4	1421.5
32.5°	1413.5	1397.3	1403.2	1385.4	1383.7
35°	1353.6	1337.7	1341.8	1324.0	1322.6
37.5°	1285.4	1270.9	1273.3	1253.8	1252.3
40°	1237.0	1222.5	1223.7	1203.0	1201.5
42.5°	1183.8	1169.4	1168.2	1147.5	1146.0
45°	1095.3	1080.8	1076.1	1056.8	1053.9
47.5°	994.3	979.9	971.0	955.3	953.3
50°	921.1	906.6	898.9	885.6	881.2
52.5°	842.0	827.5	821.0	808.8	804.5
55°	717.4	705.8	701.1	689.3	686.4
57.5°	599.0	591.2	589.8	578.3	577.2
60°	527.0	522.6	522.5	512.2	512.2
62.5°	465.6	462.4	464.7	457.9	456.7
65°	385.3	382.4	386.7	383.8	383.8
67.5°	321.8	321.8	324.4	323.3	323.3
70°	286.4	286.4	287.8	287.8	287.8
72.5°	254.5	253.3	257.1	257.1	256.0
75°	208.1	208.1	208.1	209.6	209.6
77.5°	162.1	162.4	163.6	163.2	162.1
80°	131.4	132.8	132.8	131.4	131.4
82.5°	100.7	102.1	102.1	101.8	100.7
85°	53.1	56.0	59.0	59.0	59.0
87.5°	15.6	20.8	25.9	24.7	23.6
90°	1.4	4.2	11.5	5.7	5.7
92.5°	6.0	29.0	64.2	28.4	18.3
95°	14.3	56.4	187.7	96.7	65.9
97.5°	24.9	61.9	280.9	223.3	164.5
100°	33.0	66.6	309.5	313.7	243.6
102.5°	39.8	71.2	317.5	390.7	330.7
105°	51.6	78.2	316.7	480.7	448.5
107.5°	63.6	88.3	298.6	527.5	535.3
110°	71.6	94.1	283.7	539.5	573.2



TEST NUMBER: P563879

CATALOG NUMBER: SQ4-PR1-025U-075D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	79.7	101.0	270.0	531.9	583.5
115°	91.7	111.3	253.6	506.0	577.5
117.5°	103.5	121.4	242.5	470.1	549.4
120°	110.3	127.1	237.9	446.0	523.0
122.5°	117.2	134.0	234.4	421.9	497.8
125°	127.5	142.9	230.7	389.9	460.0
127.5°	135.8	151.5	227.5	364.2	423.3
130°	140.4	157.2	226.4	348.0	402.7
132.5°	145.0	161.8	225.3	334.1	383.2
135°	151.9	167.3	223.5	314.8	356.8
137.5°	159.1	174.2	223.3	300.3	334.7
140°	164.8	178.8	222.1	288.8	321.0
142.5°	169.4	182.3	222.1	280.6	308.4
145°	176.3	187.5	220.7	268.4	289.5
147.5°	183.1	194.1	220.7	258.3	275.7
150°	187.7	197.5	220.7	252.5	266.5
152.5°	192.3	199.9	220.7	247.9	258.5
155°	199.2	204.8	220.7	242.3	249.3
157.5°	204.3	209.7	220.7	237.4	242.5
160°	207.8	212.0	220.7	235.1	237.9
162.5°	211.2	214.3	220.7	232.8	235.6
165°	214.9	217.7	220.7	229.3	232.1
167.5°	218.4	219.8	222.1	227.9	229.0
170°	220.7	222.1	222.1	227.8	227.8
172.5°	221.8	222.1	222.1	226.7	225.5
175°	223.5	223.5	222.1	225.0	225.0
177.5°	223.5	223.5	222.4	224.7	223.5
180°	223.5	223.5	223.5	223.5	223.5

(END OF REPORT)