

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564527

Luminaire Tested: **SQ4-PW1-025U-050D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564527
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-050D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4342.1 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564527
CATALOG NUMBER: SQ4-PW1-025U-050D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564527

CATALOG NUMBER: SQ4-PW1-025U-050D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	63	62	61	56
2	93	85	79	74	87	80	75	70	72	67	64	63	60	57	56	53	51	47
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	46	44	40
4	78	66	58	52	73	63	56	50	56	50	46	50	45	42	44	41	38	35
5	71	59	51	45	67	56	49	43	50	44	40	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	23
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6992	6992	6992
5°	7037	6981	6950
10°	6981	6925	6887
15°	6906	6830	6805
20°	6824	6719	6706
25°	6729	6607	6586
30°	6587	6487	6445
35°	6400	6310	6272
40°	6200	6103	6079
45°	5959	5880	5854
50°	5712	5664	5626
55°	5445	5445	5359
60°	5113	5211	5026
65°	4679	4912	4563
70°	4124	4521	4016
75°	3522	4047	3427
80°	2731	3404	2766
85°	1764	2618	2329



TEST NUMBER: P564527

CATALOG NUMBER: SQ4-PW1-025U-050D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.0	2.5
10°-20°	302.2	7.0
20°-30°	448.3	10.3
30°-40°	524.5	12.1
40°-50°	522.2	12.0
50°-60°	450.9	10.4
60°-70°	324.6	7.5
70°-80°	170.2	3.9
80°-90°	43.4	1.0
90°-100°	108.9	2.5
100°-110°	286.4	6.6
110°-120°	297.0	6.8
120°-130°	238.2	5.5
130°-140°	186.9	4.3
140°-150°	143.5	3.3
150°-160°	103.3	2.4
160°-170°	63.2	1.5
170°-180°	21.4	0.5
0°-30°	857.5	19.7
0°-40°	1382.0	31.8
0°-60°	2355.1	54.2
0°-90°	2893.3	66.6
90°-120°	692.3	15.9
90°-150°	1261.0	29.0
90°-180°	1449.0	33.4
0°-180°	4342.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1137	1137	1137	1137	1137	
5°	1140	1127	1131	1128	1126	108
15°	1085	1071	1073	1071	1069	306
25°	992	975	974	968	970	456
35°	852	840	840	832	835	533
45°	685	679	676	674	673	529
55°	508	507	508	501	500	453
65°	322	331	338	324	314	319
75°	148	162	170	159	144	159
85°	25	33	37	35	33	33
90°	1	4	12	6	6	2
95°	14	56	188	97	66	16
105°	52	78	317	481	448	55
115°	92	111	254	506	578	91
125°	128	143	231	390	460	113
135°	152	167	224	315	357	118
145°	176	188	221	268	290	110
155°	199	205	221	242	249	92
165°	215	218	221	229	232	61
175°	224	224	222	225	225	21
180°	224	224	224	224	224	

TEST NUMBER: P564527

CATALOG NUMBER: SQ4-PW1-025U-050D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1136.7	1136.7	1136.7	1136.7	1136.7
2.5°	1143.1	1133.7	1136.7	1134.2	1128.7
5°	1139.7	1127.0	1130.7	1127.6	1125.7
7.5°	1128.1	1116.3	1119.1	1115.8	1114.7
10°	1117.7	1105.9	1108.7	1104.6	1102.7
12.5°	1105.7	1093.1	1095.8	1091.8	1090.6
15°	1084.6	1070.9	1072.6	1070.6	1068.6
17.5°	1060.2	1046.3	1046.6	1043.4	1043.0
20°	1042.6	1027.9	1026.5	1022.6	1024.5
22.5°	1023.3	1007.9	1006.5	1001.0	1003.7
25°	991.5	974.8	973.5	967.5	970.5
27.5°	954.6	938.2	938.2	929.9	933.0
30°	927.4	911.7	913.4	903.4	907.4
32.5°	898.5	884.4	885.3	875.4	879.3
35°	852.3	840.5	840.3	832.3	835.3
37.5°	805.0	794.6	793.0	788.4	789.2
40°	772.2	763.3	760.1	757.1	757.1
42.5°	737.7	729.7	726.5	724.3	723.5
45°	685.0	679.2	676.0	674.0	673.0
47.5°	632.9	627.5	624.7	623.3	622.3
50°	596.9	593.0	591.9	588.9	587.9
52.5°	560.8	558.5	557.4	553.6	552.6
55°	507.8	506.8	507.8	500.7	499.7
57.5°	452.5	454.0	457.3	447.8	445.5
60°	415.6	419.5	423.6	412.5	408.6
62.5°	378.0	384.2	390.0	377.2	371.8
65°	321.5	331.3	337.5	324.2	313.5
67.5°	267.0	279.1	286.6	272.3	260.2
70°	229.3	243.1	251.4	237.0	223.3
72.5°	196.5	211.8	218.5	205.0	191.3
75°	148.2	161.9	170.3	158.9	144.2
77.5°	105.2	118.1	125.0	115.1	103.0
80°	77.1	90.8	96.1	87.9	78.1
82.5°	54.7	66.0	69.7	64.7	58.1
85°	25.0	32.9	37.1	35.0	33.0
87.5°	6.7	12.7	17.5	16.4	17.2
90°	1.4	4.2	11.5	5.7	5.7
92.5°	6.0	29.0	64.2	28.4	18.3
95°	14.3	56.4	187.7	96.7	65.9
97.5°	24.9	61.9	280.9	223.3	164.5
100°	33.0	66.6	309.5	313.7	243.6
102.5°	39.8	71.2	317.5	390.7	330.7
105°	51.6	78.2	316.7	480.7	448.5
107.5°	63.6	88.3	298.6	527.5	535.3
110°	71.6	94.1	283.7	539.5	573.2



TEST NUMBER: P564527

CATALOG NUMBER: SQ4-PW1-025U-050D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	79.7	101.0	270.0	531.9	583.5
115°	91.7	111.3	253.6	506.0	577.5
117.5°	103.5	121.4	242.5	470.1	549.4
120°	110.3	127.1	237.9	446.0	523.0
122.5°	117.2	134.0	234.4	421.9	497.8
125°	127.5	142.9	230.7	389.9	460.0
127.5°	135.8	151.5	227.5	364.2	423.3
130°	140.4	157.2	226.4	348.0	402.7
132.5°	145.0	161.8	225.3	334.1	383.2
135°	151.9	167.3	223.5	314.8	356.8
137.5°	159.1	174.2	223.3	300.3	334.7
140°	164.8	178.8	222.1	288.8	321.0
142.5°	169.4	182.3	222.1	280.6	308.4
145°	176.3	187.5	220.7	268.4	289.5
147.5°	183.1	194.1	220.7	258.3	275.7
150°	187.7	197.5	220.7	252.5	266.5
152.5°	192.3	199.9	220.7	247.9	258.5
155°	199.2	204.8	220.7	242.3	249.3
157.5°	204.3	209.7	220.7	237.4	242.5
160°	207.8	212.0	220.7	235.1	237.9
162.5°	211.2	214.3	220.7	232.8	235.6
165°	214.9	217.7	220.7	229.3	232.1
167.5°	218.4	219.8	222.1	227.9	229.0
170°	220.7	222.1	222.1	227.8	227.8
172.5°	221.8	222.1	222.1	226.7	225.5
175°	223.5	223.5	222.1	225.0	225.0
177.5°	223.5	223.5	222.4	224.7	223.5
180°	223.5	223.5	223.5	223.5	223.5

(END OF REPORT)