

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564575

Luminaire Tested: **SQ4-PW1-025U-100D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564575  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-025U-100D-835-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7113.8 lumens  
Efficiency: N/A  
Efficacy: 112.0 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 63.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564575  
CATALOG NUMBER: SQ4-PW1-025U-100D-835-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P564575

CATALOG NUMBER: SQ4-PW1-025U-100D-835-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	105	100	96	93	100	96	92	89	88	85	83	81	79	77	74	72	71	67
2	95	88	81	76	91	84	78	73	77	73	69	71	67	64	65	62	60	57
3	87	77	70	63	83	74	67	62	68	63	58	63	58	54	58	54	51	48
4	80	69	60	54	76	66	58	52	61	55	50	56	51	47	52	48	44	41
5	73	61	53	46	70	59	51	45	55	48	43	51	45	41	47	42	38	36
6	68	55	47	41	65	53	45	40	49	43	38	46	40	36	42	38	34	32
7	63	50	42	36	60	48	40	35	45	38	33	42	36	32	39	34	30	28
8	58	46	37	32	56	44	36	31	41	35	30	38	33	28	36	31	27	25
9	55	42	34	29	52	40	33	28	38	31	27	35	30	26	33	28	25	23
10	51	39	31	26	49	37	30	25	35	29	24	33	27	23	31	26	22	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13692	13692	13692
5°	13780	13672	13611
10°	13671	13560	13487
15°	13526	13376	13326
20°	13364	13159	13133
25°	13178	12938	12898
30°	12899	12704	12620
35°	12533	12356	12282
40°	12142	11952	11905
45°	11669	11516	11465
50°	11185	11091	11017
55°	10664	10664	10495
60°	10012	10205	9844
65°	9163	9620	8935
70°	8076	8853	7866
75°	6899	7923	6711
80°	5349	6670	5419
85°	3458	5124	4566



TEST NUMBER: P564575

CATALOG NUMBER: SQ4-PW1-025U-100D-835-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.6	2.9
10°-20°	591.8	8.3
20°-30°	877.9	12.3
30°-40°	1027.2	14.4
40°-50°	1022.6	14.4
50°-60°	883.1	12.4
60°-70°	635.6	8.9
70°-80°	333.3	4.7
80°-90°	83.8	1.2
90°-100°	108.9	1.5
100°-110°	286.4	4.0
110°-120°	297.0	4.2
120°-130°	238.2	3.3
130°-140°	186.9	2.6
140°-150°	143.5	2.0
150°-160°	103.3	1.5
160°-170°	63.2	0.9
170°-180°	21.4	0.3
0°-30°	1679.3	23.6
0°-40°	2706.5	38.0
0°-60°	4612.1	64.8
0°-90°	5664.9	79.6
90°-120°	692.3	9.7
90°-150°	1261.0	17.7
90°-180°	1449.0	20.4
0°-180°	7113.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2226	2226	2226	2226	2226	
5°	2232	2207	2214	2208	2204	211
15°	2124	2097	2100	2096	2093	599
25°	1942	1909	1906	1895	1900	893
35°	1669	1646	1646	1630	1636	1043
45°	1342	1330	1324	1320	1318	1035
55°	994	992	994	981	979	887
65°	630	649	661	635	614	624
75°	290	317	333	311	282	311
85°	49	64	73	69	65	65
90°	1	4	12	6	6	3
95°	14	56	188	97	66	16
105°	52	78	317	481	448	55
115°	92	111	254	506	578	91
125°	128	143	231	390	460	113
135°	152	167	224	315	357	118
145°	176	188	221	268	290	110
155°	199	205	221	242	249	92
165°	215	218	221	229	232	61
175°	224	224	222	225	225	21
180°	224	224	224	224	224	



TEST NUMBER: P564575

CATALOG NUMBER: SQ4-PW1-025U-100D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2226.1	2226.1	2226.1	2226.1	2226.1
2.5°	2238.6	2220.2	2226.1	2221.1	2210.4
5°	2231.9	2207.0	2214.3	2208.3	2204.5
7.5°	2209.2	2186.2	2191.5	2185.2	2182.9
10°	2188.8	2165.8	2171.1	2163.2	2159.4
12.5°	2165.3	2140.7	2146.0	2138.1	2135.8
15°	2124.1	2097.2	2100.5	2096.5	2092.7
17.5°	2076.2	2049.0	2049.5	2043.3	2042.5
20°	2041.7	2012.9	2010.3	2002.6	2006.4
22.5°	2004.0	1973.7	1971.1	1960.2	1965.6
25°	1941.7	1909.1	1906.4	1894.7	1900.5
27.5°	1869.5	1837.3	1837.3	1821.0	1827.1
30°	1816.2	1785.5	1788.7	1769.3	1776.9
32.5°	1759.7	1732.1	1733.8	1714.3	1722.0
35°	1669.1	1646.0	1645.5	1630.0	1635.7
37.5°	1576.5	1556.2	1552.9	1544.0	1545.5
40°	1512.2	1494.9	1488.6	1482.7	1482.7
42.5°	1444.7	1429.0	1422.7	1418.4	1416.8
45°	1341.5	1330.0	1323.9	1319.9	1318.0
47.5°	1239.5	1228.8	1223.5	1220.7	1218.7
50°	1168.9	1161.3	1159.1	1153.2	1151.3
52.5°	1098.3	1093.7	1091.7	1084.2	1082.2
55°	994.4	992.5	994.4	980.6	978.7
57.5°	886.1	889.2	895.5	877.0	872.4
60°	813.9	821.6	829.6	807.9	800.2
62.5°	740.2	752.5	763.7	738.8	728.0
65°	629.6	648.8	661.0	635.0	613.9
67.5°	522.9	546.7	561.3	533.3	509.5
70°	449.1	476.0	492.3	464.2	437.4
72.5°	384.8	414.7	428.0	401.5	374.6
75°	290.3	317.1	333.4	311.2	282.4
77.5°	205.9	231.2	244.8	225.4	201.6
80°	151.0	177.9	188.3	172.2	153.0
82.5°	107.1	129.3	136.5	126.8	113.8
85°	49.0	64.4	72.6	68.6	64.7
87.5°	12.8	24.1	32.1	31.0	32.5
90°	1.4	4.2	11.5	5.7	5.7
92.5°	6.0	29.0	64.2	28.4	18.3
95°	14.3	56.4	187.7	96.7	65.9
97.5°	24.9	61.9	280.9	223.3	164.5
100°	33.0	66.6	309.5	313.7	243.6
102.5°	39.8	71.2	317.5	390.7	330.7
105°	51.6	78.2	316.7	480.7	448.5
107.5°	63.6	88.3	298.6	527.5	535.3
110°	71.6	94.1	283.7	539.5	573.2

TEST NUMBER: P564575

CATALOG NUMBER: SQ4-PW1-025U-100D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	79.7	101.0	270.0	531.9	583.5
115°	91.7	111.3	253.6	506.0	577.5
117.5°	103.5	121.4	242.5	470.1	549.4
120°	110.3	127.1	237.9	446.0	523.0
122.5°	117.2	134.0	234.4	421.9	497.8
125°	127.5	142.9	230.7	389.9	460.0
127.5°	135.8	151.5	227.5	364.2	423.3
130°	140.4	157.2	226.4	348.0	402.7
132.5°	145.0	161.8	225.3	334.1	383.2
135°	151.9	167.3	223.5	314.8	356.8
137.5°	159.1	174.2	223.3	300.3	334.7
140°	164.8	178.8	222.1	288.8	321.0
142.5°	169.4	182.3	222.1	280.6	308.4
145°	176.3	187.5	220.7	268.4	289.5
147.5°	183.1	194.1	220.7	258.3	275.7
150°	187.7	197.5	220.7	252.5	266.5
152.5°	192.3	199.9	220.7	247.9	258.5
155°	199.2	204.8	220.7	242.3	249.3
157.5°	204.3	209.7	220.7	237.4	242.5
160°	207.8	212.0	220.7	235.1	237.9
162.5°	211.2	214.3	220.7	232.8	235.6
165°	214.9	217.7	220.7	229.3	232.1
167.5°	218.4	219.8	222.1	227.9	229.0
170°	220.7	222.1	222.1	227.8	227.8
172.5°	221.8	222.1	222.1	226.7	225.5
175°	223.5	223.5	222.1	225.0	225.0
177.5°	223.5	223.5	222.4	224.7	223.5
180°	223.5	223.5	223.5	223.5	223.5

(END OF REPORT)