

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564791

Luminaire Tested: **SQ4-PW1-075U-125D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564791
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-075U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11720.1 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 97.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564791
CATALOG NUMBER: SQ4-PW1-075U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564791

CATALOG NUMBER: SQ4-PW1-075U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	69	65	62	61	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41	37
4	77	66	58	51	71	62	55	49	55	49	44	48	43	40	42	38	35	32
5	70	59	50	44	66	55	48	42	49	43	38	43	38	35	37	34	31	28
6	65	53	44	38	61	50	42	37	44	38	34	39	34	30	34	30	27	24
7	60	48	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17473	17473	17473
5°	17586	17447	17370
10°	17445	17305	17211
15°	17261	17069	17006
20°	17054	16792	16759
25°	16816	16511	16460
30°	16461	16212	16105
35°	15993	15768	15674
40°	15494	15253	15193
45°	14892	14695	14630
50°	14274	14154	14059
55°	13608	13608	13393
60°	12778	13024	12562
65°	11693	12276	11402
70°	10308	11297	10037
75°	8803	10112	8565
80°	6826	8512	6914
85°	4418	6535	5829



TEST NUMBER: P564791

CATALOG NUMBER: SQ4-PW1-075U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.5	2.3
10°-20°	755.2	6.4
20°-30°	1120.3	9.6
30°-40°	1310.8	11.2
40°-50°	1305.0	11.1
50°-60°	1126.9	9.6
60°-70°	811.2	6.9
70°-80°	425.4	3.6
80°-90°	107.2	0.9
90°-100°	325.1	2.8
100°-110°	894.5	7.6
110°-120°	923.3	7.9
120°-130°	739.7	6.3
130°-140°	581.0	5.0
140°-150°	445.2	3.8
150°-160°	320.1	2.7
160°-170°	195.7	1.7
170°-180°	66.0	0.6
0°-30°	2143.0	18.3
0°-40°	3453.8	29.5
0°-60°	5885.6	50.2
0°-90°	7229.4	61.7
90°-120°	2142.9	18.3
90°-150°	3908.8	33.4
90°-180°	4491.0	38.3
0°-180°	11720.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2841	2841	2841	2841	2841	
5°	2848	2816	2826	2818	2813	270
15°	2711	2676	2681	2676	2671	764
25°	2478	2436	2433	2418	2425	1139
35°	2130	2101	2100	2080	2087	1332
45°	1712	1697	1689	1684	1682	1321
55°	1269	1266	1269	1251	1249	1132
65°	803	828	844	810	783	796
75°	370	405	426	397	360	397
85°	63	82	93	88	83	83
90°	2	6	10	13	13	5
95°	48	178	575	246	157	51
105°	160	246	986	1501	1401	169
115°	283	345	790	1574	1786	279
125°	390	445	717	1213	1421	348
135°	471	522	697	981	1110	363
145°	544	581	686	836	900	341
155°	616	636	682	751	773	283
165°	666	674	685	713	717	188
175°	689	691	686	695	694	65
180°	689	689	689	689	689	

TEST NUMBER: P564791

CATALOG NUMBER: SQ4-PW1-075U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2840.8	2840.8	2840.8	2840.8	2840.8
2.5°	2856.8	2833.3	2840.8	2834.4	2820.7
5°	2848.3	2816.5	2825.7	2818.1	2813.2
7.5°	2819.2	2789.9	2796.7	2788.6	2785.7
10°	2793.2	2763.8	2770.7	2760.6	2755.7
12.5°	2763.2	2731.8	2738.6	2728.6	2725.6
15°	2710.6	2676.3	2680.6	2675.5	2670.6
17.5°	2649.5	2614.8	2615.5	2607.5	2606.5
20°	2605.5	2568.8	2565.4	2555.5	2560.4
22.5°	2557.4	2518.8	2515.4	2501.5	2508.4
25°	2477.8	2436.2	2432.8	2417.9	2425.3
27.5°	2385.7	2344.6	2344.7	2323.8	2331.7
30°	2317.7	2278.5	2282.6	2257.8	2267.6
32.5°	2245.6	2210.3	2212.5	2187.7	2197.5
35°	2129.9	2100.6	2099.9	2080.1	2087.4
37.5°	2011.8	1985.9	1981.8	1970.3	1972.3
40°	1929.7	1907.7	1899.7	1892.2	1892.2
42.5°	1843.6	1823.5	1815.6	1810.0	1808.1
45°	1712.0	1697.3	1689.4	1684.4	1681.9
47.5°	1581.8	1568.1	1561.3	1557.7	1555.3
50°	1491.7	1481.9	1479.2	1471.6	1469.2
52.5°	1401.6	1395.7	1393.1	1383.5	1381.1
55°	1269.0	1266.5	1269.0	1251.4	1248.9
57.5°	1130.8	1134.7	1142.8	1119.1	1113.3
60°	1038.7	1048.5	1058.7	1031.0	1021.2
62.5°	944.6	960.2	974.6	942.8	929.1
65°	803.4	827.9	843.5	810.3	783.4
67.5°	667.3	697.6	716.3	680.6	650.2
70°	573.2	607.4	628.2	592.4	558.1
72.5°	491.1	529.2	546.1	512.3	478.0
75°	370.4	404.7	425.5	397.1	360.4
77.5°	262.8	295.1	312.4	287.6	257.3
80°	192.7	227.0	240.3	219.7	195.2
82.5°	136.7	165.0	174.2	161.8	145.2
85°	62.6	82.1	92.6	87.5	82.6
87.5°	16.3	30.9	40.1	40.7	42.7
90°	1.5	5.8	10.3	13.2	13.2
92.5°	20.2	86.5	149.9	57.6	47.2
95°	48.4	177.5	574.9	245.8	156.9
97.5°	78.9	196.8	877.3	676.0	477.0
100°	101.2	208.8	972.4	981.5	800.8
102.5°	122.3	223.0	997.0	1217.7	1051.9
105°	159.9	245.9	985.6	1501.0	1400.6
107.5°	195.7	274.2	929.6	1639.8	1669.6
110°	221.5	293.2	887.3	1674.3	1777.6

TEST NUMBER: P564791

CATALOG NUMBER: SQ4-PW1-075U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	244.9	314.3	845.1	1652.1	1809.3
115°	283.1	344.7	790.5	1574.1	1786.4
117.5°	319.4	376.2	755.9	1464.8	1704.8
120°	341.7	396.2	740.7	1382.8	1630.9
122.5°	361.7	416.2	730.1	1311.0	1546.4
125°	390.1	444.6	717.2	1213.2	1421.2
127.5°	417.1	469.0	708.7	1131.7	1314.1
130°	431.2	484.3	704.0	1083.2	1249.6
132.5°	447.6	500.7	700.5	1040.6	1190.9
135°	470.8	522.4	696.7	981.2	1110.3
137.5°	492.5	540.4	693.4	933.2	1039.6
140°	508.9	553.4	692.3	901.2	997.3
142.5°	523.0	564.0	689.9	872.8	955.1
145°	544.1	581.4	686.4	836.0	900.5
147.5°	566.7	598.8	684.6	803.4	855.1
150°	580.8	609.5	683.5	785.6	825.7
152.5°	593.7	620.1	682.3	770.2	803.4
155°	616.0	636.1	682.0	751.4	772.9
157.5°	632.1	648.5	682.0	736.0	750.9
160°	643.9	656.8	682.0	727.7	739.2
162.5°	653.2	663.9	683.2	720.6	729.8
165°	665.9	674.5	684.9	712.9	717.2
167.5°	674.7	681.3	686.4	706.4	707.5
170°	680.5	684.8	686.4	704.0	704.0
172.5°	685.2	687.2	686.4	700.4	699.3
175°	689.3	690.8	686.4	695.2	693.7
177.5°	690.5	690.5	685.8	692.8	690.5
180°	689.3	689.3	689.3	689.3	689.3

(END OF REPORT)