

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519684

Luminaire Tested: **SQ4-050U-0D-935-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519684
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-050U-0D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1730.7 lumens
Efficiency: N/A
Efficacy: 140.7 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 12.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519684
CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519684

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	1990	23458	6860
100°	2083	19972	16349
105°	2189	13550	19414
110°	2323	9220	18508
115°	2382	6643	15053
120°	2423	5253	11560
125°	2413	4428	8802
130°	2386	3890	6888
135°	2358	3492	5561
140°	2351	3202	4609
145°	2352	2976	3888
150°	2389	2806	3378
155°	2403	2672	3019
160°	2427	2577	2795
165°	2442	2516	2630
170°	2452	2475	2531
175°	2455	2447	2471



TEST NUMBER: P519684

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	127.2	7.4
100°-110°	345.7	20.0
110°-120°	355.4	20.5
120°-130°	284.2	16.4
130°-140°	223.3	12.9
140°-150°	171.2	9.9
150°-160°	123.1	7.1
160°-170°	75.3	4.4
170°-180°	25.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	828.3	47.9
90°-150°	1507.0	87.1
90°-180°	1731.0	100.0
0°-180°	1730.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	3	6	8	8	
95°	19	70	222	96	65	21
105°	61	96	380	579	545	65
115°	109	132	304	605	690	108
125°	150	171	275	464	547	134
135°	181	201	268	378	426	140
145°	209	224	264	321	345	131
155°	236	244	262	288	297	109
165°	256	259	263	274	275	72
175°	265	266	264	268	267	25
180°	265	265	265	265	265	



TEST NUMBER: P519684

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	0.9	3.4	6.0	7.7	7.7
92.5°	7.7	34.8	60.5	26.0	22.0
95°	18.8	69.6	221.6	96.4	64.8
97.5°	31.0	76.9	339.7	264.3	185.6
100°	39.2	81.7	375.9	381.0	307.7
102.5°	47.4	86.6	385.4	471.2	406.6
105°	61.4	95.5	380.1	578.8	544.6
107.5°	75.9	106.0	358.2	634.4	643.9
110°	86.1	113.6	341.8	645.3	686.1
112.5°	95.0	121.1	325.4	636.2	697.7
115°	109.1	132.4	304.3	605.4	689.5
117.5°	122.4	144.7	290.8	561.6	656.5
120°	131.3	152.9	284.7	532.3	626.5
122.5°	138.8	160.4	280.6	502.9	593.7
125°	150.0	170.8	275.3	463.9	547.2
127.5°	160.1	180.7	272.4	434.3	505.8
130°	166.2	186.2	271.0	415.7	479.9
132.5°	172.3	192.3	269.7	399.8	456.7
135°	180.7	200.7	267.6	377.8	426.2
137.5°	189.7	207.9	266.6	358.4	399.1
140°	195.2	212.7	265.9	346.0	382.7
142.5°	200.6	216.8	265.2	336.3	367.0
145°	208.8	223.8	264.2	321.0	345.2
147.5°	218.0	230.9	263.4	309.0	328.0
150°	224.2	235.0	263.4	302.1	317.1
152.5°	228.9	238.4	262.7	295.9	308.2
155°	236.1	244.4	262.5	288.3	296.6
157.5°	243.1	249.6	262.5	283.1	289.5
160°	247.2	253.0	262.5	279.7	284.7
162.5°	251.3	255.8	263.2	276.9	280.6
165°	255.7	259.0	263.4	274.5	275.3
167.5°	260.3	262.0	264.2	271.6	272.2
170°	261.7	263.3	264.2	270.2	270.2
172.5°	263.0	264.0	264.2	268.8	268.8
175°	265.1	265.9	264.2	267.6	266.8
177.5°	265.8	265.8	263.7	266.4	265.1
180°	265.1	265.1	265.1	265.1	265.1

(END OF REPORT)