

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519708

Luminaire Tested: **SQ4-075U-0D-935-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519708
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2601.3 lumens
Efficiency: N/A
Efficacy: 140.6 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 18.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519708
CATALOG NUMBER: SQ4-075U-0D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519708

CATALOG NUMBER: SQ4-075U-0D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2964	35251	9623
100°	3114	29929	24648
105°	3301	20351	28921
110°	3461	13865	27777
115°	3580	9996	22591
120°	3654	7916	17432
125°	3635	6682	13241
130°	3585	5853	10389
135°	3558	5265	8391
140°	3551	4830	6958
145°	3550	4478	5875
150°	3584	4218	5096
155°	3632	4022	4558
160°	3662	3879	4204
165°	3684	3790	3968
170°	3693	3725	3820
175°	3698	3682	3721



TEST NUMBER: P519708

CATALOG NUMBER: SQ4-075U-0D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	188.3	7.2
100°-110°	518.1	19.9
110°-120°	534.8	20.6
120°-130°	428.5	16.5
130°-140°	336.5	12.9
140°-150°	257.9	9.9
150°-160°	185.4	7.1
160°-170°	113.4	4.4
170°-180°	38.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1241.3	47.7
90°-150°	2264.2	87.0
90°-180°	2601.0	100.0
0°-180°	2601.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	3	6	8	8	
95°	28	103	333	142	91	31
105°	93	142	571	870	811	98
115°	164	200	458	912	1035	162
125°	226	258	415	703	823	202
135°	273	303	404	568	643	210
145°	315	337	398	484	522	198
155°	357	368	395	435	448	164
165°	386	391	397	413	415	109
175°	399	400	398	403	402	38
180°	399	399	399	399	399	



TEST NUMBER: P519708

CATALOG NUMBER: SQ4-075U-0D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	0.8	3.3	5.9	7.6	7.6
92.5°	11.7	50.1	86.8	33.3	27.4
95°	28.0	102.8	333.0	142.4	90.9
97.5°	45.7	114.0	508.2	391.6	276.3
100°	58.6	120.9	563.3	568.5	463.9
102.5°	70.9	129.2	577.5	705.3	609.3
105°	92.6	142.4	570.9	869.5	811.3
107.5°	113.3	158.9	538.5	949.9	967.2
110°	128.3	169.8	514.0	969.9	1029.7
112.5°	141.9	182.1	489.5	957.0	1048.0
115°	164.0	199.7	457.9	911.8	1034.8
117.5°	185.0	217.9	437.9	848.5	987.5
120°	198.0	229.5	429.0	801.0	944.7
122.5°	209.5	241.1	422.9	759.4	895.8
125°	226.0	257.6	415.4	702.8	823.2
127.5°	241.6	271.7	410.5	655.6	761.2
130°	249.8	280.5	407.8	627.5	723.8
132.5°	259.3	290.0	405.8	602.8	689.9
135°	272.7	302.6	403.5	568.4	643.1
137.5°	285.3	313.0	401.7	540.5	602.2
140°	294.8	320.6	401.0	522.1	577.7
142.5°	303.0	326.7	399.6	505.6	553.2
145°	315.2	336.8	397.6	484.3	521.6
147.5°	328.3	346.9	396.6	465.4	495.3
150°	336.4	353.0	395.9	455.1	478.3
152.5°	343.9	359.2	395.2	446.1	465.4
155°	356.8	368.5	395.1	435.3	447.7
157.5°	366.2	375.6	395.1	426.3	435.0
160°	373.0	380.4	395.1	421.5	428.2
162.5°	378.4	384.5	395.7	417.4	422.7
165°	385.7	390.7	396.8	412.9	415.4
167.5°	390.8	394.6	397.6	409.2	409.8
170°	394.2	396.7	397.6	407.8	407.8
172.5°	396.9	398.1	397.6	405.7	405.1
175°	399.3	400.1	397.6	402.7	401.8
177.5°	400.0	400.0	397.3	401.3	400.0
180°	399.3	399.3	399.3	399.3	399.3

(END OF REPORT)