

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519732

Luminaire Tested: **SQ4-100U-0D-935-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519732
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3489.7 lumens
Efficiency: N/A
Efficacy: 139.0 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 25.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519732
CATALOG NUMBER: SQ4-100U-0D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519732

CATALOG NUMBER: SQ4-100U-0D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	3917	48303	12915
100°	4203	40226	32920
105°	4410	27235	39148
110°	4683	18567	37183
115°	4840	13433	30243
120°	4884	10640	23342
125°	4893	8971	17818
130°	4836	7881	13926
135°	4777	7075	11246
140°	4761	6489	9335
145°	4781	6030	7889
150°	4833	5676	6848
155°	4873	5407	6132
160°	4919	5222	5653
165°	4950	5098	5336
170°	4967	5007	5137
175°	4974	4950	5006



TEST NUMBER: P519732

CATALOG NUMBER: SQ4-100U-0D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	251.5	7.2
100°-110°	694.4	19.9
110°-120°	716.1	20.5
120°-130°	575.5	16.5
130°-140°	452.3	13.0
140°-150°	346.9	9.9
150°-160°	249.3	7.1
160°-170°	152.5	4.4
170°-180°	51.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1662.0	47.6
90°-150°	3036.6	87.0
90°-180°	3490.0	100.0
0°-180°	3489.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	3	7	8	9	
95°	37	136	456	188	122	42
105°	124	191	764	1166	1098	132
115°	222	268	615	1218	1385	218
125°	304	346	558	944	1108	271
135°	366	406	542	764	862	283
145°	424	454	535	651	700	266
155°	479	495	531	584	602	221
165°	518	525	534	554	559	146
175°	537	538	534	542	540	51
180°	537	537	537	537	537	

TEST NUMBER: P519732

CATALOG NUMBER: SQ4-100U-OD-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.7	3.4	6.9	7.8	8.6
92.5°	15.5	64.2	114.8	41.9	32.7
95°	37.0	136.1	456.3	187.6	122.0
97.5°	61.2	152.4	676.0	520.4	376.9
100°	79.1	162.2	757.1	762.4	619.6
102.5°	96.2	173.4	772.9	942.0	806.6
105°	123.7	191.0	764.0	1166.3	1098.2
107.5°	153.0	212.8	721.3	1274.5	1299.3
110°	173.6	227.4	688.3	1297.7	1378.4
112.5°	192.2	243.9	657.4	1279.4	1398.3
115°	221.7	267.9	615.3	1218.1	1385.3
117.5°	247.5	293.5	587.6	1131.8	1322.0
120°	264.7	310.1	576.6	1073.4	1265.0
122.5°	281.2	324.5	567.7	1018.8	1200.3
125°	304.2	346.2	557.7	943.9	1107.7
127.5°	323.8	365.8	551.9	880.4	1021.8
130°	336.9	378.9	549.1	841.6	970.2
132.5°	349.2	389.2	546.4	809.1	925.5
135°	366.1	405.6	542.2	764.5	861.9
137.5°	385.0	421.0	540.2	727.0	810.2
140°	395.3	430.6	538.8	702.0	775.1
142.5°	407.0	439.6	537.4	679.8	744.2
145°	424.5	453.9	535.4	650.8	700.4
147.5°	441.4	467.1	533.5	626.3	664.8
150°	453.7	474.7	532.8	611.7	642.8
152.5°	463.4	483.0	532.1	599.2	624.9
155°	478.7	494.6	531.1	583.9	602.4
157.5°	492.8	505.0	531.2	572.8	585.4
160°	501.0	511.9	531.9	566.5	575.8
162.5°	507.9	517.5	532.6	561.0	568.2
165°	518.2	524.9	533.7	554.4	558.6
167.5°	526.1	530.1	534.5	550.4	551.7
170°	530.2	533.6	534.5	548.3	548.3
172.5°	533.7	535.7	534.5	545.5	544.8
175°	537.1	537.9	534.5	542.2	540.5
177.5°	538.5	537.8	534.3	539.1	537.8
180°	537.1	537.1	537.1	537.1	537.1

(END OF REPORT)