

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519756

Luminaire Tested: **SQ4-125U-0D-935-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519756
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4343.9 lumens
Efficiency: N/A
Efficacy: 137.0 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519756
CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519756

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5081	54623	19330
100°	5239	47957	41629
105°	5593	33430	46933
110°	5805	23239	44720
115°	6045	17048	37257
120°	6137	13428	29055
125°	6080	11279	22433
130°	6004	9892	17484
135°	5939	8892	14126
140°	5905	8156	11728
145°	5928	7579	9887
150°	6009	7123	8611
155°	6083	6789	7705
160°	6143	6556	7095
165°	6189	6395	6681
170°	6232	6280	6432
175°	6239	6208	6279



TEST NUMBER: P519756

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	314.8	7.2
100°-110°	847.9	19.5
110°-120°	889.9	20.5
120°-130°	722.1	16.6
130°-140°	566.3	13.0
140°-150°	434.8	10.0
150°-160°	312.6	7.2
160°-170°	191.0	4.4
170°-180°	64.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2052.6	47.3
90°-150°	3775.9	86.9
90°-180°	4344.0	100.0
0°-180°	4343.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	5	10	11	11	
95°	48	171	516	264	183	53
105°	157	244	938	1403	1317	165
115°	277	339	781	1509	1707	272
125°	378	434	701	1185	1395	338
135°	455	508	682	956	1083	351
145°	526	567	673	817	878	330
155°	598	619	667	733	757	275
165°	648	656	670	696	700	183
175°	674	673	670	680	678	64
180°	673	673	673	673	673	



TEST NUMBER: P519756

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.7	5.1	10.3	11.1	11.1
92.5°	20.9	73.9	146.1	70.3	48.9
95°	48.0	171.2	516.0	263.9	182.6
97.5°	76.6	196.0	809.3	676.1	509.9
100°	98.6	205.9	902.6	944.4	783.5
102.5°	119.8	219.7	933.5	1145.3	1013.2
105°	156.9	244.0	937.8	1403.0	1316.6
107.5°	191.8	269.6	897.8	1535.4	1557.7
110°	215.2	288.9	861.5	1576.5	1657.8
112.5°	239.8	308.2	826.5	1567.4	1701.0
115°	276.9	338.9	780.9	1508.8	1706.6
117.5°	310.6	368.8	745.6	1415.4	1635.7
120°	332.6	388.7	727.7	1348.3	1574.6
122.5°	351.8	407.3	714.7	1279.8	1505.4
125°	378.0	434.2	701.2	1185.1	1394.6
127.5°	403.2	458.5	692.6	1101.6	1288.7
130°	418.3	473.6	689.2	1053.8	1218.1
132.5°	433.4	488.0	685.7	1011.6	1162.5
135°	455.2	508.0	681.5	956.1	1082.6
137.5°	475.9	526.5	679.2	908.9	1012.8
140°	490.3	538.9	677.2	879.9	973.8
142.5°	505.4	550.7	675.8	852.8	931.9
145°	526.3	567.4	672.9	817.4	877.8
147.5°	548.9	584.6	670.0	787.6	835.1
150°	564.0	595.0	668.6	768.9	808.3
152.5°	577.7	604.7	667.9	753.7	785.7
155°	597.5	619.2	666.9	733.4	756.9
157.5°	614.8	631.7	667.1	719.2	734.9
160°	625.7	640.0	667.7	710.9	722.6
162.5°	635.3	646.9	668.4	703.9	712.3
165°	648.0	655.6	669.5	696.1	699.5
167.5°	658.3	662.7	670.3	690.1	691.4
170°	665.2	666.8	670.3	686.6	686.6
172.5°	669.3	669.6	671.0	683.2	683.2
175°	673.7	672.9	670.3	679.7	678.0
177.5°	675.6	674.3	670.8	676.3	674.9
180°	672.9	672.9	672.9	672.9	672.9

(END OF REPORT)