

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519337

Luminaire Tested: **SQ4-WB-0U-125D-835-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519337
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6157.4 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519337
CATALOG NUMBER: SQ4-WB-0U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519337

CATALOG NUMBER: SQ4-WB-OU-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25991	25991	25991
5°	25667	25575	25723
10°	24250	24469	25036
15°	22385	22905	23932
20°	20329	21093	22489
25°	18233	19227	20951
30°	16303	17369	19358
35°	14256	15286	17472
40°	11999	12952	15126
45°	9902	10757	12629
50°	8268	9013	10521
55°	7019	7735	8689
60°	5998	6706	6934
65°	4777	5640	4480
70°	4235	4401	2734
75°	3921	3569	1675
80°	3613	3284	1445
85°	3275	3006	1179



TEST NUMBER: P519337

CATALOG NUMBER: SQ4-WB-OU-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.6	6.3
10°-20°	1008.1	16.4
20°-30°	1305.8	21.2
30°-40°	1278.7	20.8
40°-50°	978.8	15.9
50°-60°	652.2	10.6
60°-70°	355.9	5.8
70°-80°	148.3	2.4
80°-90°	42.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2701.5	43.9
0°-40°	3980.2	64.6
0°-60°	5611.2	91.1
0°-90°	6157.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6157.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4226	4226	4226	4226	4226	
5°	4157	4115	4142	4152	4166	387
15°	3515	3503	3597	3695	3758	982
25°	2687	2694	2833	2957	3087	1236
35°	1899	1908	2036	2173	2327	1180
45°	1138	1160	1237	1330	1452	888
55°	654	682	721	749	810	593
65°	328	355	388	339	308	341
75°	165	165	150	103	70	176
85°	46	46	43	28	17	53
90°	0	0	0	0	0	



TEST NUMBER: P519337

CATALOG NUMBER: SQ4-WB-OU-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4225.6	4225.6	4225.6	4225.6	4225.6
2.5°	4236.0	4198.2	4207.8	4207.5	4195.9
5°	4157.0	4115.3	4142.1	4151.7	4166.2
7.5°	4002.7	3971.2	4020.1	4056.4	4085.8
10°	3882.6	3855.4	3917.8	3970.6	4008.6
12.5°	3743.1	3720.3	3797.6	3868.5	3918.2
15°	3515.4	3502.7	3597.0	3694.9	3758.3
17.5°	3271.8	3265.6	3373.8	3488.0	3569.2
20°	3105.7	3103.9	3222.5	3341.4	3435.7
22.5°	2938.1	2942.0	3066.7	3190.4	3297.8
25°	2686.6	2693.9	2833.1	2956.6	3087.1
27.5°	2454.1	2457.4	2601.3	2731.7	2870.9
30°	2295.4	2304.5	2445.6	2580.5	2725.6
32.5°	2136.7	2147.2	2285.4	2424.9	2572.8
35°	1898.6	1907.7	2035.8	2172.8	2326.9
37.5°	1653.1	1665.5	1779.2	1908.8	2060.3
40°	1494.4	1512.6	1613.1	1735.1	1883.8
42.5°	1341.7	1364.1	1457.3	1573.1	1707.3
45°	1138.4	1160.2	1236.7	1330.3	1451.8
47.5°	963.4	988.4	1047.2	1127.8	1231.5
50°	864.0	887.6	941.9	1001.6	1099.5
52.5°	776.5	800.1	848.5	894.5	977.9
55°	654.5	681.7	721.3	748.6	810.3
57.5°	554.4	580.5	611.9	624.2	661.6
60°	487.6	516.6	545.1	543.7	563.7
62.5°	426.8	451.5	479.8	460.2	461.3
65°	328.2	355.4	387.5	338.6	307.8
67.5°	265.1	270.9	304.1	236.1	199.5
70°	235.5	235.5	244.7	182.9	152.0
72.5°	207.3	207.3	198.8	148.7	116.4
75°	165.0	165.0	150.2	103.1	70.5
77.5°	127.2	125.7	115.0	76.9	51.2
80°	102.0	102.0	92.7	60.7	40.8
82.5°	79.7	79.7	71.9	47.4	30.4
85°	46.4	46.4	42.6	27.6	16.7
87.5°	16.3	16.3	14.8	8.9	7.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)