

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562810

Luminaire Tested: **SQ4-PC3-0U-050D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562810
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-050D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1710.0 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 16.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562810
CATALOG NUMBER: SQ4-PC3-0U-050D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562810

CATALOG NUMBER: SQ4-PC3-0U-050D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92		94	92	89		91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48		59	52	47		57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42		53	46	41		52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37		48	42	37		47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27		38	31	27		37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5780	5780	5780
5°	5825	5787	5765
10°	5810	5783	5766
15°	5780	5780	5774
20°	5742	5758	5758
25°	5688	5728	5711
30°	5618	5686	5661
35°	5535	5619	5580
40°	5443	5520	5464
45°	5344	5382	5299
50°	5205	5205	5121
55°	5040	4974	4900
60°	4796	4700	4624
65°	4432	4344	4305
70°	3882	3911	3898
75°	3123	3454	3476
80°	2221	2928	2959
85°	1355	2456	2456



TEST NUMBER: P562810

CATALOG NUMBER: SQ4-PC3-0U-050D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.3	3.5
10°-20°	170.2	10.0
20°-30°	257.7	15.1
30°-40°	308.9	18.1
40°-50°	315.0	18.4
50°-60°	275.0	16.1
60°-70°	196.9	11.5
70°-80°	101.4	5.9
80°-90°	25.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	487.1	28.5
0°-40°	796.1	46.6
0°-60°	1386.1	81.1
0°-90°	1710.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1710.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	626	626	626	626	626	
5°	629	623	625	623	622	60
15°	605	600	605	605	604	171
25°	559	555	563	561	561	257
35°	491	490	499	495	495	307
45°	410	408	412	407	406	315
55°	313	309	309	305	305	279
65°	203	198	199	197	197	201
75°	88	92	97	98	98	95
85°	13	20	23	24	23	18
90°	0	0	0	0	0	



TEST NUMBER: P562810

CATALOG NUMBER: SQ4-PC3-0U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	626.5	626.5	626.5	626.5	626.5
2.5°	630.3	624.8	626.5	625.1	622.8
5°	628.9	622.6	624.8	623.0	622.5
7.5°	624.3	618.1	621.0	619.8	619.2
10°	620.2	613.9	617.3	616.1	615.5
12.5°	614.6	608.8	612.6	611.5	611.3
15°	605.1	600.0	605.1	605.1	604.5
17.5°	593.1	588.5	593.9	594.3	593.9
20°	584.8	579.7	586.5	585.9	586.5
22.5°	574.6	570.4	577.7	576.2	576.8
25°	558.7	554.7	562.7	561.0	561.0
27.5°	539.9	537.0	545.8	543.9	543.9
30°	527.3	524.5	533.7	531.4	531.4
32.5°	513.4	511.5	520.3	517.5	517.5
35°	491.4	490.2	498.9	495.4	495.4
37.5°	468.6	467.6	475.5	471.3	469.9
40°	451.9	451.4	458.3	453.7	453.7
42.5°	435.2	434.6	440.7	435.1	435.1
45°	409.6	408.4	412.5	407.2	406.1
47.5°	381.6	380.5	383.0	377.3	376.7
50°	362.6	361.4	362.6	357.3	356.8
52.5°	343.1	341.0	341.2	336.0	335.9
55°	313.3	309.3	309.2	304.6	304.6
57.5°	281.7	276.5	277.0	273.0	272.4
60°	259.9	254.2	254.7	251.2	250.6
62.5°	238.5	232.0	233.3	229.4	229.3
65°	203.0	198.5	199.0	197.2	197.2
67.5°	168.9	164.7	167.8	166.4	166.3
70°	143.9	141.0	145.0	145.0	144.5
72.5°	120.7	120.6	125.5	125.5	125.9
75°	87.6	91.6	96.9	97.5	97.5
77.5°	58.5	65.5	71.4	71.6	71.5
80°	41.8	49.7	55.1	56.3	55.7
82.5°	28.3	36.7	41.2	42.3	41.8
85°	12.8	19.6	23.2	23.8	23.2
87.5°	3.7	7.8	9.3	9.3	8.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)