

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936216

Luminaire Tested: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936216
REPORT IS A COMBINATION OF REPORTS P933453 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5163.0 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936216
CATALOG NUMBER: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P936216

CATALOG NUMBER: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	39	35	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1935	1935	1935
5°	1891	2237	2601
10°	1715	3261	4313
15°	1458	4260	5208
20°	1186	4937	5307
25°	990	5166	5200
30°	835	5199	5190
35°	738	5112	5324
40°	643	5000	5463
45°	583	4918	5484
50°	534	4844	5393
55°	512	4736	5154
60°	524	4528	4777
65°	545	4212	4258
70°	581	3673	3597
75°	644	2995	2807
80°	704	2077	1891
85°	624	1102	968

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5484 cd/sqm



TEST NUMBER: P936216

CATALOG NUMBER: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.0
10°-20°	239.1	4.6
20°-30°	418.3	8.1
30°-40°	538.5	10.4
40°-50°	601.5	11.6
50°-60°	576.1	11.2
60°-70°	456.5	8.8
70°-80°	268.5	5.2
80°-90°	75.7	1.5
90°-100°	145.5	2.8
100°-110°	382.5	7.4
110°-120°	396.6	7.7
120°-130°	318.1	6.2
130°-140°	249.6	4.8
140°-150°	191.6	3.7
150°-160°	138.0	2.7
160°-170°	84.4	1.6
170°-180°	28.5	0.6
<hr/>		
0°-30°	711.4	13.8
0°-40°	1249.9	24.2
0°-60°	2427.4	47.0
0°-90°	3228.2	62.5
90°-120°	924.6	17.9
90°-150°	1684.0	32.6
90°-180°	1935.0	37.5
0°-180°	5163.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	417	417	417	417	417	
5°	406	436	491	555	575	38
15°	304	562	947	1148	1184	85
25°	194	637	1128	1178	1179	90
35°	131	609	1062	1123	1167	82
45°	90	486	939	1076	1124	70
55°	64	308	797	926	951	59
65°	51	164	592	665	675	51
75°	38	101	325	357	358	39
85°	13	31	80	88	90	14
90°	2	6	15	8	8	3
95°	19	75	251	129	88	21
105°	69	104	423	642	599	73
115°	122	149	339	676	771	121
125°	170	191	308	521	614	151
135°	203	223	298	420	476	157
145°	235	250	295	359	387	147
155°	266	273	295	324	333	122
165°	287	291	295	306	310	81
175°	298	298	297	300	300	28
180°	298	298	298	298	298	



TEST NUMBER: P936216
 CATALOG NUMBER: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	417.1	417.1	417.1	417.1	417.1	417.1	417.1	417.1	417.1	417.1	417.1
2.5°	417.1	417.1	419.8	421.2	423.8	425.2	427.9	430.6	438.6	439.9	442.6
5°	406.4	411.8	429.2	435.9	454.7	480.2	490.9	508.3	544.6	555.3	562.0
7.5°	390.3	402.4	445.3	456.0	503.0	570.0	598.2	635.8	693.4	721.6	744.4
10°	364.8	390.3	466.8	492.3	568.7	670.6	723.0	775.3	862.4	901.3	916.1
12.5°	336.7	378.2	489.6	524.4	634.4	783.3	846.4	904.0	1003.3	1055.6	1063.6
15°	304.5	360.8	511.0	562.0	704.2	877.2	947.0	1018.0	1110.6	1148.1	1157.5
17.5°	276.3	347.4	531.2	584.8	757.8	961.7	1032.8	1091.8	1166.9	1192.4	1199.1
20°	241.4	325.9	544.6	614.3	814.2	1023.4	1091.8	1137.4	1188.4	1204.5	1207.2
22.5°	215.9	303.1	552.6	625.0	851.7	1061.0	1118.6	1154.9	1189.7	1195.1	1196.4
25°	194.5	277.6	551.3	637.1	883.9	1083.8	1128.0	1154.9	1175.0	1177.7	1177.7
27.5°	174.4	249.5	545.9	639.8	908.1	1089.1	1124.0	1142.8	1152.2	1157.5	1157.5
30°	156.9	222.7	532.5	634.4	918.8	1083.8	1111.9	1121.3	1130.7	1138.8	1142.8
32.5°	143.5	197.2	512.4	623.7	920.1	1070.3	1090.5	1095.8	1109.2	1128.0	1134.7
35°	131.4	171.7	489.6	608.9	912.1	1048.9	1062.3	1067.7	1094.5	1122.7	1132.0
37.5°	119.4	152.9	460.1	583.5	900.0	1023.4	1032.8	1042.2	1083.8	1117.3	1128.0
40°	107.3	136.8	425.2	555.3	881.2	992.6	1000.6	1015.4	1070.3	1109.2	1120.0
42.5°	97.9	123.4	387.6	525.8	857.1	957.7	969.8	991.2	1054.3	1095.8	1107.9
45°	89.9	110.0	347.4	485.5	826.2	921.5	938.9	968.4	1035.5	1075.7	1086.4
47.5°	81.8	100.6	305.8	444.0	792.7	885.3	908.1	941.6	1010.0	1048.9	1058.3
50°	75.1	91.2	264.2	399.7	756.5	846.4	873.2	908.1	977.8	1014.0	1026.1
52.5°	69.7	83.2	225.3	355.4	714.9	806.1	837.0	873.2	938.9	973.8	981.8
55°	64.4	76.5	191.8	308.5	672.0	763.2	796.7	831.6	896.0	925.5	930.9
57.5°	61.7	71.1	163.6	264.2	626.4	714.9	752.5	784.7	845.0	867.8	873.2
60°	57.7	67.1	142.2	226.7	576.8	669.3	701.5	733.7	784.7	803.4	807.5
62.5°	53.7	64.4	126.1	190.5	525.8	615.7	647.8	677.4	720.3	733.7	739.1
65°	51.0	61.7	114.0	163.6	473.5	559.3	591.5	617.0	651.9	665.3	668.0
67.5°	48.3	59.0	104.6	140.8	421.2	503.0	527.1	551.3	578.1	591.5	592.8
70°	44.3	56.3	96.6	124.7	367.5	438.6	458.7	484.2	505.7	512.4	516.4
72.5°	41.6	52.3	91.2	112.7	312.5	376.9	395.7	410.4	429.2	435.9	435.9
75°	37.6	46.9	85.8	100.6	256.2	308.5	324.6	339.3	354.1	356.8	352.8
77.5°	33.5	41.6	73.8	84.5	199.9	244.1	257.5	265.6	277.6	280.3	281.7
80°	28.2	36.2	57.7	65.7	144.9	179.7	189.1	195.8	206.6	206.6	209.2
82.5°	21.5	28.2	41.6	46.9	97.9	123.4	131.4	135.5	142.2	142.2	142.2
85°	13.4	17.4	26.8	30.8	59.0	75.1	80.5	81.8	87.2	88.5	88.5
87.5°	6.7	9.4	17.4	18.8	30.8	38.9	38.9	41.6	41.6	40.2	38.9
90°	2.0	3.6	5.2	5.6	8.8	13.1	15.2	13.5	10.1	7.6	7.6
92.5°	8.0	21.6	35.3	38.7	54.4	75.3	85.7	75.1	54.0	38.1	36.6
95°	19.2	44.1	69.1	75.3	133.7	211.6	250.6	223.6	169.7	129.2	124.6
97.5°	33.3	55.3	77.2	82.7	180.1	310.0	375.0	358.0	323.9	298.3	289.6
100°	44.1	64.0	83.9	88.9	197.0	341.1	413.2	414.5	417.0	418.9	408.5
102.5°	53.3	71.9	90.5	95.1	204.8	351.0	424.1	445.8	489.2	521.8	512.9
105°	68.9	84.7	100.5	104.4	210.6	352.1	422.9	471.6	569.0	642.0	637.2
107.5°	84.9	99.6	114.3	118.0	211.6	336.4	398.8	466.7	602.6	704.5	705.7
110°	95.8	109.0	122.3	125.6	210.0	322.5	378.8	454.7	606.6	720.5	725.5



TEST NUMBER: P936216

CATALOG NUMBER: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	106.4	119.0	131.6	134.8	210.1	310.4	360.6	438.3	593.7	710.3	718.0
115°	122.4	134.0	145.7	148.6	212.0	296.5	338.7	413.6	563.4	675.7	686.3
117.5°	138.2	148.8	159.4	162.1	216.0	287.8	323.7	391.3	526.4	627.8	639.6
120°	147.4	157.4	167.4	169.9	219.2	284.9	317.7	379.4	502.9	595.5	606.9
122.5°	156.4	166.5	176.6	179.1	223.8	283.3	313.1	368.7	479.9	563.3	574.6
125°	170.3	179.5	188.6	190.9	230.0	282.1	308.1	355.3	449.8	520.6	531.0
127.5°	181.5	190.7	200.0	202.3	236.2	281.3	303.9	344.5	425.6	486.4	495.2
130°	187.5	197.5	207.4	209.9	240.7	281.8	302.3	338.4	410.6	464.7	472.8
132.5°	193.7	203.7	213.6	216.1	244.4	282.1	300.9	333.2	397.8	446.3	453.6
135°	202.9	212.0	221.1	223.4	248.4	281.8	298.5	325.6	379.7	420.3	426.5
137.5°	212.3	221.3	230.3	232.6	254.4	283.5	298.1	321.0	366.7	401.0	406.1
140°	220.1	228.4	236.7	238.8	258.1	283.8	296.7	316.5	356.0	385.6	390.4
142.5°	226.2	233.8	241.5	243.4	261.2	284.9	296.7	314.1	348.8	374.8	378.9
145°	235.4	242.1	248.7	250.4	265.2	284.9	294.7	308.9	337.3	358.6	361.7
147.5°	244.6	251.1	257.6	259.2	271.0	286.8	294.7	305.9	328.2	344.9	347.5
150°	250.6	256.5	262.3	263.8	274.1	287.8	294.7	304.1	323.0	337.1	339.2
152.5°	256.8	261.2	265.7	266.8	276.1	288.5	294.7	302.7	318.8	330.9	332.5
155°	266.0	269.3	272.6	273.4	280.5	290.0	294.7	301.1	313.9	323.5	324.5
157.5°	272.8	276.0	279.2	280.0	284.9	291.4	294.7	299.7	309.6	317.1	317.8
160°	277.4	279.9	282.4	283.0	286.9	292.1	294.7	299.0	307.5	313.9	314.3
162.5°	282.0	283.9	285.7	286.2	289.0	292.8	294.7	298.3	305.5	310.9	311.3
165°	287.1	288.8	290.5	290.9	292.2	293.9	294.7	297.3	302.4	306.3	306.7
167.5°	291.7	292.5	293.3	293.5	294.6	296.0	296.7	298.4	301.8	304.3	304.5
170°	294.7	295.5	296.3	296.5	296.6	296.7	296.7	298.4	301.8	304.3	304.3
172.5°	296.3	296.5	296.7	296.7	296.7	296.7	296.7	298.0	300.7	302.7	302.5
175°	298.5	298.5	298.5	298.5	297.9	297.1	296.7	297.5	299.2	300.5	300.5
177.5°	298.5	298.5	298.5	298.5	298.0	297.4	297.1	297.8	299.1	300.1	299.9
180°	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5



TEST NUMBER: P936216

CATALOG NUMBER: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	417.1	417.1
2.5°	445.3	442.6
5°	572.7	575.4
7.5°	771.2	769.9
10°	959.0	971.1
12.5°	1095.8	1098.5
15°	1179.0	1184.4
17.5°	1211.2	1212.5
20°	1212.5	1209.8
22.5°	1197.8	1195.1
25°	1180.3	1179.0
27.5°	1164.2	1165.6
30°	1157.5	1161.6
32.5°	1157.5	1164.2
35°	1160.2	1166.9
37.5°	1158.9	1166.9
40°	1153.5	1162.9
42.5°	1138.8	1145.5
45°	1116.0	1124.0
47.5°	1086.4	1091.8
50°	1048.9	1054.3
52.5°	1001.9	1003.3
55°	945.6	951.0
57.5°	885.3	886.6
60°	818.2	822.2
62.5°	747.1	747.1
65°	672.0	674.7
67.5°	594.2	600.9
70°	515.1	516.4
72.5°	437.3	437.3
75°	356.8	358.1
77.5°	280.3	280.3
80°	207.9	209.2
82.5°	143.5	146.2
85°	89.9	89.9
87.5°	41.6	37.6
90°	7.6	7.6
92.5°	30.5	24.4
95°	106.3	87.9
97.5°	254.6	219.7
100°	366.9	325.3
102.5°	477.3	441.7
105°	618.1	598.9
107.5°	710.3	714.9
110°	745.4	765.4



TEST NUMBER: P936216

CATALOG NUMBER: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	748.6	779.2
115°	728.8	771.2
117.5°	686.7	733.8
120°	652.7	698.5
122.5°	619.7	664.8
125°	572.6	614.2
127.5°	530.2	565.3
130°	505.2	537.6
132.5°	482.6	511.6
135°	451.5	476.5
137.5°	426.6	447.1
140°	409.5	428.7
142.5°	395.4	411.8
145°	374.2	386.6
147.5°	357.8	368.2
150°	347.6	356.0
152.5°	338.8	345.1
155°	328.7	332.9
157.5°	320.8	323.7
160°	316.0	317.7
162.5°	312.9	314.5
165°	308.4	310.1
167.5°	305.2	305.9
170°	304.3	304.3
172.5°	301.9	301.3
175°	300.5	300.5
177.5°	299.2	298.5
180°	298.5	298.5



TEST NUMBER: P936216
 CATALOG NUMBER: SQ4-FB-025U-050D-835-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.36	5.40	5.20	6.26	7.34	17.54	18.58	18.38	19.44	20.52
	3H	5.08	6.02	5.93	6.89	7.99	19.40	20.33	20.24	21.20	22.31
	4H	5.39	6.27	6.25	7.15	8.26	20.05	20.93	20.91	21.81	22.93
	6H	5.65	6.47	6.52	7.35	8.48	20.49	21.31	21.36	22.19	23.32
	8H	5.72	6.50	6.60	7.40	8.53	20.61	21.39	21.50	22.30	23.43
	12H	5.75	6.49	6.63	7.39	8.54	20.69	21.43	21.58	22.33	23.48
4H	2H	11.60	12.49	12.47	13.36	14.48	17.84	18.72	18.70	19.60	20.71
	3H	13.18	13.93	14.06	14.84	15.97	19.90	20.64	20.78	21.55	22.68
	4H	13.29	13.96	14.18	14.87	16.03	20.67	21.35	21.57	22.26	23.41
	6H	13.31	13.90	14.21	14.83	15.98	21.22	21.81	22.13	22.74	23.90
	8H	13.29	13.84	14.20	14.76	15.94	21.39	21.94	22.30	22.87	24.04
	12H	13.26	13.75	14.18	14.69	15.87	21.49	21.99	22.42	22.93	24.11
8H	4H	14.75	15.30	15.66	16.22	17.39	20.75	21.30	21.66	22.22	23.40
	6H	15.00	15.45	15.93	16.42	17.59	21.39	21.84	22.32	22.81	23.98
	8H	15.02	15.42	15.96	16.38	17.57	21.61	22.02	22.56	22.97	24.16
	12H	15.00	15.35	15.94	16.30	17.54	21.76	22.12	22.71	23.07	24.31
12H	4H	14.90	15.40	15.83	16.34	17.52	20.71	21.21	21.64	22.15	23.33
	6H	15.26	15.66	16.20	16.62	17.81	21.37	21.78	22.32	22.74	23.92
	8H	15.34	15.69	16.29	16.64	17.88	21.61	21.97	22.56	22.92	24.16