

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563146

Luminaire Tested: **SQ4-PC3-150U-100D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563146
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8584.6 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563146
CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563146

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	80	74	69	79	73	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	17	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11321	11321	11321
5°	11405	11332	11290
10°	11378	11325	11293
15°	11319	11319	11307
20°	11244	11277	11277
25°	11138	11218	11184
30°	11002	11135	11087
35°	10838	11004	10927
40°	10659	10809	10700
45°	10466	10540	10377
50°	10192	10192	10029
55°	9868	9740	9595
60°	9392	9202	9056
65°	8680	8508	8433
70°	7602	7661	7631
75°	6117	6762	6805
80°	4346	5733	5797
85°	2646	4806	4806



TEST NUMBER: P563146

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.1	1.4
10°-20°	333.2	3.9
20°-30°	504.6	5.9
30°-40°	605.0	7.0
40°-50°	616.9	7.2
50°-60°	538.5	6.3
60°-70°	385.5	4.5
70°-80°	198.6	2.3
80°-90°	51.9	0.6
90°-100°	377.3	4.4
100°-110°	1020.1	11.9
110°-120°	1072.5	12.5
120°-130°	871.2	10.1
130°-140°	683.3	8.0
140°-150°	524.5	6.1
150°-160°	377.2	4.4
160°-170°	230.4	2.7
170°-180°	77.7	0.9
0°-30°	954.0	11.1
0°-40°	1559.0	18.2
0°-60°	2714.4	31.6
0°-90°	3350.4	39.0
90°-120°	2469.9	28.8
90°-150°	4548.9	53.0
90°-180°	5234.0	61.0
0°-180°	8584.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1227	1227	1227	1227	1227	
5°	1232	1219	1224	1220	1219	117
15°	1185	1175	1185	1185	1184	334
25°	1094	1086	1102	1099	1099	504
35°	962	960	977	970	970	602
45°	802	800	808	798	795	617
55°	614	606	606	596	596	547
65°	398	389	390	386	386	393
75°	172	179	190	191	191	185
85°	25	38	45	47	45	34
90°	2	5	11	12	11	5
95°	58	206	627	325	193	61
105°	190	293	1132	1669	1601	200
115°	334	408	938	1817	2051	330
125°	457	524	846	1428	1677	407
135°	548	613	823	1153	1305	423
145°	637	685	812	987	1062	399
155°	719	747	805	885	914	332
165°	783	791	808	840	844	221
175°	813	812	809	820	818	77
180°	812	812	812	812	812	

TEST NUMBER: P563146

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1227.0	1227.0	1227.0	1227.0	1227.0
2.5°	1234.3	1223.6	1227.0	1224.2	1219.7
5°	1231.5	1219.3	1223.6	1220.1	1219.0
7.5°	1222.7	1210.5	1216.1	1213.8	1212.7
10°	1214.5	1202.3	1208.8	1206.5	1205.4
12.5°	1203.6	1192.3	1199.7	1197.4	1197.2
15°	1185.0	1175.0	1185.0	1184.9	1183.8
17.5°	1161.5	1152.4	1163.1	1163.8	1163.1
20°	1145.2	1135.2	1148.6	1147.5	1148.6
22.5°	1125.2	1117.0	1131.3	1128.4	1129.5
25°	1094.1	1086.3	1102.0	1098.6	1098.6
27.5°	1057.3	1051.7	1068.8	1065.2	1065.2
30°	1032.7	1027.2	1045.2	1040.7	1040.7
32.5°	1005.4	1001.7	1018.9	1013.4	1013.4
35°	962.3	960.1	977.0	970.2	970.2
37.5°	917.7	915.7	931.1	922.9	920.2
40°	885.0	883.9	897.5	888.4	888.4
42.5°	852.3	851.2	863.0	852.1	852.1
45°	802.1	799.9	807.8	797.5	795.3
47.5°	747.3	745.1	750.1	738.9	737.8
50°	710.1	707.8	710.1	699.8	698.7
52.5°	671.9	667.9	668.3	658.0	657.8
55°	613.5	605.7	605.5	596.5	596.5
57.5°	551.7	541.5	542.4	534.6	533.5
60°	509.0	497.9	498.7	491.9	490.8
62.5°	467.2	454.3	456.9	449.2	449.0
65°	397.6	388.7	389.7	386.3	386.3
67.5°	330.8	322.6	328.6	325.8	325.6
70°	281.8	276.2	284.0	284.0	282.9
72.5°	236.3	236.1	245.9	245.9	246.5
75°	171.6	179.3	189.7	190.9	190.9
77.5°	114.5	128.3	139.7	140.2	140.0
80°	81.8	97.4	107.9	110.2	109.1
82.5°	55.4	71.9	80.7	82.9	81.8
85°	25.0	38.3	45.4	46.6	45.4
87.5°	7.6	16.3	20.4	20.6	18.6
90°	1.7	5.2	11.4	12.2	11.4
92.5°	24.8	90.4	178.4	77.5	56.1
95°	58.5	205.5	627.4	324.7	193.1
97.5°	94.0	235.7	978.0	809.4	594.4
100°	120.6	247.9	1087.1	1133.7	916.7
102.5°	145.1	264.9	1125.6	1379.7	1217.3
105°	189.6	293.0	1131.7	1669.3	1600.9
107.5°	230.9	325.2	1082.2	1850.0	1872.7
110°	263.0	348.5	1038.2	1898.5	1995.1



TEST NUMBER: P563146

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.7	371.7	997.6	1888.8	2051.0
115°	333.8	408.2	938.5	1816.9	2051.0
117.5°	375.1	444.8	899.6	1706.9	1972.3
120°	400.2	468.6	876.5	1628.1	1898.9
122.5°	424.0	491.0	862.5	1543.5	1816.4
125°	457.0	523.7	845.9	1427.5	1677.0
127.5°	487.4	552.9	836.1	1332.8	1552.2
130°	504.2	571.7	831.9	1274.2	1472.5
132.5°	521.7	588.5	827.7	1221.5	1404.0
135°	547.9	612.9	823.2	1152.6	1304.7
137.5°	574.3	635.7	819.3	1096.7	1220.6
140°	592.5	649.7	817.9	1060.8	1171.0
142.5°	610.0	663.8	815.2	1028.3	1124.9
145°	637.1	684.9	811.8	986.6	1061.8
147.5°	661.7	704.1	808.0	948.8	1006.5
150°	679.9	717.5	806.6	928.2	974.4
152.5°	696.7	729.5	805.9	909.2	947.1
155°	719.2	747.4	804.8	885.0	914.1
157.5°	742.6	762.3	805.0	868.2	887.3
160°	755.9	772.1	805.7	857.6	871.3
162.5°	766.4	779.9	806.4	849.1	859.4
165°	783.0	790.7	808.3	839.9	844.2
167.5°	794.4	799.7	808.5	832.0	834.0
170°	801.3	803.9	809.2	828.4	828.4
172.5°	806.9	807.4	809.2	824.2	823.5
175°	812.7	811.8	809.2	819.7	817.9
177.5°	814.6	812.6	809.0	816.0	813.9
180°	811.8	811.8	811.8	811.8	811.8

(END OF REPORT)