

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562680

Luminaire Tested: **SQ4-PC3-050U-125D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562680  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-050U-125D-835-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 13822.5 lumens  
Efficiency: N/A  
Efficacy: 120.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 114.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562680  
CATALOG NUMBER: SQ4-PC3-050U-125D-835-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P562680

CATALOG NUMBER: SQ4-PC3-050U-125D-835-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	28
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	25
8	57	44	36	30	54	42	35	30	39	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16626	16626	16626
5°	16752	16643	16582
10°	16711	16632	16586
15°	16623	16623	16607
20°	16514	16563	16563
25°	16358	16476	16425
30°	16159	16354	16283
35°	15918	16163	16049
40°	15655	15876	15716
45°	15370	15479	15240
50°	14968	14968	14729
55°	14494	14306	14091
60°	13793	13516	13301
65°	12749	12494	12385
70°	11163	11253	11208
75°	8981	9933	9992
80°	6384	8421	8512
85°	3885	7066	7066



TEST NUMBER: P562680

CATALOG NUMBER: SQ4-PC3-050U-125D-835-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	341.1	2.5
10°-20°	978.8	7.1
20°-30°	1482.3	10.7
30°-40°	1777.1	12.9
40°-50°	1812.0	13.1
50°-60°	1581.8	11.4
60°-70°	1132.4	8.2
70°-80°	583.3	4.2
80°-90°	149.8	1.1
90°-100°	292.9	2.1
100°-110°	795.7	5.8
110°-120°	818.1	5.9
120°-130°	654.1	4.7
130°-140°	513.9	3.7
140°-150°	394.1	2.9
150°-160°	283.4	2.1
160°-170°	173.3	1.3
170°-180°	58.4	0.4
0°-30°	2802.2	20.3
0°-40°	4579.4	33.1
0°-60°	7973.2	57.7
0°-90°	9838.7	71.2
90°-120°	1906.7	13.8
90°-150°	3468.7	25.1
90°-180°	3984.0	28.8
0°-180°	13822.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3604	3604	3604	3604	3604	
5°	3618	3582	3594	3584	3581	343
15°	3481	3451	3481	3481	3477	981
25°	3214	3191	3237	3227	3227	1479
35°	2827	2820	2870	2850	2850	1768
45°	2356	2350	2373	2342	2336	1814
55°	1802	1779	1779	1752	1752	1606
65°	1168	1142	1145	1135	1135	1155
75°	504	527	557	561	561	545
85°	73	113	134	137	134	100
90°	2	8	14	18	18	6
95°	43	160	510	222	149	46
105°	141	220	875	1332	1254	150
115°	251	305	700	1393	1587	248
125°	345	393	634	1068	1260	308
135°	416	462	616	870	981	322
145°	481	515	608	739	795	302
155°	543	563	604	664	683	251
165°	589	596	606	632	634	166
175°	610	612	608	616	614	58
180°	610	610	610	610	610	



TEST NUMBER: P562680

CATALOG NUMBER: SQ4-PC3-050U-125D-835-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3604.1	3604.1	3604.1	3604.1	3604.1
2.5°	3625.5	3594.2	3604.1	3595.8	3582.8
5°	3617.5	3581.6	3594.1	3584.0	3580.8
7.5°	3591.4	3555.6	3572.1	3565.3	3562.1
10°	3567.4	3531.5	3550.7	3544.0	3540.7
12.5°	3535.4	3502.1	3524.0	3517.3	3516.7
15°	3480.7	3451.3	3480.7	3480.6	3477.3
17.5°	3411.9	3385.2	3416.6	3418.5	3416.6
20°	3363.9	3334.5	3373.9	3370.6	3373.9
22.5°	3305.1	3281.0	3323.1	3314.5	3317.8
25°	3213.7	3190.8	3237.0	3227.0	3227.0
27.5°	3105.6	3089.2	3139.6	3128.9	3128.9
30°	3033.5	3017.2	3070.2	3056.8	3056.8
32.5°	2953.4	2942.3	2992.8	2976.7	2976.7
35°	2826.6	2820.0	2870.0	2849.9	2849.9
37.5°	2695.8	2689.9	2735.1	2710.9	2703.1
40°	2599.6	2596.4	2636.4	2609.7	2609.7
42.5°	2503.5	2500.3	2534.9	2502.9	2502.9
45°	2356.0	2349.5	2372.7	2342.5	2336.0
47.5°	2195.2	2188.7	2203.2	2170.4	2167.1
50°	2085.7	2079.2	2085.7	2055.6	2052.4
52.5°	1973.6	1961.8	1962.9	1932.9	1932.2
55°	1802.1	1779.2	1778.7	1752.0	1752.0
57.5°	1620.5	1590.5	1593.2	1570.4	1567.1
60°	1495.0	1462.4	1465.0	1444.9	1441.7
62.5°	1372.2	1334.4	1342.2	1319.5	1318.8
65°	1168.0	1141.9	1144.6	1134.6	1134.6
67.5°	971.8	947.6	965.1	957.1	956.4
70°	827.6	811.3	834.3	834.2	831.0
72.5°	694.1	693.5	722.2	722.2	724.2
75°	503.9	526.8	557.3	560.6	560.6
77.5°	336.4	376.8	410.5	411.8	411.1
80°	240.3	286.0	317.0	323.6	320.4
82.5°	162.9	211.1	236.9	243.5	240.3
85°	73.4	112.6	133.5	136.7	133.5
87.5°	21.8	46.4	56.1	56.8	51.6
90°	2.0	7.7	13.7	17.7	17.7
92.5°	17.7	80.2	139.3	59.8	50.6
95°	43.2	160.2	510.1	222.0	149.1
97.5°	71.4	176.9	782.0	608.4	427.3
100°	90.2	188.1	865.2	877.1	708.2
102.5°	109.1	199.2	887.2	1084.7	935.8
105°	141.3	219.9	875.0	1332.3	1253.6
107.5°	174.6	244.1	824.4	1460.1	1482.0
110°	198.2	261.5	786.7	1485.3	1579.3

TEST NUMBER: P562680

CATALOG NUMBER: SQ4-PC3-050U-125D-835-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	218.6	278.8	749.1	1464.4	1606.0
115°	251.1	304.8	700.4	1393.4	1587.2
117.5°	281.7	333.1	669.4	1292.7	1511.0
120°	302.1	352.0	655.3	1225.2	1442.0
122.5°	319.4	369.3	645.9	1157.6	1366.7
125°	345.3	393.3	633.7	1067.7	1259.5
127.5°	368.4	416.0	627.0	999.6	1164.2
130°	382.6	428.6	623.9	956.8	1104.5
132.5°	396.7	442.7	620.7	920.4	1051.2
135°	415.9	462.0	616.0	869.7	980.9
137.5°	436.7	478.5	613.7	824.9	918.6
140°	449.3	489.6	612.1	796.5	880.9
142.5°	461.8	499.0	610.5	774.2	844.8
145°	480.7	515.2	608.2	738.9	794.6
147.5°	501.9	531.4	606.2	711.2	754.9
150°	516.0	540.9	606.2	695.3	729.8
152.5°	527.0	548.8	604.7	681.0	709.4
155°	543.4	562.6	604.3	663.6	682.7
157.5°	559.5	574.5	604.3	651.7	666.3
160°	568.9	582.4	604.3	643.8	655.3
162.5°	578.4	588.7	605.8	637.4	645.9
165°	588.6	596.2	606.2	631.8	633.7
167.5°	599.2	603.0	608.2	625.1	626.6
170°	602.3	606.1	608.2	621.9	621.9
172.5°	605.4	607.7	608.2	618.8	618.8
175°	610.1	612.1	608.2	616.0	614.1
177.5°	611.7	611.7	607.0	613.2	610.1
180°	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)