

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563818

Luminaire Tested: **SQ4-PP3-150U-100D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563818
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8552.9 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563818
CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563818

CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	34	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	73	62	54	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	38	33	38	32	28	30	26	24	23	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	52	40	33	28	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11957	11957	11957
5°	12045	11971	11929
10°	12025	11939	11886
15°	11944	11879	11814
20°	11865	11799	11709
25°	11724	11644	11528
30°	11508	11447	11302
35°	11207	11130	10989
40°	10848	10779	10656
45°	10552	10477	10374
50°	10174	10108	10010
55°	9646	9519	9445
60°	8781	8531	8488
65°	7737	7414	7390
70°	6679	6404	6404
75°	5750	5668	5586
80°	5069	5127	5010
85°	3970	4330	4330



TEST NUMBER: P563818

CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	1.4
10°-20°	349.9	4.1
20°-30°	524.1	6.1
30°-40°	614.8	7.2
40°-50°	616.7	7.2
50°-60°	526.1	6.2
60°-70°	343.1	4.0
70°-80°	172.1	2.0
80°-90°	49.3	0.6
90°-100°	377.3	4.4
100°-110°	1020.1	11.9
110°-120°	1072.5	12.5
120°-130°	871.2	10.2
130°-140°	683.3	8.0
140°-150°	524.5	6.1
150°-160°	377.2	4.4
160°-170°	230.4	2.7
170°-180°	77.7	0.9
0°-30°	996.6	11.7
0°-40°	1611.4	18.8
0°-60°	2754.1	32.2
0°-90°	3318.7	38.8
90°-120°	2469.9	28.9
90°-150°	4548.9	53.2
90°-180°	5234.0	61.2
0°-180°	8552.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1296	1296	1296	1296	1296	
5°	1300	1288	1293	1288	1288	124
15°	1250	1238	1244	1239	1237	353
25°	1152	1138	1144	1134	1132	530
35°	995	985	988	977	976	622
45°	809	803	803	795	795	623
55°	600	598	592	588	587	533
65°	354	348	340	337	338	354
75°	161	161	159	158	157	175
85°	38	41	41	41	41	44
90°	2	5	11	12	11	5
95°	58	206	627	325	193	61
105°	190	293	1132	1669	1601	200
115°	334	408	938	1817	2051	330
125°	457	524	846	1428	1677	407
135°	548	613	823	1153	1305	423
145°	637	685	812	987	1062	399
155°	719	747	805	885	914	332
165°	783	791	808	840	844	221
175°	813	812	809	820	818	77
180°	812	812	812	812	812	

TEST NUMBER: P563818

CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1296.0	1296.0	1296.0	1296.0	1296.0
2.5°	1304.2	1293.5	1296.0	1294.0	1288.7
5°	1300.5	1288.3	1292.6	1288.0	1288.0
7.5°	1291.7	1278.3	1282.6	1278.0	1277.8
10°	1283.5	1270.2	1274.4	1269.8	1268.7
12.5°	1271.7	1258.3	1263.5	1258.0	1257.8
15°	1250.5	1238.3	1243.7	1239.1	1236.9
17.5°	1226.7	1213.4	1219.9	1213.5	1212.6
20°	1208.5	1195.2	1201.7	1192.6	1192.6
22.5°	1186.7	1173.4	1180.8	1169.0	1169.0
25°	1151.7	1138.4	1143.8	1133.5	1132.4
27.5°	1110.2	1097.1	1102.7	1091.1	1090.9
30°	1080.2	1068.0	1074.5	1062.0	1060.9
32.5°	1047.5	1036.1	1040.9	1028.4	1027.2
35°	995.0	985.0	988.2	976.8	975.7
37.5°	939.8	929.6	933.2	923.4	923.0
40°	900.7	894.1	895.0	887.0	884.8
42.5°	864.4	856.8	857.8	849.8	849.4
45°	808.7	803.2	803.0	795.1	795.1
47.5°	749.6	745.4	744.2	737.6	737.4
50°	708.8	705.4	704.2	698.5	697.4
52.5°	666.1	664.5	660.6	655.8	655.6
55°	599.7	597.5	591.8	588.3	587.2
57.5°	527.7	523.3	516.8	511.8	512.7
60°	475.9	471.5	462.3	460.0	460.0
62.5°	425.9	420.6	411.4	408.3	410.0
65°	354.4	347.7	339.6	337.4	338.5
67.5°	289.4	283.4	274.6	274.6	273.7
70°	247.6	244.3	237.4	237.4	237.4
72.5°	210.4	208.8	203.8	203.7	202.9
75°	161.3	161.3	159.0	157.9	156.7
77.5°	120.9	121.3	120.2	119.0	117.0
80°	95.4	97.6	96.5	95.4	94.3
82.5°	71.8	74.0	73.8	71.8	71.6
85°	37.5	40.8	40.9	40.9	40.9
87.5°	10.3	14.6	16.8	17.0	17.7
90°	1.7	5.2	11.4	12.2	11.4
92.5°	24.8	90.4	178.4	77.5	56.1
95°	58.5	205.5	627.4	324.7	193.1
97.5°	94.0	235.7	978.0	809.4	594.4
100°	120.6	247.9	1087.1	1133.7	916.7
102.5°	145.1	264.9	1125.6	1379.7	1217.3
105°	189.6	293.0	1131.7	1669.3	1600.9
107.5°	230.9	325.2	1082.2	1850.0	1872.7
110°	263.0	348.5	1038.2	1898.5	1995.1



TEST NUMBER: P563818

CATALOG NUMBER: SQ4-PP3-150U-100D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.7	371.7	997.6	1888.8	2051.0
115°	333.8	408.2	938.5	1816.9	2051.0
117.5°	375.1	444.8	899.6	1706.9	1972.3
120°	400.2	468.6	876.5	1628.1	1898.9
122.5°	424.0	491.0	862.5	1543.5	1816.4
125°	457.0	523.7	845.9	1427.5	1677.0
127.5°	487.4	552.9	836.1	1332.8	1552.2
130°	504.2	571.7	831.9	1274.2	1472.5
132.5°	521.7	588.5	827.7	1221.5	1404.0
135°	547.9	612.9	823.2	1152.6	1304.7
137.5°	574.3	635.7	819.3	1096.7	1220.6
140°	592.5	649.7	817.9	1060.8	1171.0
142.5°	610.0	663.8	815.2	1028.3	1124.9
145°	637.1	684.9	811.8	986.6	1061.8
147.5°	661.7	704.1	808.0	948.8	1006.5
150°	679.9	717.5	806.6	928.2	974.4
152.5°	696.7	729.5	805.9	909.2	947.1
155°	719.2	747.4	804.8	885.0	914.1
157.5°	742.6	762.3	805.0	868.2	887.3
160°	755.9	772.1	805.7	857.6	871.3
162.5°	766.4	779.9	806.4	849.1	859.4
165°	783.0	790.7	808.3	839.9	844.2
167.5°	794.4	799.7	808.5	832.0	834.0
170°	801.3	803.9	809.2	828.4	828.4
172.5°	806.9	807.4	809.2	824.2	823.5
175°	812.7	811.8	809.2	819.7	817.9
177.5°	814.6	812.6	809.0	816.0	813.9
180°	811.8	811.8	811.8	811.8	811.8

(END OF REPORT)