

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563914

Luminaire Tested: **SQ4-PR1-025U-100D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563914
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4137.3 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 38.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563914
CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563914

CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80				
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68				
2	96	88	82	77	92	85	79	74	78	74	70	72	68	65	66	63	61	58				
3	88	78	71	65	84	75	68	63	69	64	59	64	59	56	59	55	52	49				
4	81	70	61	55	77	67	60	54	62	56	51	57	52	48	53	49	45	43				
5	74	62	54	48	71	60	52	47	56	49	44	52	46	42	48	43	40	37				
6	69	56	48	42	66	54	47	41	50	44	39	47	41	37	44	39	35	33				
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	31	29				
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	37	32	28	26				
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24				
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	31	27	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12169	12169	12169
5°	12279	12184	12121
10°	12240	12155	12091
15°	12186	12111	12046
20°	12125	12047	11958
25°	12040	11958	11820
30°	11910	11825	11656
35°	11734	11631	11465
40°	11466	11343	11138
45°	10999	10806	10584
50°	10175	9931	9736
55°	8881	8680	8498
60°	7484	7422	7274
65°	6473	6499	6449
70°	5945	5975	5975
75°	5711	5711	5750
80°	5372	5430	5372
85°	4330	4806	4806



TEST NUMBER: P563914

CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	3.0
10°-20°	356.9	8.6
20°-30°	538.3	13.0
30°-40°	641.4	15.5
40°-50°	632.3	15.3
50°-60°	483.2	11.7
60°-70°	299.1	7.2
70°-80°	169.9	4.1
80°-90°	52.4	1.3
90°-100°	63.1	1.5
100°-110°	165.9	4.0
110°-120°	172.0	4.2
120°-130°	138.0	3.3
130°-140°	108.3	2.6
140°-150°	83.1	2.0
150°-160°	59.9	1.4
160°-170°	36.6	0.9
170°-180°	12.4	0.3
0°-30°	1019.9	24.7
0°-40°	1661.2	40.2
0°-60°	2776.8	67.1
0°-90°	3298.1	79.7
90°-120°	401.1	9.7
90°-150°	730.4	17.7
90°-180°	839.0	20.3
0°-180°	4137.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1326	1311	1316	1311	1309	126
15°	1276	1262	1268	1263	1261	360
25°	1183	1168	1175	1162	1161	544
35°	1042	1030	1033	1019	1018	650
45°	843	832	828	813	811	646
55°	552	543	540	530	528	495
65°	296	294	298	295	295	300
75°	160	160	160	161	161	169
85°	41	43	45	45	45	48
90°	1	2	7	3	3	2
95°	8	33	109	56	38	9
105°	30	45	183	278	260	32
115°	53	64	147	293	334	52
125°	74	83	134	226	266	66
135°	88	97	130	182	207	68
145°	102	109	128	156	168	64
155°	115	119	128	140	144	53
165°	124	126	128	133	134	35
175°	130	130	129	130	130	12
180°	130	130	130	130	130	

TEST NUMBER: P563914

CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.0	1319.0	1319.0	1319.0	1319.0
2.5°	1327.2	1315.6	1319.0	1316.1	1309.9
5°	1325.8	1311.4	1315.6	1311.0	1308.8
7.5°	1315.6	1301.4	1305.6	1301.0	1299.7
10°	1306.5	1293.2	1297.4	1292.8	1290.6
12.5°	1296.5	1282.3	1287.4	1281.9	1279.7
15°	1275.8	1262.5	1267.9	1263.3	1261.1
17.5°	1253.1	1238.9	1244.3	1239.0	1236.1
20°	1234.9	1221.6	1227.0	1219.0	1217.9
22.5°	1214.9	1201.6	1207.0	1196.3	1196.1
25°	1182.7	1168.2	1174.7	1162.2	1161.1
27.5°	1144.3	1130.9	1136.3	1123.6	1122.2
30°	1117.9	1104.6	1110.0	1096.3	1094.1
32.5°	1087.9	1075.5	1080.0	1066.3	1065.0
35°	1041.8	1029.6	1032.7	1019.1	1017.9
37.5°	989.3	978.2	980.0	965.0	963.9
40°	952.0	940.9	941.8	925.9	924.8
42.5°	911.2	900.0	899.1	883.2	882.1
45°	843.0	831.9	828.2	813.4	811.2
47.5°	765.3	754.2	747.3	735.2	733.7
50°	708.9	697.8	691.9	681.6	678.3
52.5°	648.0	636.9	631.9	622.5	619.2
55°	552.1	543.3	539.6	530.5	528.3
57.5°	461.0	455.0	454.0	445.1	444.2
60°	405.6	402.3	402.2	394.2	394.2
62.5°	358.3	355.9	357.6	352.4	351.5
65°	296.5	294.3	297.7	295.4	295.4
67.5°	247.7	247.7	249.7	248.8	248.8
70°	220.4	220.4	221.5	221.5	221.5
72.5°	195.9	195.0	197.9	197.9	197.0
75°	160.2	160.2	160.2	161.3	161.3
77.5°	124.7	125.0	125.9	125.6	124.7
80°	101.1	102.2	102.2	101.1	101.1
82.5°	77.5	78.6	78.6	78.4	77.5
85°	40.9	43.1	45.4	45.4	45.4
87.5°	12.0	15.9	19.5	18.8	17.9
90°	0.8	2.5	6.6	3.3	3.3
92.5°	3.5	16.8	37.2	16.5	10.6
95°	8.3	32.6	108.7	56.0	38.2
97.5°	14.4	35.9	162.7	129.4	95.3
100°	19.1	38.6	179.3	181.7	141.1
102.5°	23.1	41.3	183.9	226.3	191.6
105°	29.9	45.3	183.4	278.5	259.8
107.5°	36.9	51.1	173.0	305.6	310.1
110°	41.5	54.5	164.3	312.5	332.0

TEST NUMBER: P563914

CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	46.2	58.5	156.4	308.1	338.0
115°	53.1	64.5	146.9	293.1	334.5
117.5°	59.9	70.3	140.4	272.3	318.2
120°	63.9	73.7	137.8	258.3	303.0
122.5°	67.9	77.6	135.8	244.4	288.4
125°	73.9	82.8	133.6	225.9	266.4
127.5°	78.7	87.8	131.8	210.9	245.2
130°	81.3	91.1	131.1	201.6	233.2
132.5°	84.0	93.7	130.5	193.5	222.0
135°	88.0	96.9	129.5	182.3	206.7
137.5°	92.1	100.9	129.3	173.9	193.9
140°	95.5	103.6	128.7	167.3	185.9
142.5°	98.1	105.6	128.7	162.6	178.6
145°	102.1	108.6	127.8	155.5	167.7
147.5°	106.1	112.4	127.8	149.6	159.7
150°	108.7	114.4	127.8	146.3	154.4
152.5°	111.4	115.8	127.8	143.6	149.7
155°	115.4	118.6	127.8	140.4	144.4
157.5°	118.4	121.4	127.8	137.5	140.4
160°	120.4	122.8	127.8	136.2	137.8
162.5°	122.3	124.1	127.8	134.8	136.5
165°	124.5	126.1	127.8	132.8	134.5
167.5°	126.5	127.3	128.7	132.0	132.6
170°	127.8	128.6	128.7	132.0	132.0
172.5°	128.5	128.7	128.7	131.3	130.6
175°	129.5	129.5	128.7	130.3	130.3
177.5°	129.5	129.5	128.8	130.1	129.5
180°	129.5	129.5	129.5	129.5	129.5

(END OF REPORT)