

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562824

Luminaire Tested: **SQ4-PC3-0U-075D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562824
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5801.1 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562824
CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562824

CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9806	9806	9806
5°	9879	9816	9779
10°	9855	9809	9782
15°	9804	9804	9794
20°	9739	9768	9768
25°	9647	9717	9687
30°	9530	9645	9603
35°	9388	9532	9466
40°	9233	9363	9268
45°	9065	9129	8988
50°	8828	8828	8687
55°	8548	8437	8311
60°	8135	7971	7844
65°	7519	7369	7305
70°	6583	6636	6610
75°	5297	5859	5893
80°	3764	4968	5018
85°	2292	4166	4166



TEST NUMBER: P562824

CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.2	3.5
10°-20°	577.3	10.0
20°-30°	874.2	15.1
30°-40°	1048.1	18.1
40°-50°	1068.7	18.4
50°-60°	932.9	16.1
60°-70°	667.9	11.5
70°-80°	344.0	5.9
80°-90°	87.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1652.7	28.5
0°-40°	2700.7	46.6
0°-60°	4702.3	81.1
0°-90°	5801.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5801.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2126	2126	2126	2126	2126	
5°	2133	2112	2120	2114	2112	203
15°	2053	2035	2053	2053	2051	579
25°	1895	1882	1909	1903	1903	872
35°	1667	1663	1693	1681	1681	1043
45°	1390	1386	1399	1382	1378	1070
55°	1063	1049	1049	1033	1033	947
65°	689	673	675	669	669	681
75°	297	311	329	331	331	321
85°	43	66	79	81	79	61
90°	0	0	0	0	0	



TEST NUMBER: P562824

CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2125.6	2125.6	2125.6	2125.6	2125.6
2.5°	2138.2	2119.7	2125.6	2120.7	2113.0
5°	2133.4	2112.3	2119.7	2113.7	2111.8
7.5°	2118.1	2096.9	2106.7	2102.7	2100.8
10°	2103.9	2082.8	2094.1	2090.1	2088.2
12.5°	2085.0	2065.4	2078.3	2074.4	2074.0
15°	2052.8	2035.4	2052.8	2052.7	2050.8
17.5°	2012.2	1996.4	2015.0	2016.1	2015.0
20°	1983.9	1966.5	1989.8	1987.8	1989.8
22.5°	1949.2	1935.0	1959.9	1954.8	1956.7
25°	1895.3	1881.8	1909.1	1903.2	1903.2
27.5°	1831.5	1821.9	1851.6	1845.3	1845.3
30°	1789.0	1779.4	1810.7	1802.8	1802.8
32.5°	1741.8	1735.2	1765.0	1755.6	1755.6
35°	1667.0	1663.2	1692.6	1680.8	1680.8
37.5°	1589.9	1586.4	1613.1	1598.8	1594.2
40°	1533.2	1531.2	1554.8	1539.1	1539.1
42.5°	1476.5	1474.6	1495.0	1476.1	1476.1
45°	1389.5	1385.6	1399.3	1381.5	1377.7
47.5°	1294.6	1290.8	1299.4	1280.0	1278.1
50°	1230.1	1226.2	1230.1	1212.3	1210.4
52.5°	1163.9	1157.0	1157.7	1139.9	1139.5
55°	1062.8	1049.3	1049.0	1033.3	1033.3
57.5°	955.7	938.0	939.6	926.2	924.2
60°	881.7	862.5	864.0	852.2	850.2
62.5°	809.3	787.0	791.6	778.2	777.8
65°	688.8	673.4	675.1	669.2	669.2
67.5°	573.1	558.9	569.2	564.4	564.1
70°	488.1	478.5	492.0	492.0	490.1
72.5°	409.4	409.0	425.9	425.9	427.1
75°	297.2	310.7	328.7	330.6	330.6
77.5°	198.4	222.2	242.1	242.9	242.5
80°	141.7	168.6	187.0	190.9	188.9
82.5°	96.0	124.5	139.7	143.6	141.7
85°	43.3	66.4	78.7	80.6	78.7
87.5°	12.6	26.5	31.5	31.4	28.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)