

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564130

Luminaire Tested: **SQ4-PR1-075U-125D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564130
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6810.2 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564130
CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564130

CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	51	47	47	44	42	38
4	77	66	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	38	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20
9	53	40	33	28	49	38	31	27	34	29	24	31	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15530	15530	15530
5°	15669	15549	15468
10°	15620	15511	15430
15°	15551	15455	15371
20°	15473	15374	15260
25°	15365	15261	15084
30°	15198	15091	14874
35°	14974	14844	14631
40°	14632	14476	14213
45°	14037	13790	13507
50°	12986	12673	12423
55°	11334	11078	10845
60°	9551	9470	9283
65°	8261	8294	8230
70°	7588	7626	7626
75°	7286	7286	7340
80°	6854	6934	6854
85°	5526	6140	6140



TEST NUMBER: P564130

CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	2.3
10°-20°	455.4	6.7
20°-30°	686.9	10.1
30°-40°	818.5	12.0
40°-50°	806.9	11.8
50°-60°	616.7	9.1
60°-70°	381.6	5.6
70°-80°	216.8	3.2
80°-90°	66.9	1.0
90°-100°	188.3	2.8
100°-110°	518.1	7.6
110°-120°	534.8	7.9
120°-130°	428.5	6.3
130°-140°	336.5	4.9
140°-150°	257.9	3.8
150°-160°	185.4	2.7
160°-170°	113.4	1.7
170°-180°	38.2	0.6
0°-30°	1301.5	19.1
0°-40°	2119.9	31.1
0°-60°	3543.6	52.0
0°-90°	4208.9	61.8
90°-120°	1241.3	18.2
90°-150°	2264.2	33.2
90°-180°	2601.0	38.2
0°-180°	6810.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1683	1683	1683	1683	1683	
5°	1692	1674	1679	1673	1670	161
15°	1628	1611	1618	1612	1609	459
25°	1509	1491	1499	1483	1482	695
35°	1330	1314	1318	1300	1299	830
45°	1076	1062	1057	1038	1035	824
55°	705	693	689	677	674	631
65°	378	376	380	377	377	383
75°	204	204	204	206	206	216
85°	52	55	58	58	58	61
90°	1	3	6	8	8	4
95°	28	103	333	142	91	30
105°	93	142	571	870	811	98
115°	164	200	458	912	1035	162
125°	226	258	415	703	823	202
135°	273	303	404	568	643	210
145°	315	337	398	484	522	198
155°	357	368	395	435	448	164
165°	386	391	397	413	415	109
175°	399	400	398	403	402	38
180°	399	399	399	399	399	

TEST NUMBER: P564130

CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1683.2	1683.2	1683.2	1683.2	1683.2
2.5°	1693.7	1678.9	1683.2	1679.6	1671.6
5°	1691.9	1673.5	1678.9	1673.0	1670.2
7.5°	1678.9	1660.7	1666.1	1660.3	1658.6
10°	1667.3	1650.3	1655.7	1649.8	1647.0
12.5°	1654.5	1636.4	1642.9	1635.9	1633.1
15°	1628.1	1611.1	1618.0	1612.1	1609.3
17.5°	1599.1	1581.0	1587.8	1581.1	1577.4
20°	1575.9	1558.9	1565.8	1555.6	1554.2
22.5°	1550.4	1533.4	1540.3	1526.6	1526.4
25°	1509.3	1490.8	1499.1	1483.1	1481.7
27.5°	1460.3	1443.2	1450.1	1433.8	1432.1
30°	1426.6	1409.6	1416.5	1399.0	1396.2
32.5°	1388.3	1372.5	1378.2	1360.8	1359.1
35°	1329.5	1313.9	1317.9	1300.4	1299.0
37.5°	1262.5	1248.3	1250.6	1231.4	1230.0
40°	1214.9	1200.8	1201.9	1181.6	1180.1
42.5°	1162.7	1148.6	1147.4	1127.1	1125.6
45°	1075.8	1061.6	1056.9	1038.0	1035.2
47.5°	976.6	962.4	953.7	938.3	936.3
50°	904.7	890.5	882.9	869.8	865.5
52.5°	827.0	812.8	806.4	794.4	790.1
55°	704.6	693.3	688.7	677.0	674.2
57.5°	588.3	580.7	579.3	568.0	566.9
60°	517.6	513.3	513.2	503.1	503.1
62.5°	457.3	454.2	456.4	449.7	448.6
65°	378.4	375.6	379.9	377.0	377.0
67.5°	316.1	316.1	318.7	317.5	317.5
70°	281.3	281.3	282.7	282.7	282.7
72.5°	249.9	248.8	252.6	252.5	251.4
75°	204.4	204.4	204.4	205.9	205.9
77.5°	159.2	159.5	160.6	160.3	159.2
80°	129.0	130.5	130.5	129.0	129.0
82.5°	98.9	100.3	100.3	100.0	98.9
85°	52.2	55.0	58.0	58.0	58.0
87.5°	15.2	20.3	24.4	24.7	23.6
90°	0.8	3.3	5.9	7.6	7.6
92.5°	11.7	50.1	86.8	33.3	27.4
95°	28.0	102.8	333.0	142.4	90.9
97.5°	45.7	114.0	508.2	391.6	276.3
100°	58.6	120.9	563.3	568.5	463.9
102.5°	70.9	129.2	577.5	705.3	609.3
105°	92.6	142.4	570.9	869.5	811.3
107.5°	113.3	158.9	538.5	949.9	967.2
110°	128.3	169.8	514.0	969.9	1029.7



TEST NUMBER: P564130

CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.9	182.1	489.5	957.0	1048.0
115°	164.0	199.7	457.9	911.8	1034.8
117.5°	185.0	217.9	437.9	848.5	987.5
120°	198.0	229.5	429.0	801.0	944.7
122.5°	209.5	241.1	422.9	759.4	895.8
125°	226.0	257.6	415.4	702.8	823.2
127.5°	241.6	271.7	410.5	655.6	761.2
130°	249.8	280.5	407.8	627.5	723.8
132.5°	259.3	290.0	405.8	602.8	689.9
135°	272.7	302.6	403.5	568.4	643.1
137.5°	285.3	313.0	401.7	540.5	602.2
140°	294.8	320.6	401.0	522.1	577.7
142.5°	303.0	326.7	399.6	505.6	553.2
145°	315.2	336.8	397.6	484.3	521.6
147.5°	328.3	346.9	396.6	465.4	495.3
150°	336.4	353.0	395.9	455.1	478.3
152.5°	343.9	359.2	395.2	446.1	465.4
155°	356.8	368.5	395.1	435.3	447.7
157.5°	366.2	375.6	395.1	426.3	435.0
160°	373.0	380.4	395.1	421.5	428.2
162.5°	378.4	384.5	395.7	417.4	422.7
165°	385.7	390.7	396.8	412.9	415.4
167.5°	390.8	394.6	397.6	409.2	409.8
170°	394.2	396.7	397.6	407.8	407.8
172.5°	396.9	398.1	397.6	405.7	405.1
175°	399.3	400.1	397.6	402.7	401.8
177.5°	400.0	400.0	397.3	401.3	400.0
180°	399.3	399.3	399.3	399.3	399.3

(END OF REPORT)