

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563256

Luminaire Tested: **SQ4-PP3-025U-125D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563256
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-125D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11676.7 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 101.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563256
CATALOG NUMBER: SQ4-PP3-025U-125D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563256

CATALOG NUMBER: SQ4-PP3-025U-125D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	83
1	106	101	97	94	101	97	94	91	90	87	85	84	81	79	77	76	74	71
2	96	89	82	77	92	86	80	75	79	75	71	74	70	67	68	66	63	60
3	88	78	71	65	84	76	69	63	70	65	60	65	61	57	61	57	54	51
4	81	70	61	55	77	67	60	54	63	56	51	58	53	49	55	50	47	44
5	74	62	54	48	71	60	52	47	56	50	45	53	47	43	49	45	41	38
6	69	56	48	42	66	54	46	41	51	44	39	48	42	37	45	40	36	34
7	64	51	43	37	61	49	42	36	46	40	35	44	38	33	41	36	32	30
8	59	46	38	33	57	45	37	32	42	36	31	40	34	30	38	33	29	27
9	55	43	35	29	53	41	34	29	39	32	28	37	31	27	35	30	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17561	17561	17561
5°	17690	17582	17520
10°	17660	17535	17457
15°	17543	17448	17352
20°	17427	17329	17198
25°	17220	17101	16931
30°	16901	16812	16599
35°	16459	16346	16139
40°	15932	15832	15651
45°	15498	15389	15237
50°	14941	14845	14701
55°	14168	13980	13873
60°	12897	12528	12466
65°	11362	10889	10852
70°	9810	9405	9405
75°	8445	8325	8206
80°	7446	7534	7356
85°	5828	6357	6357



TEST NUMBER: P563256

CATALOG NUMBER: SQ4-PP3-025U-125D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.0	3.1
10°-20°	1027.8	8.8
20°-30°	1539.5	13.2
30°-40°	1805.8	15.5
40°-50°	1811.5	15.5
50°-60°	1545.3	13.2
60°-70°	1007.8	8.6
70°-80°	505.6	4.3
80°-90°	141.5	1.2
90°-100°	145.3	1.2
100°-110°	381.9	3.3
110°-120°	396.0	3.4
120°-130°	317.6	2.7
130°-140°	249.2	2.1
140°-150°	191.3	1.6
150°-160°	137.8	1.2
160°-170°	84.3	0.7
170°-180°	28.5	0.2
0°-30°	2927.3	25.1
0°-40°	4733.2	40.5
0°-60°	8089.9	69.3
0°-90°	9744.9	83.5
90°-120°	923.2	7.9
90°-150°	1681.3	14.4
90°-180°	1932.0	16.5
0°-180°	11676.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3807	3807	3807	3807	3807	
5°	3820	3784	3797	3783	3783	363
15°	3673	3638	3653	3640	3633	1036
25°	3383	3344	3360	3330	3326	1556
35°	2923	2893	2903	2869	2866	1826
45°	2376	2359	2359	2336	2336	1829
55°	1762	1755	1738	1728	1725	1566
65°	1041	1021	998	991	994	1039
75°	474	474	467	464	460	514
85°	110	120	120	120	120	129
90°	2	6	15	8	8	6
95°	19	75	250	129	88	21
105°	69	104	422	641	598	73
115°	122	148	338	675	770	121
125°	170	191	308	520	613	151
135°	202	223	298	420	476	157
145°	235	250	294	358	386	147
155°	266	273	294	323	332	122
165°	287	290	294	306	310	81
175°	298	298	296	300	300	28
180°	298	298	298	298	298	

TEST NUMBER: P563256

CATALOG NUMBER: SQ4-PP3-025U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3806.8	3806.8	3806.8	3806.8	3806.8
2.5°	3830.8	3799.5	3806.8	3801.1	3785.4
5°	3820.1	3784.3	3796.8	3783.4	3783.4
7.5°	3794.1	3755.0	3767.4	3754.1	3753.4
10°	3770.1	3730.9	3743.4	3730.0	3726.7
12.5°	3735.4	3696.2	3711.4	3695.3	3694.7
15°	3673.3	3637.5	3653.3	3639.8	3633.3
17.5°	3603.3	3564.1	3583.3	3564.5	3561.9
20°	3549.9	3510.7	3529.9	3503.2	3503.2
22.5°	3485.8	3446.7	3468.5	3433.8	3433.8
25°	3383.1	3343.9	3359.7	3329.6	3326.4
27.5°	3261.0	3222.5	3238.9	3204.9	3204.2
30°	3172.9	3137.0	3156.2	3119.4	3116.2
32.5°	3076.8	3043.5	3057.4	3020.7	3017.4
35°	2922.7	2893.3	2902.6	2869.2	2865.9
37.5°	2760.5	2730.5	2741.2	2712.4	2711.1
40°	2645.7	2626.2	2629.1	2605.6	2599.0
42.5°	2539.0	2516.8	2519.6	2496.2	2494.9
45°	2375.5	2359.2	2358.8	2335.5	2335.5
47.5°	2202.0	2189.6	2186.0	2166.6	2166.0
50°	2081.9	2072.1	2068.5	2051.8	2048.5
52.5°	1956.4	1951.9	1940.4	1926.4	1925.8
55°	1761.6	1755.1	1738.2	1728.2	1724.9
57.5°	1550.1	1537.0	1518.0	1503.4	1506.0
60°	1397.9	1384.9	1357.9	1351.2	1351.2
62.5°	1251.1	1235.5	1208.4	1199.2	1204.4
65°	1040.9	1021.4	997.6	991.0	994.2
67.5°	850.1	832.5	806.7	806.7	804.1
70°	727.3	717.5	697.3	697.3	697.3
72.5°	617.9	613.3	598.5	598.5	595.9
75°	473.8	473.8	467.1	463.7	460.4
77.5°	355.0	356.3	353.0	349.5	343.6
80°	280.3	286.8	283.6	280.2	276.9
82.5°	210.9	217.4	216.9	210.8	210.2
85°	110.1	119.9	120.1	120.1	120.1
87.5°	29.7	40.9	45.8	44.3	46.9
90°	1.9	5.6	15.3	7.6	7.6
92.5°	8.0	38.7	85.6	37.9	24.5
95°	19.1	75.1	250.3	129.0	87.9
97.5°	33.2	82.6	374.5	297.8	219.3
100°	43.9	88.8	412.7	418.2	324.8
102.5°	53.1	95.0	423.4	520.9	441.0
105°	68.8	104.3	422.2	641.0	598.0
107.5°	84.8	117.7	398.2	703.3	713.8
110°	95.5	125.4	378.3	719.4	764.2

TEST NUMBER: P563256

CATALOG NUMBER: SQ4-PP3-025U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	106.2	134.6	360.0	709.2	778.0
115°	122.3	148.4	338.2	674.7	770.0
117.5°	137.9	161.9	323.3	626.8	732.5
120°	147.1	169.5	317.2	594.6	697.4
122.5°	156.3	178.7	312.6	562.5	663.7
125°	170.0	190.6	307.6	519.9	613.3
127.5°	181.1	202.0	303.4	485.5	564.4
130°	187.2	209.7	301.9	464.0	536.9
132.5°	193.4	215.8	300.3	445.5	510.9
135°	202.5	223.1	298.0	419.7	475.7
137.5°	212.1	232.2	297.7	400.4	446.3
140°	219.7	238.4	296.1	385.0	428.0
142.5°	225.8	243.0	296.1	374.2	411.2
145°	235.0	249.9	294.2	357.9	385.9
147.5°	244.2	258.7	294.2	344.4	367.6
150°	250.3	263.4	294.2	336.7	355.4
152.5°	256.4	266.5	294.2	330.5	344.7
155°	265.6	273.0	294.2	323.1	332.4
157.5°	272.4	279.5	294.2	316.5	323.3
160°	277.0	282.6	294.2	313.4	317.2
162.5°	281.6	285.7	294.2	310.4	314.1
165°	286.6	290.3	294.2	305.8	309.5
167.5°	291.2	293.0	296.1	303.8	305.3
170°	294.2	296.1	296.1	303.8	303.8
172.5°	295.8	296.1	296.1	302.2	300.7
175°	298.0	298.0	296.1	300.0	300.0
177.5°	298.0	298.0	296.5	299.5	298.0
180°	298.0	298.0	298.0	298.0	298.0

(END OF REPORT)