

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563304

Luminaire Tested: **SQ4-PP3-050U-075D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563304
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9732.4 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563304
CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563304

CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	64	61	59	56	54	51	49	47	42
3	83	74	67	61	78	69	63	58	61	56	51	53	49	46	45	42	40	36
4	76	66	58	52	71	62	54	49	54	48	44	47	43	39	40	37	34	31
5	70	58	50	44	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	44	38	60	49	42	37	44	38	33	38	33	30	33	29	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	26	30	26	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10357	10357	10357
5°	10433	10369	10333
10°	10415	10341	10296
15°	10346	10290	10234
20°	10278	10220	10142
25°	10156	10085	9986
30°	9967	9915	9790
35°	9707	9641	9518
40°	9397	9337	9230
45°	9140	9075	8986
50°	8812	8755	8670
55°	8356	8245	8182
60°	7606	7388	7352
65°	6701	6422	6401
70°	5785	5546	5546
75°	4980	4910	4839
80°	4391	4444	4338
85°	3435	3747	3747



TEST NUMBER: P563304

CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.3	2.2
10°-20°	606.2	6.2
20°-30°	908.0	9.3
30°-40°	1065.0	10.9
40°-50°	1068.3	11.0
50°-60°	911.4	9.4
60°-70°	594.4	6.1
70°-80°	298.2	3.1
80°-90°	84.9	0.9
90°-100°	292.9	3.0
100°-110°	795.7	8.2
110°-120°	818.1	8.4
120°-130°	654.1	6.7
130°-140°	513.9	5.3
140°-150°	394.1	4.0
150°-160°	283.4	2.9
160°-170°	173.3	1.8
170°-180°	58.4	0.6
0°-30°	1726.4	17.7
0°-40°	2791.4	28.7
0°-60°	4771.1	49.0
0°-90°	5748.5	59.1
90°-120°	1906.7	19.6
90°-150°	3468.7	35.6
90°-180°	3984.0	40.9
0°-180°	9732.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2245	2245	2245	2245	2245	
5°	2253	2232	2239	2231	2231	214
15°	2166	2145	2155	2147	2143	611
25°	1995	1972	1981	1964	1962	917
35°	1724	1706	1712	1692	1690	1077
45°	1401	1391	1391	1377	1377	1079
55°	1039	1035	1025	1019	1017	923
65°	614	602	588	584	586	613
75°	279	279	276	274	272	303
85°	65	71	71	71	71	76
90°	2	8	14	18	18	5
95°	43	160	510	222	149	46
105°	141	220	875	1332	1254	150
115°	251	305	700	1393	1587	248
125°	345	393	634	1068	1260	308
135°	416	462	616	870	981	322
145°	481	515	608	739	795	302
155°	543	563	604	664	683	251
165°	589	596	606	632	634	166
175°	610	612	608	616	614	58
180°	610	610	610	610	610	

TEST NUMBER: P563304

CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2245.1	2245.1	2245.1	2245.1	2245.1
2.5°	2259.3	2240.8	2245.1	2241.7	2232.5
5°	2253.0	2231.8	2239.2	2231.3	2231.3
7.5°	2237.6	2214.5	2221.9	2214.0	2213.6
10°	2223.5	2200.4	2207.7	2199.8	2197.9
12.5°	2203.0	2179.9	2188.8	2179.4	2179.0
15°	2166.4	2145.2	2154.6	2146.6	2142.8
17.5°	2125.1	2102.0	2113.3	2102.2	2100.7
20°	2093.6	2070.5	2081.8	2066.0	2066.0
22.5°	2055.8	2032.7	2045.6	2025.1	2025.1
25°	1995.2	1972.1	1981.4	1963.7	1961.8
27.5°	1923.2	1900.5	1910.2	1890.1	1889.7
30°	1871.2	1850.1	1861.4	1839.7	1837.8
32.5°	1814.6	1795.0	1803.2	1781.5	1779.5
35°	1723.7	1706.4	1711.9	1692.1	1690.2
37.5°	1628.0	1610.3	1616.6	1599.7	1598.9
40°	1560.4	1548.8	1550.5	1536.7	1532.8
42.5°	1497.4	1484.3	1486.0	1472.2	1471.4
45°	1401.0	1391.4	1391.1	1377.4	1377.4
47.5°	1298.7	1291.3	1289.2	1277.8	1277.4
50°	1227.8	1222.0	1219.9	1210.1	1208.1
52.5°	1153.8	1151.1	1144.4	1136.1	1135.7
55°	1038.9	1035.1	1025.1	1019.2	1017.3
57.5°	914.2	906.5	895.3	886.7	888.2
60°	824.4	816.8	800.8	796.9	796.9
62.5°	737.9	728.6	712.7	707.2	710.3
65°	613.9	602.4	588.3	584.4	586.4
67.5°	501.4	491.0	475.8	475.7	474.2
70°	428.9	423.2	411.2	411.2	411.2
72.5°	364.4	361.7	353.0	353.0	351.4
75°	279.4	279.4	275.5	273.5	271.5
77.5°	209.4	210.1	208.2	206.1	202.7
80°	165.3	169.1	167.3	165.2	163.3
82.5°	124.4	128.2	127.9	124.3	124.0
85°	64.9	70.7	70.8	70.8	70.8
87.5°	17.7	25.0	27.9	28.8	30.3
90°	2.0	7.7	13.7	17.7	17.7
92.5°	17.7	80.2	139.3	59.8	50.6
95°	43.2	160.2	510.1	222.0	149.1
97.5°	71.4	176.9	782.0	608.4	427.3
100°	90.2	188.1	865.2	877.1	708.2
102.5°	109.1	199.2	887.2	1084.7	935.8
105°	141.3	219.9	875.0	1332.3	1253.6
107.5°	174.6	244.1	824.4	1460.1	1482.0
110°	198.2	261.5	786.7	1485.3	1579.3



TEST NUMBER: P563304

CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.6	278.8	749.1	1464.4	1606.0
115°	251.1	304.8	700.4	1393.4	1587.2
117.5°	281.7	333.1	669.4	1292.7	1511.0
120°	302.1	352.0	655.3	1225.2	1442.0
122.5°	319.4	369.3	645.9	1157.6	1366.7
125°	345.3	393.3	633.7	1067.7	1259.5
127.5°	368.4	416.0	627.0	999.6	1164.2
130°	382.6	428.6	623.9	956.8	1104.5
132.5°	396.7	442.7	620.7	920.4	1051.2
135°	415.9	462.0	616.0	869.7	980.9
137.5°	436.7	478.5	613.7	824.9	918.6
140°	449.3	489.6	612.1	796.5	880.9
142.5°	461.8	499.0	610.5	774.2	844.8
145°	480.7	515.2	608.2	738.9	794.6
147.5°	501.9	531.4	606.2	711.2	754.9
150°	516.0	540.9	606.2	695.3	729.8
152.5°	527.0	548.8	604.7	681.0	709.4
155°	543.4	562.6	604.3	663.6	682.7
157.5°	559.5	574.5	604.3	651.7	666.3
160°	568.9	582.4	604.3	643.8	655.3
162.5°	578.4	588.7	605.8	637.4	645.9
165°	588.6	596.2	606.2	631.8	633.7
167.5°	599.2	603.0	608.2	625.1	626.6
170°	602.3	606.1	608.2	621.9	621.9
172.5°	605.4	607.7	608.2	618.8	618.8
175°	610.1	612.1	608.2	616.0	614.1
177.5°	611.7	611.7	607.0	613.2	610.1
180°	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)