

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564610

Luminaire Tested: **SQ4-PW1-025U-125D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564610
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-125D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5026.7 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564610
CATALOG NUMBER: SQ4-PW1-025U-125D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564610

CATALOG NUMBER: SQ4-PW1-025U-125D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71
2	96	88	82	77	92	85	79	74	79	74	70	73	69	66	68	65	62	59
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50
4	81	69	61	54	77	67	59	53	62	56	51	58	53	48	54	50	46	43
5	74	62	53	47	71	60	52	46	56	49	44	52	46	42	49	44	40	38
6	68	56	47	41	65	54	46	40	50	44	39	47	41	37	44	39	35	33
7	63	51	42	36	61	49	41	36	46	39	34	43	37	33	40	35	31	29
8	59	46	38	32	57	45	37	32	42	35	31	40	34	29	37	32	28	26
9	55	42	34	29	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	31	26	50	38	31	26	36	29	25	34	28	24	32	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15182	15182	15182
5°	15280	15159	15092
10°	15158	15036	14954
15°	14998	14832	14776
20°	14819	14591	14563
25°	14611	14346	14302
30°	14302	14086	13993
35°	13896	13700	13618
40°	13463	13253	13201
45°	12940	12769	12712
50°	12403	12298	12215
55°	11824	11824	11638
60°	11103	11317	10915
65°	10160	10667	9907
70°	8956	9816	8721
75°	7650	8787	7443
80°	5929	7396	6009
85°	3832	5674	5060



TEST NUMBER: P564610

CATALOG NUMBER: SQ4-PW1-025U-125D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	3.1
10°-20°	437.5	8.7
20°-30°	648.9	12.9
30°-40°	759.3	15.1
40°-50°	755.9	15.0
50°-60°	652.8	13.0
60°-70°	469.9	9.3
70°-80°	246.4	4.9
80°-90°	61.8	1.2
90°-100°	63.1	1.3
100°-110°	165.9	3.3
110°-120°	172.0	3.4
120°-130°	138.0	2.7
130°-140°	108.3	2.2
140°-150°	83.1	1.7
150°-160°	59.9	1.2
160°-170°	36.6	0.7
170°-180°	12.4	0.2
0°-30°	1241.3	24.7
0°-40°	2000.7	39.8
0°-60°	3409.3	67.8
0°-90°	4187.4	83.3
90°-120°	401.1	8.0
90°-150°	730.4	14.5
90°-180°	839.0	16.7
0°-180°	5026.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1646	1646	1646	1646	1646	
5°	1650	1632	1637	1632	1630	156
15°	1570	1550	1553	1550	1547	443
25°	1435	1411	1409	1401	1405	660
35°	1234	1217	1216	1205	1209	771
45°	992	983	979	976	974	765
55°	735	734	735	725	724	656
65°	465	480	489	469	454	461
75°	215	234	246	230	209	230
85°	36	48	54	51	48	48
90°	1	2	7	3	3	2
95°	8	33	109	56	38	9
105°	30	45	183	278	260	32
115°	53	64	147	293	334	52
125°	74	83	134	226	266	66
135°	88	97	130	182	207	68
145°	102	109	128	156	168	64
155°	115	119	128	140	144	53
165°	124	126	128	133	134	35
175°	130	130	129	130	130	12
180°	130	130	130	130	130	

TEST NUMBER: P564610

CATALOG NUMBER: SQ4-PW1-025U-125D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1645.5	1645.5	1645.5	1645.5	1645.5
2.5°	1654.8	1641.2	1645.5	1641.9	1633.9
5°	1649.9	1631.5	1636.8	1632.4	1629.6
7.5°	1633.1	1616.1	1620.0	1615.3	1613.6
10°	1618.0	1601.0	1604.9	1599.1	1596.2
12.5°	1600.6	1582.5	1586.4	1580.6	1578.9
15°	1570.2	1550.3	1552.8	1549.8	1547.0
17.5°	1534.8	1514.6	1515.1	1510.4	1509.8
20°	1509.3	1488.0	1486.1	1480.3	1483.2
22.5°	1481.4	1459.0	1457.1	1449.0	1453.0
25°	1435.3	1411.2	1409.2	1400.6	1404.9
27.5°	1382.0	1358.1	1358.2	1346.1	1350.6
30°	1342.5	1319.8	1322.2	1307.9	1313.5
32.5°	1300.8	1280.4	1281.6	1267.3	1272.9
35°	1233.8	1216.8	1216.4	1204.9	1209.1
37.5°	1165.4	1150.3	1148.0	1141.3	1142.5
40°	1117.8	1105.1	1100.4	1096.1	1096.1
42.5°	1067.9	1056.3	1051.7	1048.5	1047.3
45°	991.7	983.2	978.6	975.7	974.3
47.5°	916.3	908.3	904.4	902.3	900.9
50°	864.1	858.4	856.8	852.5	851.0
52.5°	811.9	808.5	807.0	801.4	800.0
55°	735.1	733.6	735.1	724.9	723.5
57.5°	655.0	657.3	662.0	648.3	644.9
60°	601.7	607.3	613.3	597.2	591.5
62.5°	547.2	556.2	564.6	546.1	538.2
65°	465.4	479.6	488.6	469.4	453.8
67.5°	386.5	404.1	414.9	394.2	376.7
70°	332.0	351.9	363.9	343.2	323.3
72.5°	284.5	306.6	316.3	296.8	276.9
75°	214.6	234.4	246.5	230.0	208.8
77.5°	152.2	170.9	180.9	166.6	149.0
80°	111.6	131.5	139.2	127.3	113.1
82.5°	79.2	95.6	100.9	93.7	84.1
85°	36.2	47.6	53.6	50.7	47.8
87.5°	9.4	17.7	23.4	22.7	23.9
90°	0.8	2.5	6.6	3.3	3.3
92.5°	3.5	16.8	37.2	16.5	10.6
95°	8.3	32.6	108.7	56.0	38.2
97.5°	14.4	35.9	162.7	129.4	95.3
100°	19.1	38.6	179.3	181.7	141.1
102.5°	23.1	41.3	183.9	226.3	191.6
105°	29.9	45.3	183.4	278.5	259.8
107.5°	36.9	51.1	173.0	305.6	310.1
110°	41.5	54.5	164.3	312.5	332.0

TEST NUMBER: P564610

CATALOG NUMBER: SQ4-PW1-025U-125D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	46.2	58.5	156.4	308.1	338.0
115°	53.1	64.5	146.9	293.1	334.5
117.5°	59.9	70.3	140.4	272.3	318.2
120°	63.9	73.7	137.8	258.3	303.0
122.5°	67.9	77.6	135.8	244.4	288.4
125°	73.9	82.8	133.6	225.9	266.4
127.5°	78.7	87.8	131.8	210.9	245.2
130°	81.3	91.1	131.1	201.6	233.2
132.5°	84.0	93.7	130.5	193.5	222.0
135°	88.0	96.9	129.5	182.3	206.7
137.5°	92.1	100.9	129.3	173.9	193.9
140°	95.5	103.6	128.7	167.3	185.9
142.5°	98.1	105.6	128.7	162.6	178.6
145°	102.1	108.6	127.8	155.5	167.7
147.5°	106.1	112.4	127.8	149.6	159.7
150°	108.7	114.4	127.8	146.3	154.4
152.5°	111.4	115.8	127.8	143.6	149.7
155°	115.4	118.6	127.8	140.4	144.4
157.5°	118.4	121.4	127.8	137.5	140.4
160°	120.4	122.8	127.8	136.2	137.8
162.5°	122.3	124.1	127.8	134.8	136.5
165°	124.5	126.1	127.8	132.8	134.5
167.5°	126.5	127.3	128.7	132.0	132.6
170°	127.8	128.6	128.7	132.0	132.0
172.5°	128.5	128.7	128.7	131.3	130.6
175°	129.5	129.5	128.7	130.3	130.3
177.5°	129.5	129.5	128.8	130.1	129.5
180°	129.5	129.5	129.5	129.5	129.5

(END OF REPORT)