

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563424

Luminaire Tested: **SQ4-PP3-075U-100D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563424
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13624.9 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 108.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563424
CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563424

CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	46	45	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33	30
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	27	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13761	13761	13761
5°	13862	13777	13729
10°	13839	13741	13679
15°	13747	13672	13597
20°	13656	13579	13477
25°	13494	13400	13268
30°	13244	13175	13007
35°	12897	12810	12647
40°	12485	12406	12264
45°	12144	12059	11939
50°	11708	11633	11521
55°	11102	10955	10871
60°	10106	9818	9769
65°	8904	8533	8504
70°	7687	7370	7370
75°	6616	6523	6431
80°	5834	5903	5765
85°	4568	4981	4981



TEST NUMBER: P563424

CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.1	2.1
10°-20°	805.4	5.9
20°-30°	1206.4	8.9
30°-40°	1415.1	10.4
40°-50°	1419.5	10.4
50°-60°	1210.9	8.9
60°-70°	789.7	5.8
70°-80°	396.2	2.9
80°-90°	112.0	0.8
90°-100°	433.5	3.2
100°-110°	1192.6	8.8
110°-120°	1231.0	9.0
120°-130°	986.3	7.2
130°-140°	774.7	5.7
140°-150°	593.7	4.4
150°-160°	426.8	3.1
160°-170°	261.0	1.9
170°-180°	88.0	0.6
0°-30°	2293.9	16.8
0°-40°	3709.0	27.2
0°-60°	6339.4	46.5
0°-90°	7637.3	56.1
90°-120°	2857.1	21.0
90°-150°	5211.7	38.3
90°-180°	5988.0	43.9
0°-180°	13624.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2983	2983	2983	2983	2983	
5°	2994	2965	2975	2965	2965	284
15°	2878	2850	2863	2852	2847	812
25°	2651	2620	2633	2609	2607	1219
35°	2290	2267	2275	2248	2246	1431
45°	1862	1849	1848	1830	1830	1433
55°	1380	1375	1362	1354	1352	1227
65°	816	800	782	776	779	814
75°	371	371	366	363	361	403
85°	86	94	94	94	94	101
90°	2	8	14	18	18	7
95°	64	237	767	328	209	68
105°	213	328	1314	2001	1868	225
115°	377	460	1054	2099	2382	372
125°	520	593	956	1618	1895	464
135°	628	697	929	1308	1480	484
145°	726	775	915	1115	1201	455
155°	821	848	909	1002	1031	377
165°	888	899	913	950	956	250
175°	919	921	915	927	925	87
180°	919	919	919	919	919	

TEST NUMBER: P563424

CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2983.1	2983.1	2983.1	2983.1	2983.1
2.5°	3001.9	2977.4	2983.1	2978.6	2966.3
5°	2993.5	2965.4	2975.2	2964.8	2964.8
7.5°	2973.1	2942.5	2952.2	2941.7	2941.2
10°	2954.3	2923.6	2933.4	2922.9	2920.3
12.5°	2927.1	2896.4	2908.3	2895.7	2895.2
15°	2878.5	2850.4	2862.8	2852.2	2847.1
17.5°	2823.6	2792.9	2807.9	2793.2	2791.2
20°	2781.8	2751.1	2766.1	2745.2	2745.2
22.5°	2731.6	2700.9	2718.0	2690.8	2690.8
25°	2651.0	2620.4	2632.7	2609.1	2606.6
27.5°	2555.3	2525.2	2538.1	2511.4	2510.9
30°	2486.3	2458.2	2473.3	2444.4	2441.9
32.5°	2411.0	2385.0	2395.9	2367.0	2364.5
35°	2290.2	2267.2	2274.6	2248.4	2245.8
37.5°	2163.2	2139.7	2148.0	2125.5	2124.5
40°	2073.2	2057.9	2060.2	2041.8	2036.6
42.5°	1989.6	1972.2	1974.4	1956.1	1955.1
45°	1861.5	1848.7	1848.4	1830.1	1830.1
47.5°	1725.5	1715.8	1713.0	1697.8	1697.3
50°	1631.4	1623.7	1620.9	1607.8	1605.3
52.5°	1533.1	1529.5	1520.6	1509.6	1509.1
55°	1380.4	1375.3	1362.1	1354.2	1351.7
57.5°	1214.7	1204.4	1189.6	1178.1	1180.2
60°	1095.4	1085.2	1064.1	1058.8	1058.8
62.5°	980.4	968.1	946.9	939.7	943.8
65°	815.7	800.4	781.7	776.5	779.1
67.5°	666.2	652.4	632.2	632.1	630.1
70°	569.9	562.3	546.4	546.4	546.4
72.5°	484.2	480.6	469.0	469.0	466.9
75°	371.2	371.2	366.0	363.3	360.8
77.5°	278.2	279.2	276.6	273.9	269.3
80°	219.6	224.7	222.2	219.6	217.0
82.5°	165.2	170.3	169.9	165.2	164.7
85°	86.3	93.9	94.1	94.1	94.1
87.5°	23.4	32.7	36.2	37.0	39.1
90°	2.0	7.7	13.7	17.6	17.6
92.5°	27.0	115.3	199.9	76.7	63.0
95°	64.5	236.6	766.6	327.8	209.2
97.5°	105.2	262.4	1169.8	901.3	635.9
100°	134.9	278.3	1296.5	1308.6	1067.7
102.5°	163.1	297.3	1329.4	1623.5	1402.5
105°	213.2	327.9	1314.1	2001.4	1867.5
107.5°	260.9	365.6	1239.4	2186.4	2226.2
110°	295.3	390.9	1183.1	2232.4	2370.1

TEST NUMBER: P563424

CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	326.6	419.1	1126.8	2202.8	2412.3
115°	377.4	459.6	1054.0	2098.8	2381.8
117.5°	425.9	501.6	1007.9	1953.0	2273.1
120°	455.6	528.3	987.5	1843.8	2174.6
122.5°	482.2	554.9	973.5	1747.9	2061.9
125°	520.2	592.8	956.3	1617.7	1894.9
127.5°	556.2	625.4	944.9	1508.9	1752.2
130°	574.9	645.7	938.7	1444.3	1666.1
132.5°	596.8	667.6	934.0	1387.5	1587.9
135°	627.7	696.6	928.9	1308.3	1480.3
137.5°	656.7	720.5	924.6	1244.2	1386.1
140°	678.6	737.8	923.0	1201.7	1329.8
142.5°	697.3	752.0	919.9	1163.7	1273.4
145°	725.5	775.2	915.2	1114.7	1200.7
147.5°	755.6	798.4	912.8	1071.2	1140.1
150°	774.4	812.6	911.3	1047.4	1101.0
152.5°	791.6	826.8	909.7	1026.9	1071.2
155°	821.3	848.1	909.3	1001.9	1030.6
157.5°	842.8	864.6	909.3	981.3	1001.2
160°	858.5	875.7	909.3	970.3	985.6
162.5°	871.0	885.1	910.9	960.8	973.1
165°	887.8	899.3	913.2	950.5	956.3
167.5°	899.5	908.3	915.2	941.8	943.3
170°	907.4	913.1	915.2	938.7	938.7
172.5°	913.6	916.3	915.2	933.9	932.4
175°	919.1	921.0	915.2	926.9	925.0
177.5°	920.7	920.7	914.4	923.7	920.7
180°	919.1	919.1	919.1	919.1	919.1

(END OF REPORT)