

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564706

Luminaire Tested: **SQ4-PW1-050U-125D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564706
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-125D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5918.5 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564706
CATALOG NUMBER: SQ4-PW1-050U-125D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564706

CATALOG NUMBER: SQ4-PW1-050U-125D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	94	91	97	93	90	86	84	81	78	75	73	71	67	65	64	60
2	94	86	80	74	88	82	76	71	73	69	65	66	62	59	59	56	54	50
3	85	76	68	62	81	72	65	60	65	59	55	58	54	50	52	49	46	43
4	78	67	59	53	74	64	56	51	58	52	47	52	47	43	47	43	40	37
5	72	60	52	45	68	57	49	44	52	45	41	47	42	38	42	38	35	32
6	66	54	46	40	63	51	44	38	47	40	36	42	37	33	38	34	31	28
7	61	49	41	35	58	47	39	34	42	36	32	39	33	29	35	31	27	25
8	57	44	36	31	54	43	35	30	39	33	28	35	30	26	32	28	24	22
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15182	15182	15182
5°	15280	15159	15092
10°	15158	15036	14954
15°	14998	14832	14776
20°	14819	14591	14563
25°	14611	14346	14302
30°	14302	14086	13993
35°	13896	13700	13618
40°	13463	13253	13201
45°	12940	12769	12712
50°	12403	12298	12215
55°	11824	11824	11638
60°	11103	11317	10915
65°	10160	10667	9907
70°	8956	9816	8721
75°	7650	8787	7443
80°	5929	7396	6009
85°	3832	5674	5060



TEST NUMBER: P564706

CATALOG NUMBER: SQ4-PW1-050U-125D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	2.6
10°-20°	437.5	7.4
20°-30°	648.9	11.0
30°-40°	759.3	12.8
40°-50°	755.9	12.8
50°-60°	652.8	11.0
60°-70°	469.9	7.9
70°-80°	246.4	4.2
80°-90°	62.1	1.0
90°-100°	127.2	2.2
100°-110°	345.7	5.8
110°-120°	355.4	6.0
120°-130°	284.2	4.8
130°-140°	223.3	3.8
140°-150°	171.2	2.9
150°-160°	123.1	2.1
160°-170°	75.3	1.3
170°-180°	25.4	0.4
0°-30°	1241.3	21.0
0°-40°	2000.7	33.8
0°-60°	3409.3	57.6
0°-90°	4187.7	70.8
90°-120°	828.3	14.0
90°-150°	1507.0	25.5
90°-180°	1731.0	29.2
0°-180°	5918.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1646	1646	1646	1646	1646	
5°	1650	1632	1637	1632	1630	156
15°	1570	1550	1553	1550	1547	443
25°	1435	1411	1409	1401	1405	660
35°	1234	1217	1216	1205	1209	771
45°	992	983	979	976	974	765
55°	735	734	735	725	724	656
65°	465	480	489	469	454	461
75°	215	234	246	230	209	230
85°	36	48	54	51	48	48
90°	1	3	6	8	8	3
95°	19	70	222	96	65	20
105°	61	96	380	579	545	65
115°	109	132	304	605	690	108
125°	150	171	275	464	547	134
135°	181	201	268	378	426	140
145°	209	224	264	321	345	131
155°	236	244	262	288	297	109
165°	256	259	263	274	275	72
175°	265	266	264	268	267	25
180°	265	265	265	265	265	



TEST NUMBER: P564706

CATALOG NUMBER: SQ4-PW1-050U-125D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1645.5	1645.5	1645.5	1645.5	1645.5
2.5°	1654.8	1641.2	1645.5	1641.9	1633.9
5°	1649.9	1631.5	1636.8	1632.4	1629.6
7.5°	1633.1	1616.1	1620.0	1615.3	1613.6
10°	1618.0	1601.0	1604.9	1599.1	1596.2
12.5°	1600.6	1582.5	1586.4	1580.6	1578.9
15°	1570.2	1550.3	1552.8	1549.8	1547.0
17.5°	1534.8	1514.6	1515.1	1510.4	1509.8
20°	1509.3	1488.0	1486.1	1480.3	1483.2
22.5°	1481.4	1459.0	1457.1	1449.0	1453.0
25°	1435.3	1411.2	1409.2	1400.6	1404.9
27.5°	1382.0	1358.1	1358.2	1346.1	1350.6
30°	1342.5	1319.8	1322.2	1307.9	1313.5
32.5°	1300.8	1280.4	1281.6	1267.3	1272.9
35°	1233.8	1216.8	1216.4	1204.9	1209.1
37.5°	1165.4	1150.3	1148.0	1141.3	1142.5
40°	1117.8	1105.1	1100.4	1096.1	1096.1
42.5°	1067.9	1056.3	1051.7	1048.5	1047.3
45°	991.7	983.2	978.6	975.7	974.3
47.5°	916.3	908.3	904.4	902.3	900.9
50°	864.1	858.4	856.8	852.5	851.0
52.5°	811.9	808.5	807.0	801.4	800.0
55°	735.1	733.6	735.1	724.9	723.5
57.5°	655.0	657.3	662.0	648.3	644.9
60°	601.7	607.3	613.3	597.2	591.5
62.5°	547.2	556.2	564.6	546.1	538.2
65°	465.4	479.6	488.6	469.4	453.8
67.5°	386.5	404.1	414.9	394.2	376.7
70°	332.0	351.9	363.9	343.2	323.3
72.5°	284.5	306.6	316.3	296.8	276.9
75°	214.6	234.4	246.5	230.0	208.8
77.5°	152.2	170.9	180.9	166.6	149.0
80°	111.6	131.5	139.2	127.3	113.1
82.5°	79.2	95.6	100.9	93.7	84.1
85°	36.2	47.6	53.6	50.7	47.8
87.5°	9.4	17.9	23.2	23.6	24.7
90°	0.9	3.4	6.0	7.7	7.7
92.5°	7.7	34.8	60.5	26.0	22.0
95°	18.8	69.6	221.6	96.4	64.8
97.5°	31.0	76.9	339.7	264.3	185.6
100°	39.2	81.7	375.9	381.0	307.7
102.5°	47.4	86.6	385.4	471.2	406.6
105°	61.4	95.5	380.1	578.8	544.6
107.5°	75.9	106.0	358.2	634.4	643.9
110°	86.1	113.6	341.8	645.3	686.1

TEST NUMBER: P564706

CATALOG NUMBER: SQ4-PW1-050U-125D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.0	121.1	325.4	636.2	697.7
115°	109.1	132.4	304.3	605.4	689.5
117.5°	122.4	144.7	290.8	561.6	656.5
120°	131.3	152.9	284.7	532.3	626.5
122.5°	138.8	160.4	280.6	502.9	593.7
125°	150.0	170.8	275.3	463.9	547.2
127.5°	160.1	180.7	272.4	434.3	505.8
130°	166.2	186.2	271.0	415.7	479.9
132.5°	172.3	192.3	269.7	399.8	456.7
135°	180.7	200.7	267.6	377.8	426.2
137.5°	189.7	207.9	266.6	358.4	399.1
140°	195.2	212.7	265.9	346.0	382.7
142.5°	200.6	216.8	265.2	336.3	367.0
145°	208.8	223.8	264.2	321.0	345.2
147.5°	218.0	230.9	263.4	309.0	328.0
150°	224.2	235.0	263.4	302.1	317.1
152.5°	228.9	238.4	262.7	295.9	308.2
155°	236.1	244.4	262.5	288.3	296.6
157.5°	243.1	249.6	262.5	283.1	289.5
160°	247.2	253.0	262.5	279.7	284.7
162.5°	251.3	255.8	263.2	276.9	280.6
165°	255.7	259.0	263.4	274.5	275.3
167.5°	260.3	262.0	264.2	271.6	272.2
170°	261.7	263.3	264.2	270.2	270.2
172.5°	263.0	264.0	264.2	268.8	268.8
175°	265.1	265.9	264.2	267.6	266.8
177.5°	265.8	265.8	263.7	266.4	265.1
180°	265.1	265.1	265.1	265.1	265.1

(END OF REPORT)