

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565018

Luminaire Tested: **SQ4-PW1-125U-050D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565018
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6020.7 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 47.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565018
CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P565018

CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	32	31	30	24
2	85	77	72	67	75	69	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	17
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	18	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6114	6066	6039
10°	6065	6016	5984
15°	6001	5934	5912
20°	5929	5838	5827
25°	5846	5740	5722
30°	5723	5637	5599
35°	5561	5482	5449
40°	5387	5303	5282
45°	5177	5110	5086
50°	4963	4922	4887
55°	4731	4731	4657
60°	4443	4528	4368
65°	4065	4268	3965
70°	3582	3928	3491
75°	3062	3515	2977
80°	2375	2959	2407
85°	1535	2276	2022



TEST NUMBER: P565018

CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	1.0
10°-20°	175.0	2.9
20°-30°	259.7	4.3
30°-40°	303.8	5.0
40°-50°	302.5	5.0
50°-60°	261.2	4.3
60°-70°	188.0	3.1
70°-80°	98.6	1.6
80°-90°	26.0	0.4
90°-100°	314.8	5.2
100°-110°	847.9	14.1
110°-120°	889.9	14.8
120°-130°	722.1	12.0
130°-140°	566.3	9.4
140°-150°	434.8	7.2
150°-160°	312.6	5.2
160°-170°	191.0	3.2
170°-180°	64.4	1.1
0°-30°	496.7	8.3
0°-40°	800.5	13.3
0°-60°	1364.2	22.7
0°-90°	1676.8	27.9
90°-120°	2052.6	34.1
90°-150°	3775.9	62.7
90°-180°	4344.0	72.2
0°-180°	6020.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	658	658	658	658	658	
5°	660	653	655	653	652	63
15°	628	620	621	620	619	177
25°	574	565	564	560	562	264
35°	494	487	487	482	484	309
45°	397	393	392	390	390	306
55°	294	294	294	290	290	262
65°	186	192	196	188	182	185
75°	86	94	99	92	84	92
85°	14	19	22	20	19	19
90°	2	5	10	11	11	4
95°	48	171	516	264	183	50
105°	157	244	938	1403	1317	165
115°	277	339	781	1509	1707	272
125°	378	434	701	1185	1395	338
135°	455	508	682	956	1083	351
145°	526	567	673	817	878	330
155°	598	619	667	733	757	275
165°	648	656	670	696	700	183
175°	674	673	670	680	678	64
180°	673	673	673	673	673	

TEST NUMBER: P565018

CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	658.4	658.4	658.4	658.4	658.4
2.5°	662.2	656.7	658.4	657.0	653.8
5°	660.2	652.8	655.0	653.2	652.1
7.5°	653.5	646.7	648.2	646.4	645.7
10°	647.4	640.6	642.2	639.9	638.7
12.5°	640.5	633.2	634.8	632.4	631.8
15°	628.3	620.3	621.3	620.1	619.0
17.5°	614.1	606.1	606.2	604.4	604.1
20°	603.9	595.4	594.6	592.3	593.5
22.5°	592.8	583.8	583.0	579.8	581.4
25°	574.3	564.7	563.9	560.4	562.1
27.5°	553.0	543.5	543.5	538.6	540.4
30°	537.2	528.1	529.1	523.3	525.6
32.5°	520.5	512.3	512.8	507.1	509.4
35°	493.7	486.9	486.7	482.1	483.8
37.5°	466.3	460.3	459.3	456.7	457.1
40°	447.3	442.2	440.3	438.6	438.6
42.5°	427.3	422.7	420.8	419.5	419.1
45°	396.8	393.4	391.6	390.4	389.8
47.5°	366.6	363.5	361.9	361.1	360.5
50°	345.8	343.5	342.9	341.1	340.5
52.5°	324.9	323.5	322.9	320.7	320.1
55°	294.1	293.6	294.1	290.1	289.5
57.5°	262.1	263.0	264.9	259.4	258.0
60°	240.8	243.0	245.4	239.0	236.7
62.5°	218.9	222.6	225.9	218.5	215.3
65°	186.2	191.9	195.5	187.8	181.6
67.5°	154.7	161.7	166.0	157.8	150.7
70°	132.8	140.8	145.6	137.3	129.4
72.5°	113.8	122.7	126.6	118.7	110.8
75°	85.9	93.8	98.6	92.0	83.5
77.5°	60.9	68.4	72.4	66.7	59.6
80°	44.7	52.6	55.7	50.9	45.3
82.5°	31.7	38.3	40.4	37.5	33.6
85°	14.5	19.0	21.5	20.3	19.1
87.5°	4.1	7.9	10.9	11.1	11.5
90°	1.7	5.1	10.3	11.1	11.1
92.5°	20.9	73.9	146.1	70.3	48.9
95°	48.0	171.2	516.0	263.9	182.6
97.5°	76.6	196.0	809.3	676.1	509.9
100°	98.6	205.9	902.6	944.4	783.5
102.5°	119.8	219.7	933.5	1145.3	1013.2
105°	156.9	244.0	937.8	1403.0	1316.6
107.5°	191.8	269.6	897.8	1535.4	1557.7
110°	215.2	288.9	861.5	1576.5	1657.8



TEST NUMBER: P565018

CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	239.8	308.2	826.5	1567.4	1701.0
115°	276.9	338.9	780.9	1508.8	1706.6
117.5°	310.6	368.8	745.6	1415.4	1635.7
120°	332.6	388.7	727.7	1348.3	1574.6
122.5°	351.8	407.3	714.7	1279.8	1505.4
125°	378.0	434.2	701.2	1185.1	1394.6
127.5°	403.2	458.5	692.6	1101.6	1288.7
130°	418.3	473.6	689.2	1053.8	1218.1
132.5°	433.4	488.0	685.7	1011.6	1162.5
135°	455.2	508.0	681.5	956.1	1082.6
137.5°	475.9	526.5	679.2	908.9	1012.8
140°	490.3	538.9	677.2	879.9	973.8
142.5°	505.4	550.7	675.8	852.8	931.9
145°	526.3	567.4	672.9	817.4	877.8
147.5°	548.9	584.6	670.0	787.6	835.1
150°	564.0	595.0	668.6	768.9	808.3
152.5°	577.7	604.7	667.9	753.7	785.7
155°	597.5	619.2	666.9	733.4	756.9
157.5°	614.8	631.7	667.1	719.2	734.9
160°	625.7	640.0	667.7	710.9	722.6
162.5°	635.3	646.9	668.4	703.9	712.3
165°	648.0	655.6	669.5	696.1	699.5
167.5°	658.3	662.7	670.3	690.1	691.4
170°	665.2	666.8	670.3	686.6	686.6
172.5°	669.3	669.6	671.0	683.2	683.2
175°	673.7	672.9	670.3	679.7	678.0
177.5°	675.6	674.3	670.8	676.3	674.9
180°	672.9	672.9	672.9	672.9	672.9

(END OF REPORT)