

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565114

Luminaire Tested: **SQ4-PW1-150U-050D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565114
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6911.1 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565114
CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P565114

CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	57	44	43	42	29	28	27	21
2	84	77	71	66	74	68	64	59	53	50	47	39	37	35	25	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	22	21	20	15
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	9
8	50	38	31	26	45	35	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6114	6066	6039
10°	6065	6016	5984
15°	6001	5934	5912
20°	5929	5838	5827
25°	5846	5740	5722
30°	5723	5637	5599
35°	5561	5482	5449
40°	5387	5303	5282
45°	5177	5110	5086
50°	4963	4922	4887
55°	4731	4731	4657
60°	4443	4528	4368
65°	4065	4268	3965
70°	3582	3928	3491
75°	3062	3515	2977
80°	2375	2959	2407
85°	1535	2276	2022



TEST NUMBER: P565114

CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	0.9
10°-20°	175.0	2.5
20°-30°	259.7	3.8
30°-40°	303.8	4.4
40°-50°	302.5	4.4
50°-60°	261.2	3.8
60°-70°	188.0	2.7
70°-80°	98.6	1.4
80°-90°	26.1	0.4
90°-100°	377.3	5.5
100°-110°	1020.1	14.8
110°-120°	1072.5	15.5
120°-130°	871.2	12.6
130°-140°	683.3	9.9
140°-150°	524.5	7.6
150°-160°	377.2	5.5
160°-170°	230.4	3.3
170°-180°	77.7	1.1
0°-30°	496.7	7.2
0°-40°	800.5	11.6
0°-60°	1364.2	19.7
0°-90°	1677.0	24.3
90°-120°	2469.9	35.7
90°-150°	4548.9	65.8
90°-180°	5234.0	75.7
0°-180°	6911.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	658	658	658	658	658	
5°	660	653	655	653	652	63
15°	628	620	621	620	619	177
25°	574	565	564	560	562	264
35°	494	487	487	482	484	309
45°	397	393	392	390	390	306
55°	294	294	294	290	290	262
65°	186	192	196	188	182	185
75°	86	94	99	92	84	92
85°	14	19	22	20	19	19
90°	2	5	11	12	11	4
95°	58	206	627	325	193	61
105°	190	293	1132	1669	1601	200
115°	334	408	938	1817	2051	330
125°	457	524	846	1428	1677	407
135°	548	613	823	1153	1305	423
145°	637	685	812	987	1062	399
155°	719	747	805	885	914	332
165°	783	791	808	840	844	221
175°	813	812	809	820	818	77
180°	812	812	812	812	812	



TEST NUMBER: P565114

CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	658.4	658.4	658.4	658.4	658.4
2.5°	662.2	656.7	658.4	657.0	653.8
5°	660.2	652.8	655.0	653.2	652.1
7.5°	653.5	646.7	648.2	646.4	645.7
10°	647.4	640.6	642.2	639.9	638.7
12.5°	640.5	633.2	634.8	632.4	631.8
15°	628.3	620.3	621.3	620.1	619.0
17.5°	614.1	606.1	606.2	604.4	604.1
20°	603.9	595.4	594.6	592.3	593.5
22.5°	592.8	583.8	583.0	579.8	581.4
25°	574.3	564.7	563.9	560.4	562.1
27.5°	553.0	543.5	543.5	538.6	540.4
30°	537.2	528.1	529.1	523.3	525.6
32.5°	520.5	512.3	512.8	507.1	509.4
35°	493.7	486.9	486.7	482.1	483.8
37.5°	466.3	460.3	459.3	456.7	457.1
40°	447.3	442.2	440.3	438.6	438.6
42.5°	427.3	422.7	420.8	419.5	419.1
45°	396.8	393.4	391.6	390.4	389.8
47.5°	366.6	363.5	361.9	361.1	360.5
50°	345.8	343.5	342.9	341.1	340.5
52.5°	324.9	323.5	322.9	320.7	320.1
55°	294.1	293.6	294.1	290.1	289.5
57.5°	262.1	263.0	264.9	259.4	258.0
60°	240.8	243.0	245.4	239.0	236.7
62.5°	218.9	222.6	225.9	218.5	215.3
65°	186.2	191.9	195.5	187.8	181.6
67.5°	154.7	161.7	166.0	157.8	150.7
70°	132.8	140.8	145.6	137.3	129.4
72.5°	113.8	122.7	126.6	118.7	110.8
75°	85.9	93.8	98.6	92.0	83.5
77.5°	60.9	68.4	72.4	66.7	59.6
80°	44.7	52.6	55.7	50.9	45.3
82.5°	31.7	38.3	40.4	37.5	33.6
85°	14.5	19.0	21.5	20.3	19.1
87.5°	4.1	7.9	11.1	11.3	11.6
90°	1.7	5.2	11.4	12.2	11.4
92.5°	24.8	90.4	178.4	77.5	56.1
95°	58.5	205.5	627.4	324.7	193.1
97.5°	94.0	235.7	978.0	809.4	594.4
100°	120.6	247.9	1087.1	1133.7	916.7
102.5°	145.1	264.9	1125.6	1379.7	1217.3
105°	189.6	293.0	1131.7	1669.3	1600.9
107.5°	230.9	325.2	1082.2	1850.0	1872.7
110°	263.0	348.5	1038.2	1898.5	1995.1



TEST NUMBER: P565114

CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.7	371.7	997.6	1888.8	2051.0
115°	333.8	408.2	938.5	1816.9	2051.0
117.5°	375.1	444.8	899.6	1706.9	1972.3
120°	400.2	468.6	876.5	1628.1	1898.9
122.5°	424.0	491.0	862.5	1543.5	1816.4
125°	457.0	523.7	845.9	1427.5	1677.0
127.5°	487.4	552.9	836.1	1332.8	1552.2
130°	504.2	571.7	831.9	1274.2	1472.5
132.5°	521.7	588.5	827.7	1221.5	1404.0
135°	547.9	612.9	823.2	1152.6	1304.7
137.5°	574.3	635.7	819.3	1096.7	1220.6
140°	592.5	649.7	817.9	1060.8	1171.0
142.5°	610.0	663.8	815.2	1028.3	1124.9
145°	637.1	684.9	811.8	986.6	1061.8
147.5°	661.7	704.1	808.0	948.8	1006.5
150°	679.9	717.5	806.6	928.2	974.4
152.5°	696.7	729.5	805.9	909.2	947.1
155°	719.2	747.4	804.8	885.0	914.1
157.5°	742.6	762.3	805.0	868.2	887.3
160°	755.9	772.1	805.7	857.6	871.3
162.5°	766.4	779.9	806.4	849.1	859.4
165°	783.0	790.7	808.3	839.9	844.2
167.5°	794.4	799.7	808.5	832.0	834.0
170°	801.3	803.9	809.2	828.4	828.4
172.5°	806.9	807.4	809.2	824.2	823.5
175°	812.7	811.8	809.2	819.7	817.9
177.5°	814.6	812.6	809.0	816.0	813.9
180°	811.8	811.8	811.8	811.8	811.8

(END OF REPORT)