

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519228

Luminaire Tested: **SQ4-WB-075U-100D-935-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519228  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-075U-100D-935-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5461.2 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 51.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519228  
CATALOG NUMBER: SQ4-WB-075U-100D-935-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P519228

CATALOG NUMBER: SQ4-WB-075U-100D-935-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	96	92	89	92	89	86	83	76	74	72	64	63	61	53	52	52	46
2	92	85	79	75	85	79	74	70	68	65	62	58	55	53	48	47	45	41
3	84	76	69	64	78	71	65	60	61	57	53	52	49	47	44	42	40	36
4	78	68	61	55	72	64	57	52	55	50	47	48	44	41	40	38	36	32
5	72	61	54	48	67	57	51	46	50	45	41	43	40	37	37	34	32	29
6	67	56	48	43	62	52	45	41	46	41	37	40	36	33	34	31	29	26
7	62	51	43	38	58	48	41	36	42	37	33	37	33	30	32	29	26	24
8	58	46	39	34	54	44	37	33	39	33	30	34	30	27	29	26	24	22
9	54	43	36	31	51	40	34	30	36	31	27	31	27	24	27	24	22	20
10	51	39	33	28	47	37	31	27	33	28	25	29	25	22	26	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18102	18102	18102
5°	17876	17813	17916
10°	16889	17042	17438
15°	15591	15953	16669
20°	14158	14691	15663
25°	12700	13392	14592
30°	11355	12097	13482
35°	9930	10647	12169
40°	8357	9021	10535
45°	6897	7492	8796
50°	5759	6277	7327
55°	4888	5387	6051
60°	4178	4670	4829
65°	3327	3927	3120
70°	2948	3064	1904
75°	2731	2485	1166
80°	2513	2285	1004
85°	2276	2096	815



TEST NUMBER: P519228

CATALOG NUMBER: SQ4-WB-075U-100D-935-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.0	3.3
10°-20°	468.1	8.6
20°-30°	606.3	11.1
30°-40°	593.7	10.9
40°-50°	454.5	8.3
50°-60°	302.8	5.5
60°-70°	165.2	3.0
70°-80°	68.8	1.3
80°-90°	20.5	0.4
90°-100°	188.3	3.4
100°-110°	518.1	9.5
110°-120°	534.8	9.8
120°-130°	428.5	7.8
130°-140°	336.5	6.2
140°-150°	257.9	4.7
150°-160°	185.4	3.4
160°-170°	113.4	2.1
170°-180°	38.2	0.7
0°-30°	1254.4	23.0
0°-40°	1848.1	33.8
0°-60°	2605.4	47.7
0°-90°	2860.0	52.4
90°-120°	1241.3	22.7
90°-150°	2264.2	41.5
90°-180°	2601.0	47.6
0°-180°	5461.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1962	1962	1962	1962	1962	
5°	1930	1911	1923	1928	1934	180
15°	1632	1626	1670	1716	1745	456
25°	1248	1251	1316	1373	1433	574
35°	882	886	945	1009	1080	548
45°	529	539	574	618	674	412
55°	304	316	335	348	376	276
65°	152	165	180	157	143	158
75°	77	77	70	48	33	82
85°	22	22	20	13	8	23
90°	1	3	6	8	8	3
95°	28	103	333	142	91	30
105°	93	142	571	870	811	98
115°	164	200	458	912	1035	162
125°	226	258	415	703	823	202
135°	273	303	404	568	643	210
145°	315	337	398	484	522	198
155°	357	368	395	435	448	164
165°	386	391	397	413	415	109
175°	399	400	398	403	402	38
180°	399	399	399	399	399	

TEST NUMBER: P519228

CATALOG NUMBER: SQ4-WB-075U-100D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1962.0	1962.0	1962.0	1962.0	1962.0
2.5°	1966.8	1949.3	1953.7	1953.6	1948.2
5°	1930.1	1910.8	1923.3	1927.7	1934.5
7.5°	1858.5	1843.9	1866.6	1883.5	1897.1
10°	1802.7	1790.1	1819.1	1843.6	1861.3
12.5°	1738.0	1727.4	1763.3	1796.2	1819.3
15°	1632.3	1626.4	1670.2	1715.6	1745.1
17.5°	1519.2	1516.3	1566.5	1619.5	1657.2
20°	1442.0	1441.2	1496.3	1551.5	1595.3
22.5°	1364.2	1366.0	1423.9	1481.4	1531.2
25°	1247.5	1250.8	1315.5	1372.8	1433.4
27.5°	1139.5	1141.0	1207.8	1268.4	1333.0
30°	1065.8	1070.0	1135.5	1198.2	1265.5
32.5°	992.1	997.0	1061.2	1125.9	1194.6
35°	881.6	885.8	945.3	1008.9	1080.4
37.5°	767.6	773.3	826.1	886.3	956.6
40°	693.9	702.3	749.0	805.7	874.7
42.5°	623.0	633.4	676.7	730.4	792.7
45°	528.6	538.7	574.2	617.7	674.1
47.5°	447.3	458.9	486.2	523.7	571.8
50°	401.2	412.1	437.3	465.1	510.5
52.5°	360.5	371.5	394.0	415.3	454.0
55°	303.9	316.5	334.9	347.6	376.2
57.5°	257.4	269.5	284.1	289.8	307.2
60°	226.4	239.9	253.1	252.5	261.7
62.5°	198.2	209.6	222.8	213.7	214.2
65°	152.4	165.0	179.9	157.2	142.9
67.5°	123.1	125.8	141.2	109.6	92.6
70°	109.3	109.3	113.6	84.9	70.6
72.5°	96.2	96.2	92.3	69.0	54.1
75°	76.6	76.6	69.7	47.9	32.7
77.5°	59.1	58.4	53.4	35.7	23.8
80°	47.3	47.3	43.0	28.2	18.9
82.5°	37.0	37.0	33.4	22.0	14.1
85°	21.5	21.5	19.8	12.8	7.7
87.5°	7.7	8.2	8.1	5.6	5.0
90°	0.8	3.3	5.9	7.6	7.6
92.5°	11.7	50.1	86.8	33.3	27.4
95°	28.0	102.8	333.0	142.4	90.9
97.5°	45.7	114.0	508.2	391.6	276.3
100°	58.6	120.9	563.3	568.5	463.9
102.5°	70.9	129.2	577.5	705.3	609.3
105°	92.6	142.4	570.9	869.5	811.3
107.5°	113.3	158.9	538.5	949.9	967.2
110°	128.3	169.8	514.0	969.9	1029.7

TEST NUMBER: P519228

CATALOG NUMBER: SQ4-WB-075U-100D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	141.9	182.1	489.5	957.0	1048.0
115°	164.0	199.7	457.9	911.8	1034.8
117.5°	185.0	217.9	437.9	848.5	987.5
120°	198.0	229.5	429.0	801.0	944.7
122.5°	209.5	241.1	422.9	759.4	895.8
125°	226.0	257.6	415.4	702.8	823.2
127.5°	241.6	271.7	410.5	655.6	761.2
130°	249.8	280.5	407.8	627.5	723.8
132.5°	259.3	290.0	405.8	602.8	689.9
135°	272.7	302.6	403.5	568.4	643.1
137.5°	285.3	313.0	401.7	540.5	602.2
140°	294.8	320.6	401.0	522.1	577.7
142.5°	303.0	326.7	399.6	505.6	553.2
145°	315.2	336.8	397.6	484.3	521.6
147.5°	328.3	346.9	396.6	465.4	495.3
150°	336.4	353.0	395.9	455.1	478.3
152.5°	343.9	359.2	395.2	446.1	465.4
155°	356.8	368.5	395.1	435.3	447.7
157.5°	366.2	375.6	395.1	426.3	435.0
160°	373.0	380.4	395.1	421.5	428.2
162.5°	378.4	384.5	395.7	417.4	422.7
165°	385.7	390.7	396.8	412.9	415.4
167.5°	390.8	394.6	397.6	409.2	409.8
170°	394.2	396.7	397.6	407.8	407.8
172.5°	396.9	398.1	397.6	405.7	405.1
175°	399.3	400.1	397.6	402.7	401.8
177.5°	400.0	400.0	397.3	401.3	400.0
180°	399.3	399.3	399.3	399.3	399.3

(END OF REPORT)