

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519252

Luminaire Tested: **SQ4-WB-075U-125D-935-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519252
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-125D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6169.1 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519252
CATALOG NUMBER: SQ4-WB-075U-125D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519252

CATALOG NUMBER: SQ4-WB-075U-125D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	101	97	94	90	94	91	88	85	79	77	75	68	66	65	58	57	56	51
2	93	86	81	76	87	81	76	72	71	67	64	61	59	57	53	51	49	45
3	86	77	70	65	80	72	67	62	64	59	56	56	52	50	48	46	44	40
4	79	69	62	57	74	65	59	54	58	53	49	51	47	44	44	41	39	36
5	73	63	55	50	68	59	52	47	52	47	43	46	42	39	40	37	35	32
6	68	57	49	44	64	54	47	42	48	42	38	42	38	35	37	34	31	29
7	63	52	44	39	59	49	42	38	44	39	35	39	35	32	34	31	29	26
8	59	48	40	35	55	45	39	34	40	35	31	36	32	29	32	29	26	24
9	55	44	37	32	52	42	35	31	37	32	29	34	29	26	30	26	24	22
10	52	41	34	29	49	39	32	28	35	30	26	31	27	24	28	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22583	22583	22583
5°	22302	22222	22351
10°	21070	21261	21755
15°	19451	19902	20795
20°	17663	18328	19540
25°	15843	16706	18205
30°	14165	15092	16820
35°	12387	13283	15182
40°	10426	11254	13142
45°	8605	9347	10973
50°	7184	7831	9142
55°	6098	6720	7550
60°	5213	5827	6025
65°	4150	4901	3892
70°	3679	3825	2377
75°	3408	3101	1454
80°	3140	2853	1254
85°	2848	2615	1027



TEST NUMBER: P519252

CATALOG NUMBER: SQ4-WB-075U-125D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.5	3.6
10°-20°	584.0	9.5
20°-30°	756.4	12.3
30°-40°	740.7	12.0
40°-50°	567.0	9.2
50°-60°	377.8	6.1
60°-70°	206.2	3.3
70°-80°	85.9	1.4
80°-90°	25.3	0.4
90°-100°	188.3	3.1
100°-110°	518.1	8.4
110°-120°	534.8	8.7
120°-130°	428.5	6.9
130°-140°	336.5	5.5
140°-150°	257.9	4.2
150°-160°	185.4	3.0
160°-170°	113.4	1.8
170°-180°	38.2	0.6
0°-30°	1564.9	25.4
0°-40°	2305.6	37.4
0°-60°	3250.4	52.7
0°-90°	3567.8	57.8
90°-120°	1241.3	20.1
90°-150°	2264.2	36.7
90°-180°	2601.0	42.2
0°-180°	6169.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2448	2448	2448	2448	2448	
5°	2408	2384	2399	2405	2413	224
15°	2036	2029	2084	2140	2177	569
25°	1556	1560	1641	1713	1788	716
35°	1100	1105	1179	1259	1348	684
45°	660	672	716	771	841	514
55°	379	395	418	434	469	344
65°	190	206	224	196	178	198
75°	96	96	87	60	41	102
85°	27	27	25	16	10	29
90°	1	3	6	8	8	3
95°	28	103	333	142	91	30
105°	93	142	571	870	811	98
115°	164	200	458	912	1035	162
125°	226	258	415	703	823	202
135°	273	303	404	568	643	210
145°	315	337	398	484	522	198
155°	357	368	395	435	448	164
165°	386	391	397	413	415	109
175°	399	400	398	403	402	38
180°	399	399	399	399	399	

TEST NUMBER: P519252

CATALOG NUMBER: SQ4-WB-075U-125D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2447.7	2447.7	2447.7	2447.7	2447.7
2.5°	2453.7	2431.9	2437.4	2437.2	2430.5
5°	2408.0	2383.8	2399.4	2404.9	2413.3
7.5°	2318.6	2300.3	2328.7	2349.7	2366.7
10°	2249.0	2233.3	2269.4	2300.0	2322.1
12.5°	2168.2	2155.0	2199.8	2240.9	2269.6
15°	2036.4	2029.0	2083.6	2140.3	2177.1
17.5°	1895.2	1891.7	1954.3	2020.5	2067.5
20°	1799.0	1797.9	1866.7	1935.6	1990.2
22.5°	1701.9	1704.2	1776.4	1848.1	1910.3
25°	1556.3	1560.5	1641.1	1712.6	1788.3
27.5°	1421.6	1423.5	1506.9	1582.4	1663.0
30°	1329.6	1334.9	1416.6	1494.8	1578.8
32.5°	1237.7	1243.8	1323.8	1404.6	1490.3
35°	1099.8	1105.1	1179.3	1258.6	1347.9
37.5°	957.6	964.7	1030.6	1105.7	1193.5
40°	865.7	876.2	934.4	1005.1	1091.2
42.5°	777.2	790.2	844.2	911.3	989.0
45°	659.5	672.1	716.4	770.6	841.0
47.5°	558.1	572.6	606.6	653.3	713.4
50°	500.5	514.1	545.6	580.2	636.9
52.5°	449.8	463.5	491.5	518.1	566.4
55°	379.1	394.9	417.8	433.6	469.4
57.5°	321.1	336.3	354.4	361.6	383.2
60°	282.5	299.3	315.8	315.0	326.5
62.5°	247.2	261.5	278.0	266.6	267.2
65°	190.1	205.9	224.5	196.1	178.3
67.5°	153.6	156.9	176.1	136.8	115.6
70°	136.4	136.4	141.8	105.9	88.1
72.5°	120.1	120.1	115.1	86.1	67.4
75°	95.6	95.6	87.0	59.7	40.8
77.5°	73.7	72.8	66.6	44.6	29.6
80°	59.1	59.1	53.7	35.2	23.6
82.5°	46.2	46.2	41.7	27.5	17.6
85°	26.9	26.9	24.7	16.0	9.7
87.5°	9.6	10.1	9.8	6.7	5.8
90°	0.8	3.3	5.9	7.6	7.6
92.5°	11.7	50.1	86.8	33.3	27.4
95°	28.0	102.8	333.0	142.4	90.9
97.5°	45.7	114.0	508.2	391.6	276.3
100°	58.6	120.9	563.3	568.5	463.9
102.5°	70.9	129.2	577.5	705.3	609.3
105°	92.6	142.4	570.9	869.5	811.3
107.5°	113.3	158.9	538.5	949.9	967.2
110°	128.3	169.8	514.0	969.9	1029.7



TEST NUMBER: P519252

CATALOG NUMBER: SQ4-WB-075U-125D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.9	182.1	489.5	957.0	1048.0
115°	164.0	199.7	457.9	911.8	1034.8
117.5°	185.0	217.9	437.9	848.5	987.5
120°	198.0	229.5	429.0	801.0	944.7
122.5°	209.5	241.1	422.9	759.4	895.8
125°	226.0	257.6	415.4	702.8	823.2
127.5°	241.6	271.7	410.5	655.6	761.2
130°	249.8	280.5	407.8	627.5	723.8
132.5°	259.3	290.0	405.8	602.8	689.9
135°	272.7	302.6	403.5	568.4	643.1
137.5°	285.3	313.0	401.7	540.5	602.2
140°	294.8	320.6	401.0	522.1	577.7
142.5°	303.0	326.7	399.6	505.6	553.2
145°	315.2	336.8	397.6	484.3	521.6
147.5°	328.3	346.9	396.6	465.4	495.3
150°	336.4	353.0	395.9	455.1	478.3
152.5°	343.9	359.2	395.2	446.1	465.4
155°	356.8	368.5	395.1	435.3	447.7
157.5°	366.2	375.6	395.1	426.3	435.0
160°	373.0	380.4	395.1	421.5	428.2
162.5°	378.4	384.5	395.7	417.4	422.7
165°	385.7	390.7	396.8	412.9	415.4
167.5°	390.8	394.6	397.6	409.2	409.8
170°	394.2	396.7	397.6	407.8	407.8
172.5°	396.9	398.1	397.6	405.7	405.1
175°	399.3	400.1	397.6	402.7	401.8
177.5°	400.0	400.0	397.3	401.3	400.0
180°	399.3	399.3	399.3	399.3	399.3

(END OF REPORT)