

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519661

Luminaire Tested: **SQ4-025U-0D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519661
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1258.9 lumens
Efficiency: N/A
Efficacy: 153.5 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519661
CATALOG NUMBER: SQ4-025U-0D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519661

CATALOG NUMBER: SQ4-025U-0D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	882	11510	4044
100°	1013	9525	7499
105°	1065	6540	9261
110°	1120	4433	8956
115°	1160	3208	7303
120°	1180	2543	5590
125°	1188	2150	4286
130°	1167	1882	3348
135°	1148	1689	2697
140°	1150	1550	2239
145°	1150	1439	1888
150°	1158	1362	1645
155°	1175	1301	1470
160°	1181	1255	1353
165°	1190	1221	1284
170°	1197	1205	1237
175°	1199	1192	1207



TEST NUMBER: P519661

CATALOG NUMBER: SQ4-025U-0D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	94.7	7.5
100°-110°	248.9	19.8
110°-120°	258.1	20.5
120°-130°	207.0	16.4
130°-140°	162.4	12.9
140°-150°	124.6	9.9
150°-160°	89.8	7.1
160°-170°	54.9	4.4
170°-180°	18.6	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	601.6	47.8
90°-150°	1095.7	87.0
90°-180°	1259.0	100.0
0°-180°	1258.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	4	10	5	5	
95°	12	49	163	84	57	15
105°	45	68	275	418	390	48
115°	80	97	220	440	502	79
125°	111	124	200	339	400	98
135°	132	145	194	274	310	102
145°	153	163	192	233	252	96
155°	173	178	192	211	217	80
165°	187	189	192	199	202	53
175°	194	194	193	196	196	18
180°	194	194	194	194	194	



TEST NUMBER: P519661

CATALOG NUMBER: SQ4-025U-0D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.2	3.7	10.0	5.0	5.0
92.5°	5.2	25.2	55.8	24.7	15.9
95°	12.5	49.0	163.1	84.1	57.3
97.5°	21.7	53.8	244.0	194.1	142.9
100°	28.6	57.9	268.9	272.5	211.7
102.5°	34.6	61.9	275.9	339.5	287.4
105°	44.8	68.0	275.2	417.7	389.7
107.5°	55.3	76.7	259.5	458.3	465.2
110°	62.3	81.7	246.5	468.8	498.0
112.5°	69.2	87.7	234.6	462.2	507.0
115°	79.7	96.7	220.4	439.7	501.8
117.5°	89.9	105.5	210.7	408.5	477.4
120°	95.9	110.5	206.7	387.5	454.4
122.5°	101.8	116.5	203.7	366.6	432.5
125°	110.8	124.2	200.5	338.8	399.7
127.5°	118.0	131.7	197.7	316.4	367.8
130°	122.0	136.6	196.7	302.4	349.9
132.5°	126.0	140.6	195.7	290.3	332.9
135°	132.0	145.4	194.2	273.5	310.0
137.5°	138.2	151.3	194.0	260.9	290.8
140°	143.2	155.4	193.0	250.9	278.9
142.5°	147.2	158.4	193.0	243.8	267.9
145°	153.1	162.9	191.7	233.2	251.5
147.5°	159.1	168.6	191.7	224.5	239.6
150°	163.1	171.6	191.7	219.4	231.6
152.5°	167.1	173.7	191.7	215.4	224.6
155°	173.1	177.9	191.7	210.6	216.6
157.5°	177.5	182.2	191.7	206.3	210.7
160°	180.5	184.2	191.7	204.2	206.7
162.5°	183.5	186.2	191.7	202.3	204.7
165°	186.8	189.2	191.7	199.3	201.7
167.5°	189.7	191.0	193.0	198.0	199.0
170°	191.7	193.0	193.0	198.0	198.0
172.5°	192.7	193.0	193.0	196.9	196.0
175°	194.2	194.2	193.0	195.5	195.5
177.5°	194.2	194.2	193.2	195.2	194.2
180°	194.2	194.2	194.2	194.2	194.2

(END OF REPORT)