

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519685

Luminaire Tested: **SQ4-050U-0D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519685
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-050U-0D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2596.1 lumens
Efficiency: N/A
Efficacy: 143.4 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 18.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519685
CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519685

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	1983	23458	6860
100°	2083	19970	16347
105°	2189	13551	19416
110°	2322	9220	18509
115°	2381	6642	15053
120°	2422	5253	11560
125°	2413	4429	8802
130°	2386	3891	6888
135°	2357	3492	5561
140°	2351	3203	4609
145°	2352	2976	3888
150°	2388	2806	3378
155°	2403	2673	3019
160°	2427	2578	2795
165°	2443	2516	2630
170°	2451	2475	2531
175°	2455	2447	2471



TEST NUMBER: P519685

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	190.9	7.4
100°-110°	518.5	20.0
110°-120°	533.1	20.5
120°-130°	426.2	16.4
130°-140°	334.9	12.9
140°-150°	256.8	9.9
150°-160°	184.7	7.1
160°-170°	112.9	4.4
170°-180°	38.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1242.5	47.9
90°-150°	2260.4	87.1
90°-180°	2596.0	100.0
0°-180°	2596.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	5	9	12	12	
95°	28	104	332	145	97	32
105°	92	143	570	868	817	98
115°	164	199	456	908	1034	161
125°	225	256	413	696	821	201
135°	271	301	402	567	639	210
145°	313	336	396	482	518	197
155°	354	367	394	432	445	163
165°	384	389	395	412	413	108
175°	398	399	396	401	400	38
180°	398	398	398	398	398	

TEST NUMBER: P519685

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.3	5.0	8.9	11.5	11.5
92.5°	11.5	52.3	90.8	39.0	33.0
95°	28.1	104.4	332.4	144.7	97.2
97.5°	46.5	115.3	509.6	396.5	278.5
100°	58.8	122.6	563.8	571.5	461.5
102.5°	71.1	129.8	578.1	706.9	609.8
105°	92.1	143.3	570.2	868.2	817.0
107.5°	113.8	159.0	537.2	951.5	965.8
110°	129.1	170.4	512.7	967.9	1029.2
112.5°	142.4	181.7	488.1	954.3	1046.6
115°	163.6	198.7	456.4	908.1	1034.3
117.5°	183.6	217.1	436.2	842.4	984.7
120°	196.9	229.4	427.0	798.4	939.7
122.5°	208.1	240.6	420.9	754.3	890.6
125°	225.0	256.3	413.0	695.8	820.8
127.5°	240.1	271.1	408.6	651.4	758.7
130°	249.3	279.3	406.6	623.5	719.8
132.5°	258.5	288.5	404.5	599.8	685.0
135°	271.0	301.0	401.5	566.7	639.3
137.5°	284.6	311.8	399.9	537.6	598.6
140°	292.8	319.0	398.9	519.0	574.0
142.5°	301.0	325.2	397.9	504.5	550.5
145°	313.2	335.7	396.3	481.5	517.8
147.5°	327.0	346.3	395.1	463.5	492.0
150°	336.2	352.5	395.1	453.1	475.6
152.5°	343.4	357.7	394.0	443.8	462.3
155°	354.1	366.6	393.8	432.4	444.9
157.5°	364.6	374.4	393.8	424.7	434.2
160°	370.8	379.5	393.8	419.5	427.0
162.5°	376.9	383.7	394.8	415.4	420.9
165°	383.6	388.6	395.1	411.7	413.0
167.5°	390.5	393.0	396.3	407.4	408.4
170°	392.5	395.0	396.3	405.3	405.3
172.5°	394.5	396.0	396.3	403.2	403.2
175°	397.6	398.9	396.3	401.4	400.2
177.5°	398.6	398.6	395.6	399.6	397.6
180°	397.6	397.6	397.6	397.6	397.6

(END OF REPORT)