

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519767

Luminaire Tested: **SQ4-150U-0D-835-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519767
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18071.9 lumens
Efficiency: N/A
Efficacy: 156.5 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 115.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519767
CATALOG NUMBER: SQ4-150U-0D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519767

CATALOG NUMBER: SQ4-150U-0D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	7135	76444	23529
100°	7375	66475	56054
105°	7779	46428	65680
110°	8166	32230	61939
115°	8387	23581	51531
120°	8500	18614	40327
125°	8461	15660	31045
130°	8329	13743	24324
135°	8228	12362	19592
140°	8213	11338	16232
145°	8258	10524	13763
150°	8336	9890	11947
155°	8426	9429	10709
160°	8542	9105	9845
165°	8607	8886	9280
170°	8640	8725	8932
175°	8663	8625	8718



TEST NUMBER: P519767

CATALOG NUMBER: SQ4-150U-0D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	1302.7	7.2
100°-110°	3522.1	19.5
110°-120°	3703.0	20.5
120°-130°	3007.8	16.6
130°-140°	2359.4	13.1
140°-150°	1810.8	10.0
150°-160°	1302.3	7.2
160°-170°	795.6	4.4
170°-180°	268.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	8527.7	47.2
90°-150°	15705.8	86.9
90°-180°	18072.0	100.0
0°-180°	18071.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	6	18	39	42	39	
95°	202	710	2166	1121	667	224
105°	655	1012	3907	5764	5528	690
115°	1153	1409	3240	6273	7081	1138
125°	1578	1808	2921	4929	5790	1407
135°	1892	2116	2842	3980	4505	1462
145°	2200	2365	2803	3406	3666	1376
155°	2483	2580	2779	3056	3156	1145
165°	2703	2730	2791	2900	2915	762
175°	2806	2803	2794	2830	2824	266
180°	2803	2803	2803	2803	2803	



TEST NUMBER: P519767

CATALOG NUMBER: SQ4-150U-OD-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	6.0	17.8	39.2	42.2	39.2
92.5°	85.7	312.3	616.1	267.5	193.7
95°	202.2	709.6	2166.4	1121.1	666.8
97.5°	324.7	813.8	3376.9	2794.6	2052.3
100°	416.4	855.9	3753.4	3914.4	3165.0
102.5°	500.9	914.5	3886.2	4763.5	4203.0
105°	654.7	1011.7	3907.3	5763.5	5527.5
107.5°	797.1	1122.8	3736.5	6387.4	6465.9
110°	908.2	1203.2	3584.4	6554.9	6888.3
112.5°	1007.1	1283.3	3444.4	6521.4	7081.4
115°	1152.6	1409.2	3240.5	6273.0	7081.4
117.5°	1295.0	1535.7	3105.9	5893.5	6809.8
120°	1381.9	1617.9	3026.3	5621.2	6556.4
122.5°	1463.9	1695.2	2978.0	5329.3	6271.6
125°	1578.0	1808.1	2920.7	4928.6	5790.0
127.5°	1683.0	1909.0	2886.9	4601.6	5359.2
130°	1740.9	1974.0	2872.4	4399.5	5084.0
132.5°	1801.3	2032.0	2857.9	4217.3	4847.4
135°	1891.8	2116.0	2842.2	3979.6	4504.7
137.5°	1982.9	2194.7	2828.9	3786.7	4214.4
140°	2045.7	2243.3	2824.1	3662.5	4043.1
142.5°	2106.0	2291.9	2814.4	3550.4	3883.7
145°	2199.5	2364.7	2803.0	3406.3	3665.9
147.5°	2284.6	2431.0	2789.7	3275.8	3475.2
150°	2347.4	2477.2	2784.9	3204.9	3364.2
152.5°	2405.3	2518.6	2782.5	3139.1	3270.0
155°	2483.2	2580.5	2778.8	3055.7	3156.0
157.5°	2564.0	2631.9	2779.4	2997.6	3063.7
160°	2609.9	2665.9	2781.9	2960.9	3008.2
162.5°	2646.1	2692.7	2784.3	2931.7	2967.1
165°	2703.4	2730.0	2790.9	2899.9	2914.6
167.5°	2742.6	2760.9	2791.5	2872.5	2879.6
170°	2766.8	2775.6	2793.9	2860.3	2860.3
172.5°	2786.1	2787.9	2793.9	2845.8	2843.4
175°	2806.0	2803.0	2793.9	2830.0	2824.1
177.5°	2812.6	2805.6	2793.3	2817.3	2810.2
180°	2803.0	2803.0	2803.0	2803.0	2803.0

(END OF REPORT)